



# **RF Cable Assemblies Technical Data Sheet**

# PE3C3469

# Configuration


• Connector 1: 1.0/2.3 Plug Right Angle

• Connector 2: BNC Male

Cable Type: RG316

#### **Features**

- Max Frequency 3 GHz
- 69% Phase Velocity
- FEP Jacket



# **Applications**

· General Purpose

Laboratory Use

#### Description

Pasternack's PE3C3469 1.0/2.3 plug right angle to BNC male cable using RG316 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 1.0/2.3 to BNC cable assembly has a plug to male gender configuration with 50 ohm flexible RG316 coax. The PE3C3469 1.0/2.3 plug to BNC male cable assembly operates to 3 GHz. The right angle 1.0/2.3 interface on the RG316 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

### **Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.5:1	
Velocity of Propagation		69		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]
DC Resistance Inner Conductor		8.41 [27.59]		Ω/1000ft [Ω/Km]
Jacket Spark			2,000	Vrms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.0/2.3 Plug Right Angle to BNC Male Cable Using RG316 Coax PE3C3469

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# **RF Cable Assemblies Technical Data Sheet**

### PE3C3469

#### **Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	3	GHz
Insertion Loss (Max.)	0.16	0.24	0.38	0.53	0.58	dB/ft
	0.52	0.79	1.25	1.74	1.9	dB/m

**Electrical Specification Notes:** 

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.3dB connector loss.

### **Mechanical Specifications**

#### Cable Assembly

Diameter 0.57 in [14.48 mm]

#### Cable

Cable Type **RG316** Impedance 50 Ohms Inner Conductor Type Stranded

Inner Conductor Material and Plating Copper Clad Steel, Silver **PTFE** 

Dielectric Type Number of Shields Shield Layer 1 Jacket Material

Jacket Diameter 0.102 in [2.59 mm]

FEP, Tan

### Connectors

Description	Connector 1	Connector 2	
Туре	1.0/2.3 Plug Right Angle	BNC Male	
Specification		MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Brass, Gold	Brass, Gold	
Contact Plating Specification	30 μin minimum	50μ in. minimum	
Dielectric Type	PTFE	Teflon	
Body Material and Plating	Brass, Nickel	Brass, Nickel	
Body Plating Specification	100 µin minimum	100μ in. minimum	
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	100µ in. minimum	

Silver Plated Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.0/2.3 Plug Right Angle to BNC Male Cable Using RG316 Coax PE3C3469

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





# **RF Cable Assemblies Technical Data Sheet**

PE3C3469

Mechanical Specification Notes:

\*All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.


Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

• Values at 25°C, sea level.

#### **Typical Performance Data**



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.0/2.3 Plug Right Angle to BNC Male Cable Using RG316 Coax PE3C3469





# **RF Cable Assemblies Technical Data Sheet**

PE3C3469

#### **How to Order**



Example: PE3C3469-12 = 12 inches long cable PE3C3469-100cm = 100 cm long cable

1.0/2.3 Plug Right Angle to BNC Male Cable Using RG316 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 1.0/2.3 Plug Right Angle to BNC Male Cable Using RG316 Coax PE3C3469

URL: https://www.pasternack.com/1.0-2.3-plug-bnc-male-rg316u-cable-assembly-pe3c3469-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

**PE3C3469 CAD Drawing**1.0/2.3 Plug Right Angle to BNC Male Cable Using RG316 Coax

