



Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug
Right Angle Cable Using RG178 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE3C3987LF

Configuration

- Connector 1: Snap-OnMMBX Plug Right Angle
- Connector 2: Snap-OnMMBX Plug Right Angle
- Cable Type: RG178

Features

- Max Frequency 3 GHz
- 70% Phase Velocity
- FEP Jacket
- 100 Mating Cycles
- Snap-On mating

Applications

- General Purpose
- Laboratory Use
- PCB Probing
- PCB Testing
- PCB-to-Panel

Description

Pasternack's MMBX cable assemblies are part of our full line of RF components available for same-day shipping. These MMBX cable assemblies are designed to connect MMBX system components or test connections, delivering signal frequencies as high as 3 GHz. Our family of MMBX cables can also be used to connect from PCB to panel, offering between series MMBX options with SMA Bulkhead, TNC Bulkhead and N Bulkhead assembly configurations. If none of our standard options fit your application, you can specify your own custom MMBX cable assembly using Pasternack's online Cable Creator.

Our MMBX cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug Right Angle Cable Using RG178 Coax , LF Solder PE3C3987LF](#)



Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug
Right Angle Cable Using RG178 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE3C3987LF

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Return Loss		-15.56		dB
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.138	0.208	0.305	0.444	0.784	dB/ft
	0.45	0.68	1	1.46	2.57	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.31 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.013 lbs [5.9 g]

Cable

Cable Type RG178
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Silver Plated Copper Braid
Jacket Material FEP, Tan
Jacket Diameter 0.072 in [1.83 mm]

Repeated Minimum Bend Radius 0.4 in [10.16 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug Right Angle Cable Using RG178 Coax , LF Solder PE3C3987LF](#)

Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug
Right Angle Cable Using RG178 Coax , LF Solder



RF Cable Assemblies Technical Data Sheet

PE3C3987LF

Connectors

Description	Connector 1	Connector 2
Type	MMBX Plug Right Angle	MMBX Plug Right Angle
Impedance	50 Ohms	50 Ohms
Connection Method	Snap-On	Snap-On
Mating Cycles	100	100
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Gold	Brass, Gold
Body Material and Plating	Brass, Gold	Brass, Gold

Environmental Specifications

Temperature

Operating Range -55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug Right Angle Cable Using RG178 Coax , LF Solder PE3C3987LF](#)



Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug
Right Angle Cable Using RG178 Coax , LF Solder

RF Cable Assemblies Technical Data Sheet

PE3C3987LF

How to Order

Part Number Configuration:

PE3C3987LF

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C3987LF-12 = 12 inches long cable
PE3C3987LF-100cm = 100 cm long cable


Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug Right Angle Cable Using RG178 Coax , LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug Right Angle Cable Using RG178 Coax , LF Solder PE3C3987LF](#)

URL: <https://www.pasternack.com/snap-on-mmbx-plug-right-angle-to-snap-on-mmbx-plug-cable-using-rg178-lf-solder-pe3c3987lf-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C3987LF CAD Drawing
Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug
Right Angle Cable Using RG178 Coax , LF Solder



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS	
TOLERANCES:	
X = ±.2 [.5]	FRACTIONS ± 1/32
.XX = ±.02 [.5]	ANGLES ± 1°
XXX = ±.005 [.13]	CABLE LENGTH TOLERANCES:
	>12 [305] = +1 [25] / -0
	>12 [305] ≤ 60 [1524] = +2 [9.1] / -0
	>60 [1524] ≤ 120 [3048] = +4 [1.02] / -0
	>120 [3048] ≤ 300 [7620] = +6 [1.52] / -0
	>300 [7620] = +5% / -0
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.	



Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

DESCRIPTION Snap-On MMBX Plug Right Angle to Snap-On MMBX Plug Right Angle Cable Using RG178 Coax , LF Solder	
SIZE	CAGE CODE
A	53919
DRAWN BY	
HBAKKE	
ITEM NO.	
PE3C3987LF	
REV	A

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
SCALE	SHEET
NONE	1 OF 1