



Handheld RF Analyzer Rugged Phase Stable  
Cable N Male to 7/16 DIN Female Cable 60 Inch  
Length Using PE-FF430 Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE3C4001-60

**Configuration**

- Connector 1: N Male
- Connector 2: 7/16 DIN Female
- Cable Type: PE-FF430

**Features**

- Excellent VSWR and Insertion Loss
- Excellent Amplitude and Phase Stability with Flexure
- Rugged Armor provides crush and torque resistance
- UV resistant jacket
- Each serialized assembly includes test data
- In stock and ready to ship



**Applications**

- Field Testing
- Tower Measurements
- Base Station Analyzers
- Handheld Network Analyzers
- Portable Spectrum Analyzers
- Distance-To-Fault Measurements
- Site Maintenance

**Description**

Pasternack's Handheld RF Analyzer Phase Stable cable assemblies are designed for use with portable and handheld network analyzers, spectrum analyzers and base station analyzers. These rugged portable analyzer cable assemblies offer a unique combination of low loss, phase stability, low VSWR and durability. The tough analyzer cable armor offers crush resistance, torque resistance, water resistance and UV resistance while still maintaining a high level of flexibility. These rugged handheld analyzer cable assemblies are compatible with Fieldfox®, Site Master, CellAdvisor® and Sitehawk® analyzers, supporting site maintenance, field testing, antenna testing and distance-to-fault measurements.

**Electrical Specifications**

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		7	GHz
VSWR			1.2:1	
Phase Stability with Flexure			1.5	Degrees
Amplitude Stability with Flexure			0.1	dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Handheld RF Analyzer Rugged Phase Stable Cable N Male to 7/16 DIN Female Cable 60 Inch Length Using PE-FF430 Coax, RoHS PE3C4001-60](#)



Handheld RF Analyzer Rugged Phase Stable  
Cable N Male to 7/16 DIN Female Cable 60 Inch  
Length Using PE-FF430 Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE3C4001-60

**Specifications by Frequency**

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	7			GHz
Insertion Loss (Max.)	0.71	1.31	2.16			dB
Power Handling (Max.)	522	277	190			Watts

Electrical Specification Notes:  
Values at 25°C, sea level.

**Mechanical Specifications**

**Cable Assembly**

Length\* 60 in [152.4 cm]  
Weight 1.046 lbs [474.46 g]

**Cable**

Cable Type PE-FF430  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper, Silver  
Dielectric Type PTFE  
Number of Shields 6  
Shield Layer 1 Silver Plated Copper Tape  
Shield Layer 2 Metalized Polyimide  
Shield Layer 3 Silver Plated Copper Braid  
Jacket Material TPE  
Jacket Diameter 0.43 in [10.92 mm]  
  
One Time Minimum Bend Radius 1.5 in [38.1 mm]  
Flat Plate Crush 1,200 lbs/in [21.43 Kg/mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Handheld RF Analyzer Rugged Phase Stable Cable N Male to 7/16 DIN Female Cable 60 Inch Length Using PE-FF430 Coax, RoHS PE3C4001-60](#)



Handheld RF Analyzer Rugged Phase Stable  
Cable N Male to 7/16 DIN Female Cable 60 Inch  
Length Using PE-FF430 Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE3C4001-60

**Connectors**

Description	Connector 1	Connector 2
Type	N Male	7/16 DIN Female
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Passivated Stainless Steel
Body Material and Plating	Passivated Stainless Steel	Passivated Stainless Steel
Coupling Nut Material and Plating	Passivated Stainless Steel	

**Mechanical Specification Notes:**

\*All cable assemblies have a length tolerance of 1.5% or  $\pm 3/8$ ", whichever is greater.  
Fieldfox® is a registered trademark of Keysight Technologies  
CellAdvisor® is registered trademark Viavi Solutions  
SiteHawk® is a registered trademark of Bird Technologies

**Environmental Specifications**

**Temperature**

Operating Range -55 to +105 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Handheld RF Analyzer Rugged Phase Stable Cable N Male to 7/16 DIN Female Cable 60 Inch Length Using PE-FF430 Coax, RoHS PE3C4001-60](#)




Handheld RF Analyzer Rugged Phase Stable  
Cable N Male to 7/16 DIN Female Cable 60 Inch  
Length Using PE-FF430 Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE3C4001-60

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Handheld RF Analyzer Rugged Phase Stable Cable N Male to 7/16 DIN Female Cable 60 Inch Length Using PE-FF430 Coax, RoHS PE3C4001-60](#)



Handheld RF Analyzer Rugged Phase Stable  
Cable N Male to 7/16 DIN Female Cable 60 Inch  
Length Using PE-FF430 Coax, RoHS

RF Cable Assemblies Technical Data Sheet

PE3C4001-60

**How to Order**

Part Number Configuration:

**PE3C4001**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C4001-12 = 12 inches long cable  
PE3C4001-100cm = 100 cm long cable

Handheld RF Analyzer Rugged Phase Stable Cable N Male to 7/16 DIN Female Cable 60 Inch Length Using PE-FF430 Coax, RoHS from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Handheld RF Analyzer Rugged Phase Stable Cable N Male to 7/16 DIN Female Cable 60 Inch Length Using PE-FF430 Coax, RoHS PE3C4001-60](https://www.pasternack.com/n-male-7-16-din-female-pe-ff430-cable-assembly-pe3c4001-60)

URL: <https://www.pasternack.com/n-male-7-16-din-female-pe-ff430-cable-assembly-pe3c4001-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C4001-60 CAD Drawing

Handheld RF Analyzer Rugged Phase Stable Cable N Male to 7/16 DIN  
 Female Cable 60 Inch Length Using PE-FF430 Coax, RoHS



- NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
  2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
  3. DIMENSIONS ARE IN INCHES [mm].
  4. LENGTH TOLERANCE IS  $\pm 2\%$

DWG TITLE  
**PE3C4001**

CAGE CODE **53919**

CAD FILE 041717

SCALE N/A

SIZE A

2233

**PE PASTERNAK**  
 THE ENGINEER'S RF SOURCE  
 Pasternack Enterprises, Inc.  
 P.O. Box 16759 | Irvine | CA | 92623  
 Phone: (949) 261-1920 | Fax: (949) 261-7451  
 Website: www.pasternack.com | E-Mail: sales@pasternack.com