



Snap-On MMBX Plug to Reverse Polarity SMA Female Bulkhead Cable Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4038

Configuration

- Connector 1: Snap-On MMBX Plug
- Connector 2: SMA Female Reverse Polarity Bulkhead
- Cable Type: RG174

Features

- Max. Operating Frequency of 3 GHz
- Snap-On mating
- Low Profile Right Angle Configurations
- SMA Bulkhead, N Bulkhead and TNC Bulkhead Between-Series Configurations

Applications

- General Purpose Test
- PCB Probing
- PCB Testing
- PCB-to-Panel

Description

Pasternack's MMBX cable assemblies are part of our full line of RF components available for same-day shipping. These MMBX cable assemblies are designed to connect MMBX system components or test connections, delivering signal frequencies as high as 3 GHz. Our family of MMBX cables can also be used to connect from PCB to panel, offering between series MMBX options with SMA Bulkhead, TNC Bulkhead and N Bulkhead assembly configurations. If none of our standard options fit your application, you can specify your own custom MMBX cable assembly using Pasternack's online Cable Creator.

Our MMBX cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide an I/O for a board design, or simply create a custom cable assembly configuration, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Return Loss		-15.56		dB
Velocity of Propagation		66		%
Capacitance		31.1 [102.03]		pF/ft [pF/m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug to Reverse Polarity SMA Female Bulkhead Cable Using RG174 Coax PE3C4038](#)



Snap-On MMBX Plug to Reverse Polarity SMA Female Bulkhead Cable Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4038

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Max.)	0.06	0.08	0.14	0.22	0.32	dB/ft
	0.2	0.26	0.46	0.72	1.05	dB/m
						dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1dB per connector.

Mechanical Specifications

Cable Assembly

Diameter

0.315 in [8 mm]

Cable

Cable Type

RG174

Impedance

50 Ohms

Inner Conductor Type

Stranded

Inner Conductor Material and Plating

Copper Clad Steel, Silver

Dielectric Type

PE

Number of Shields

1

Shield Layer 1

Tinned Copper Braid

Jacket Material

PVC, Black

Jacket Diameter

0.11 in [2.79 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug to Reverse Polarity SMA Female Bulkhead Cable Using RG174 Coax PE3C4038](#)



Snap-On MMBX Plug to Reverse Polarity SMA
Female Bulkhead Cable Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4038

Connectors

Description	Connector 1	Connector 2
Type	MMBX Plug	SMA Female Reverse Polarity Bulkhead
Impedance	50 Ohms	50 Ohms
Connection Method	Snap-On	
Mating Cycles	100	
Contact Material and Plating	Beryllium Copper, Gold	Brass, Gold
Contact Plating Specification		50 µin minimum
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Gold	
Body Material and Plating	Brass, Gold	Brass, Nickel
Body Plating Specification		100 µin minimum

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug to Reverse Polarity SMA Female Bulkhead Cable Using RG174 Coax PE3C4038](#)



Snap-On MMBX Plug to Reverse Polarity SMA Female Bulkhead Cable Using RG174 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4038

How to Order

Part Number Configuration:

PE3C4038

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C4038-12 = 12 inches long cable
PE3C4038-100cm = 100 cm long cable


Snap-On MMBX Plug to Reverse Polarity SMA Female Bulkhead Cable Using RG174 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Snap-On MMBX Plug to Reverse Polarity SMA Female Bulkhead Cable Using RG174 Coax PE3C4038](https://www.pasternack.com/mmbx-plug-sma-female-rg174au-cable-assembly-pe3c4038-p.aspx)

URL: <https://www.pasternack.com/mmbx-plug-sma-female-rg174au-cable-assembly-pe3c4038-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C4038 CAD Drawing
Snap-On MMBX Plug to Reverse Polarity SMA Female
Bulkhead Cable Using RG174 Coax



NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE3C4038

Pasternack®
THE ENGINEER'S RF SOURCE
Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623
Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

CAGE CODE 53919

CAD FILE 052317

SCALE N/A

SIZE A

9999