

Push-On SMP Female to Straight Cut Lead Cable Using RG178 Coax

PE3C3799




Configuration

- Connector 1: Push-On SMP Female
- Connector 2: Straight Cut Lead
- Cable Type: RG178
- Coax Flex Type: Flexible

Features

- 70% Phase Velocity
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C3799 50 ohm SMP female push-on to straight cut lead cable using RG178 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|---------|--------------|---------|--------------|
| Velocity of Propagation | | 70 | | % |
| Capacitance | | 29.4 [96.46] | | pF/ft [pF/m] |

Mechanical Specifications

Cable Assembly

Weight 0.007 lbs [3.18 g]

Cable

| | |
|--------------------------------------|----------------------------|
| Cable Type | RG178 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Stranded |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 1 |
| Shield Layer 1 | Silver Plated Copper Braid |

Push-On SMP Female to Straight Cut Lead Cable Using RG178 Coax



PE3C3799

| | |
|------------------------------|--------------------|
| Jacket Material | FEP, Tan |
| Jacket Diameter | 0.072 in [1.83 mm] |
| Repeated Minimum Bend Radius | 0.4 in [10.16 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|---------------------------------------|------------------------|-------------------|
| Type | SMP Female | Straight Cut Lead |
| Specification | MIL-STD-348A | |
| Impedance | 50 Ohms | 0 Ohms |
| Configuration | Straight | Straight |
| Connection Method | Push-On | |
| Contact Material and Plating | Beryllium Copper, Gold | |
| Contact Plating Specification | MIL-DTL-45204 | |
| Dielectric Type | PTFE | |
| Outer Conductor Material and Plating | Beryllium Copper, Gold | |
| Outer Conductor Plating Specification | MIL-DTL-45204 | |
| Body Material and Plating | Beryllium Copper, Gold | |
| Body Plating Specification | MIL-DTL-45204 | |

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Push-On SMP Female to Straight Cut Lead Cable Using RG178 Coax



PE3C3799

Typical Performance Data

How to Order

Part Number Configuration:

PE3C3799

- xx

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3C3799-12 = 12 inches long cable
PE3C3799-100cm = 100 cm long cable

Push-On SMP Female to Straight Cut Lead Cable Using RG178 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Push-On SMP Female to Straight Cut Lead Cable Using RG178 Coax PE3C3799](https://www.pasternack.com/push-on-smp-female-to-straight-cut-lead-cable-using-rg178-coax-pe3c3799-p.aspx)

URL: <https://www.pasternack.com/push-on-smp-female-to-straight-cut-lead-cable-using-rg178-pe3c3799-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C3799 CAD Drawing
Push-On SMP Female to Straight Cut Lead Cable Using RG178 Coax

