

Waterproof IP68 SMA Male (Plug) to TNC Male (Plug) Low Loss Cable Using LMR®-195 Coax with Times Microwave Components



PE3C4164/WP

Configuration

- Connector 1: SMA Male
- Connector 2: TNC Male
- Cable Type: LMR®-195
- Coax Flex Type: Flexible

Features

- Shielding Effectivity > 90 dB
- 80% Phase Velocity
- Double Shielded
- PE Jacket
- Silicone Connector Boot
- IP68 Rated

Applications

- General Purpose
- Laboratory Use

Description

The Pasternack PE3C4164/WP is a weatherproof low loss cable assembly that comes with SMA male connection with weatherproof boot on one end and TNC male on the other. Pasternack's RF coaxial cable assembly products are designed for typical use, production, laboratory test and measurement, defense/military, aerial antenna towers, etc. The low loss cable has a 50 Ohm impedance and is specifically ready for quicker shipment than most in the industry can provide.

Our RF cable assembly has a PE jacket with 0.195 inches diameter. The SMA male to TNC male cable assembly PE3C4164/WP is built with LMR®-195 coax, which has a flexible design. This RF cable assembly with 0.5 inches diameter has copper as cable's inner conducting material and PE (F) dielectric type. The weatherproof boot low loss cable is reusable and can withstand elements including extreme temperature. Additional dimensions, specifications, and CAD drawings for this PE3C4164/WP low loss RF cable are available on our downloadable PDF datasheet.

Pasternack stocks a wide selection of weatherproof low loss cable assemblies that ship the same business day as ordered from our warehouse. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal SMA male to TNC male cable assembly as per your requirements.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		80		%
RF Shielding	90			dB
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.6 [24.93]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			1,000	Vdc

Waterproof IP68 SMA Male (Plug) to TNC Male (Plug) Low Loss Cable Using LMR®-195 Coax with Times Microwave Components



PE3C4164/WP

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			3,000	Vrms

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.582 lbs [263.99 g]

Cable

Cable Type	LMR®-195
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	TNC Male
Option	Weatherproof Boot	
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Beryllium Copper, Gold
Contact Plating Specification	ASTM B488	
Dielectric Type	Teflon	Teflon
Body Material and Plating	Passivated Stainless Steel	Brass, Silver
Coupling Nut Material and Plating	Passivated Stainless Steel	Brass, Silver
Boot Material	Silicone	Silicone

Environmental Specifications

Ingress Protection (IP) Rating	IP68
--------------------------------	------

Waterproof IP68 SMA Male (Plug) to TNC Male (Plug) Low Loss Cable Using LMR®-195 Coax with Times Microwave Components



PE3C4164/WP

Compliance Certifications (see product page for current document)

Plotted and Other Data


Notes:

Values at 25°C, sea level.

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C4164/WP-12 = 12 inches long cable
PE3C4164/WP-100cm = 100 cm long cable

Waterproof IP68 SMA Male (Plug) to TNC Male (Plug) Low Loss Cable Using LMR®-195 Coax with Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Waterproof IP68 SMA Male \(Plug\) to TNC Male \(Plug\) Low Loss Cable Using LMR®-195 Coax with Times Microwave Components PE3C4164/WP](#)

URL: <https://www.pasternack.com/waterproof-ip68-sma-male-plug-to-tnc-male-plug-low-loss-cable-using-lmr-195-pe3c4164-wp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C4164/WP CAD Drawing

Waterproof IP68 SMA Male (Plug) to TNC Male (Plug) Low Loss Cable
Using LMR®-195 Coax with Times Microwave Components

