



N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax

RF Cable Assemblies Technical Data Sheet


PE3C4489-6

Configuration

- Connector 1: N Male
- Connector 2: SSMC Plug Right Angle
- Cable Type: PE-SR405FLJ

Features

- SSMC Cable Assembly Max. Operating Frequency of 11 GHz
- Small SSMC cable connection form factor (50% smaller than SMA, radially)
- Reliable threaded coupling
- In stock and ready to ship



Applications

- SSMC Cable General Purpose Test
- Data Acquisition Systems
- A/D Conversion Systems
- Ultra Wideband Digital Receivers
- Software defined radio (SDR)

Description

Pasternack's SSMC cable assemblies are part of our full line of RF components available for same-day shipping. These SSMC cable assemblies are designed to connect SSMC system components and test connections, delivering signal frequencies as high as 12.4 GHz. Our family of SSMC cables can also be used to connect SSMC ports on data acquisition systems, A/D modules or SSMC coax patch panels. If none of our standard options fit your application, you can specify your own custom SSMC cable assembly using Pasternack's online Cable Creator.

Our SSMC cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide SSMC cabling for a data acquisition system, or simply create a custom cable assembly configuration, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		11	GHz
VSWR			1.5:1	
Velocity of Propagation		69.5		%
RF Shielding	100			dB
Group Delay	1.43 [4.69]			ns/ft [ns/m]
Capacitance	29 [95.14]			pF/ft [pF/m]
DC Resistance Inner Conductor	65.7 [215.55]			Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor	10.2 [33.46]			Ω/1000ft [Ω/Km]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax PE3C4489-6](#)


**N Male to SSMC Plug Right Angle Cable 6 Inch
Length Using PE-SR405FLJ Coax**
RF Cable Assemblies Technical Data Sheet
PE3C4489-6
Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	5	11		GHz
Insertion Loss (Max.)	0.28	0.32	0.48	0.63		dB

Mechanical Specifications
Cable Assembly

Length*
Diameter

6 in [152.4 mm]
0.79 in [20.07 mm]

Cable

Cable Type
Impedance
Inner Conductor Type
Inner Conductor Material and Plating
Dielectric Type
Number of Shields
Outer Conductor Material and Plating
Jacket Material
Jacket Diameter

PE-SR405FLJ
50 Ohms
Solid
Copper Clad Steel, Silver
PTFE
1
Tinned Copper Composite Braid
FEP, Black
0.105 in [2.67 mm]

One Time Minimum Bend Radius
Repeated Minimum Bend Radius

0.5 in [12.7 mm]
0.787 in [19.99 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax PE3C4489-6](#)



N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3C4489-6

Connectors

Description	Connector 1	Connector 2
Type	N Male	SSMC Plug Right Angle
Impedance	50 Ohms	50 Ohms
Mating Cycles		500
Contact Material and Plating	Brass, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification		MIL-G-45204
Dielectric Type	PTFE	Teflon
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification		MIL-G-45204
Coupling Nut Material and Plating	Brass, Nickel	Beryllium Copper, Gold
Coupling Nut Plating Specification		MIL-G-45204
Torque		1.75 in-lbs [0.2 Nm]

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8"$, whichever is greater.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax PE3C4489-6](#)



N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3C4489-6

How to Order

Part Number Configuration:

PE3C4489

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C4489-12 = 12 inches long cable
PE3C4489-100cm = 100 cm long cable

N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax PE3C4489-6](#)

URL: <https://www.pasternack.com/n-male-ssmc-plug-pe-sr405flj-cable-assembly-pe3c4489-6-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C4489-6 CAD Drawing

N Male to SSMC Plug Right Angle Cable 6 Inch Length Using PE-SR405FLJ Coax



SSMC PLUG RIGHT ANGLE CONNECTOR



N MALE CONNECTOR

PE-SR405FLJ COAX CABLE

LENGTH MEASURED FROM
CONTACT TO CONTACT

STANDARD TOLERANCES	
X	±0.2
.XX	±0.01
.XXX	±0.005

*STANDARD TOLERANCES APPLY
ONLY TO DIMENSIONS IN INCHES



Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451

Website: www.pasternack.com | E-Mail: sales@pasternack.com

DWG TITLE	PE3C4489
CAGE CODE	53919

NOTES:	1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].
CN2245	SCALE N/A SIZE A