



2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax

TECHNICAL DATA SHEET



PE3C4838

Configuration

- Connector 1: 2.92mm Male
- Connector 2: Mini SMP Female
- Cable Type: PE-P086HF
- Coax Flex Type: Flexible

Features

- Max Frequency 40 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C4838 2.92mm male to Mini SMP female cable using PE-P086HF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 2.92mm to Mini SMP cable assembly has a male to female gender configuration with 50 ohm flexible PE-P086HF coax. The PE3C4838 2.92mm male to Mini SMP female cable assembly operates to 40 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax PE3C4838](#)



2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax

TECHNICAL DATA SHEET

PE3C4838

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.4:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	2500	5000	10000	20000	40000	MHz	
PE3C4838	Custom Lengths Available	Insertion Loss (Typ.)	0.34	0.5	0.743	1.106	1.703	dB/ft	
			1.12	1.65	2.44	3.63	5.59	dB/m	
PE3C4838-12	12 inch	Insertion Loss (Typ.)	0.49	0.71	1.03	1.51	2.28	dB	0.029
PE3C4838-18	18 inch	Insertion Loss (Typ.)	0.66	0.96	1.4	2.07	3.13	dB	0.036
PE3C4838-24	24 inch	Insertion Loss (Typ.)	0.83	1.21	1.78	2.62	3.98	dB	0.043
PE3C4838-36	36 inch	Insertion Loss (Typ.)	1.17	1.71	2.52	3.73	5.68	dB	0.056
PE3C4838-48	48 inch	Insertion Loss (Typ.)	1.51	2.21	3.26	4.83	7.39	dB	0.069

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.04*SQRT(FGHz) dB

Loss due to Connector 2: 0.05*SQRT(FGHz) dB

Base Weight: 0.029 pounds

Additional Weight per Inch: 0.00109 pounds

Mechanical Specifications

Cable Assembly

Weight

0.029 lbs [13.15 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax PE3C4838](#)



2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax

TECHNICAL DATA SHEET

PE3C4838

Cable

Cable Type	PE-P086HF
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Tape
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	FEP, Blue
Jacket Diameter	0.104 in [2.64 mm]

One Time Minimum Bend Radius

0.52 in [13.21 mm]

Connectors

Description	Connector 1	Connector 2
Type	2.92mm Male Threaded	Mini SMP Female Push-On
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification	50 μ in minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Passivated Stainless Steel	Beryllium Copper, Gold
Body Plating Specification	SAE-AMS-2700	
Coupling Nut Material and Plating	Passivated Stainless Steel	
Coupling Nut Plating Specification	SAE-AMS-2700	
Hex Size	5/16 inch	
Torque	8 in-lbs [0.9 Nm]	

Environmental Specifications

Temperature

Operating Range

-55 to +155 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax PE3C4838](#)



2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax

TECHNICAL DATA SHEET

PE3C4838

How to Order

Part Number Configuration:

PE3C4838- **xx****uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C4838-12 = 12 inches long cable
PE3C4838-100cm = 100 cm long cable

2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax PE3C4838](#)


URL: <https://www.pasternack.com/2.92mm-male-to-mini-smp-female-cable-using-pe-p086hf-pe3c4838-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C4838 CAD Drawing

2.92mm Male to Mini SMP Female Cable Using PE-P086HF Coax

ZONE	REV.	DESCRIPTION	INITIAL RELEASE	DATE	CHANGED BY	APPROVED BY
A				11/16/2023	BPUCHASKI	AGANWANI



NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION
2. 3.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE, WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE ARE EXPORT CONTROLLED AND EXPORT FROM THE UNITED STATES OF AMERICA IS SUBJECT TO U.S. LAW AND EXPORT ADMINISTRATION REGULATIONS.



Website: www.Pastermack.com
Phone: 1 866 727 8376 | 1 949 261 1920

2.92mm MALE TO MINI SMP FEMALE CABLE USING PE-
B086HF COAX

REV A

ITEM NO. **ASKI**

SIZE	CAGE CODE	DRAWN BY
W	53010	BRUCH

SI
NS ARE FOR REFERENCE ONLY
- TO CHANGE WITHOUT NOTICE.
- OWNED/NON-CRITICAL FEATURES
- VARY IN SIZE AND LOCATION

ALL DIMENSIONIC
AND SUBJECT
UN-DIMENSIONIC
MAY VA

PRODUCTION IN PARTIES, TECHNOLOGY REGULATIONS.

ELECTRONICS, INC. ANY REFERENCE TO THE PROHIBITION OF THESE COMMODITIES IS AN ERROR. THE EXPORT ADMINISTRATION REGULATIONS DO NOT PROHIBIT THE EXPORT OF THESE COMMODITIES.

OLE PROPERTY OF INFINITE
TE ELECTRONICS, INC. IS PR
ES IN ACCORDANCE WITH THE

D IN THIS DRAWING IS THE S
WITTEN PERMISSION OF INFINI
TED FROM THE UNITED STAT
S LAW PROHIBITED

THE INFORMATION CONTAINED
OR WHOLE WITHOUT THE WR
OR SOFTWARE WERE EXPOR
DIVERSIFICATION CONTRARY TO US