



Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4890-60

Configuration

- Connector 1: Slide-On BMA Plug Bulkhead
- Connector 2: TNC Male
- Cable Type: RG405

Features

- Max Frequency 6 GHz
- Good VSWR of 1.5:1
- Gold Plated BMA Contacts
- Low Engagement Force BMA interface
- In stock and ready to ship

Applications

- General Purpose
- Laboratory Use BMA Cable RF Backplanes
- Blind Mate BMA Test
- Rack and Panel
- Phased Array Interconnects
- High Speed Switching Networks

Description

Pasternack's BMA cable assemblies using RG405 Coax are part of our full line of RF components available for same-day shipping. These BMA cable assemblies are designed to connect BMA system components, BMA racks, or BMA backplanes, delivering signal frequencies as high as 22 GHz. Our family of BMA cables can also be used to connect switching networks or phase-matched antenna arrays where low loss BMA interconnects are desired. If none of our standard options fit your application, you can specify your own custom BMA cable assembly using Pasternack's online Cable Creator.

Our BMA cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide BMA cabling or blind mate rack connections, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.5:1	
Return Loss			15.56	dB

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax PE3C4890-60](#)



Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4890-60

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	6	GHz
Insertion Loss (Typ.)	0.7	0.95	1.3	1.85	3	dB

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Diameter	0.591 in [15.01 mm]

Cable

Cable Type	RG405
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Outer Conductor Material and Plating	Copper
Repeated Minimum Bend Radius	0.05 in [1.27 mm]

Connectors

Description	Connector 1	Connector 2
Type	BMA Plug Bulkhead	TNC Male
Impedance	50 Ohms	50 Ohms
Connection Method	Slide-On	
Contact Material and Plating	Bronze, Gold	Brass, Gold over Nickel
Contact Plating Specification	51.18 μ in. minimum	
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Tri-Metal	
Outer Conductor Plating Specification	78.74 μ in. minimum	
Body Material and Plating	Brass, Tri-Metal	Brass, Nickel
Body Plating Specification	78.74 μ in. minimum	
Coupling Nut Material and Plating		Brass, Nickel
Hex Size	8 mm	

Mechanical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax PE3C4890-60](#)



Slide-On BMA Plug Bulkhead to TNC Male Cable
60 Inch Length Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4890-60

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8$ ", whichever is greater.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax PE3C4890-60](#)




Slide-On BMA Plug Bulkhead to TNC Male Cable
60 Inch Length Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4890-60

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax PE3C4890-60](#)



Slide-On BMA Plug Bulkhead to TNC Male Cable
60 Inch Length Using RG405 Coax

RF Cable Assemblies Technical Data Sheet

PE3C4890-60

How to Order

Part Number Configuration:

PE3C4890

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C4890-12 = 12 inches long cable
PE3C4890-100cm = 100 cm long cable

Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax PE3C4890-60](https://www.pasternack.com/bma-plug-tnc-male-rg405u-cable-assembly-pe3c4890-60-p.aspx)

URL: <https://www.pasternack.com/bma-plug-tnc-male-rg405u-cable-assembly-pe3c4890-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C4890-60 CAD Drawing

Slide-On BMA Plug Bulkhead to TNC Male Cable 60 Inch Length Using RG405 Coax



STANDARD TOLERANCES	
.X	±0.2
.XX	±0.01
.XXX	±0.005

*STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES

<p>NOTES:</p> <ol style="list-style-type: none"> 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm]. 	<p>DWG TITLE</p> <p>PE3C4890</p>	<p>PASTERNAK THE ENGINEER'S RF SOURCE</p> <p>Pasternack Enterprises, Inc. P.O. Box 16759 Irvine CA 92623</p> <p>Phone: (949) 261-1920 Fax: (949) 261-7451 Website: www.pasternack.com E-Mail: sales@pasternack.com</p>
<p>CAD FILE</p> <p>12/19/17</p>	<p>SCALE</p> <p>N/A</p>	<p>CAGE CODE</p> <p>53919</p>
<p>SIZE A</p> <p>CN2245</p>		