



Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3C4912-24

Configuration

- Connector 1: Slide-On BMA Plug Bulkhead
- Connector 2: N Male
- Cable Type: PE-SR402FLJ

Features

- Max Frequency 11 GHz
- Shielding Effectivity > 100 dB
- 70% Phase Velocity
- FEP Jacket
- Good VSWR of 1.5:1
- Gold Plated BMA Contacts
- Low Engagement Force BMA interface
- In stock and ready to ship


Applications

- General Purpose
- Laboratory Use BMA Cable RF Backplanes
- Blind Mate BMA Test
- Rack and Panel
- Phased Array Interconnects
- High Speed Switching Networks

Description

Pasternack's BMA cable assemblies using PE-SR402FLJ Coax are part of our full line of RF components available for same-day shipping. These BMA cable assemblies are designed to connect BMA system components, BMA racks, or BMA back-planes, delivering signal frequencies as high as 22 GHz. Our family of BMA cables can also be used to connect switching networks or phase-matched antenna arrays where low loss BMA interconnects are desired. If none of our standard options fit your application, you can specify your own custom BMA cable assembly using Pasternack's online Cable Creator.

Our BMA cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide BMA cabling or blind mate rack connections, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax](#)
PE3C4912-24


 Slide-On BMA Plug Bulkhead to N Male Cable
 24 Inch Length Using PE-SR402FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3C4912-24

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		11	GHz
VSWR			1.5:1	
Return Loss			15.56	dB
Velocity of Propagation		70		%
RF Shielding	100			dB
Group Delay		1.43 [4.69]		ns/ft [ns/m]
Capacitance		29 [95.14]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2.5	5	11	GHz
Insertion Loss (Typ.)	0.36	0.44	0.56	0.76	1.08	dB

Mechanical Specifications
Cable Assembly

 Length*
 Diameter
 24 in [609.6 mm]
 0.79 in [20.07 mm]

Cable

 Cable Type
 PE-SR402FLJ
 Impedance
 50 Ohms
 Inner Conductor Type
 Solid
 Inner Conductor Material and Plating
 Copper Clad Steel, Silver
 Dielectric Type
 PTFE
 Number of Shields
 1
 Shield Layer 1
 Tinned Copper Braid
 Jacket Material
 FEP, Black
 Jacket Diameter
 0.161 in [4.09 mm]

 One Time Minimum Bend Radius
 Repeated Minimum Bend Radius

 0.315 in [8 mm]
 1.575 in [40.01 mm]

 Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax](#)
PE3C4912-24



Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3C4912-24

Connectors

Description	Connector 1	Connector 2
Type	BMA Plug Bulkhead	N Male
Impedance	50 Ohms	50 Ohms
Connection Method	Slide-On	
Contact Material and Plating	Bronze, Gold	Brass, Gold over Nickel
Contact Plating Specification	51.18 μ in. minimum	
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Tri-Metal	
Outer Conductor Plating Specification	78.74 μ in. minimum	
Body Material and Plating	Brass, Tri-Metal	Brass, Nickel
Body Plating Specification	78.74 μ in. minimum	
Coupling Nut Material and Plating		Brass, Nickel
Hex Size	8 mm	

Mechanical Specification Notes:

*All cable assemblies have a length tolerance of 1.5% or $\pm 3/8$ ", whichever is greater.

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax](#)
PE3C4912-24




Slide-On BMA Plug Bulkhead to N Male Cable
24 Inch Length Using PE-SR402FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3C4912-24

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax](#)
PE3C4912-24



Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax

RF Cable Assemblies Technical Data Sheet

PE3C4912-24

How to Order

Part Number Configuration:

PE3C4912

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C4912-12 = 12 inches long cable
PE3C4912-100cm = 100 cm long cable

Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax PE3C4912-24](#)

URL: <https://www.pasternack.com/bma-plug-n-male-pe-sr402flj-cable-assembly-pe3c4912-24-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C4912-24 CAD Drawing

Slide-On BMA Plug Bulkhead to N Male Cable 24 Inch Length Using PE-SR402FLJ Coax



STANDARD TOLERANCES		
X	± 0.2	
.XX	± 0.01	
.XXX	± 0.005	

*STANDARD TOLERANCES APPLY
ONLY TO DIMENSIONS IN INCHES

PE PASTERNACK®
THE ENGINEER'S RESOURCE

Pasternack Enterprises, Inc.
P.O. Box 16759 | Irvine | CA | 92623

Phone: (949) 261-1920 | Fax: (949) 261-7451
Website: www.pasternack.com | E-Mail: sales@pasternack.com

NOTES:
1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL.
2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME.
3. DIMENSIONS ARE IN INCHES [mm].

DWG TITLE
PE3C4912

CAGE CODE 53919 CAD FILE 1/22/17 SCALE N/A SIZE A

CN2245