



## RF Cable Assemblies Technical Data Sheet

PE3C5836

OUTER SHIFLD

DIELECTRIC

SOLID CENTER CONDUCTOR

## Configuration

• Connector 1: 4.3-10 Female • Connector 2: 7/16 DIN Male Cable Type: SPP-250-LLPL

### **Features**

- Max Frequency 5.8 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- 100% Tested with PIM Test Results Marked on Cable
- UL910 Plenum Rated Cable
- · Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)

## **Applications**

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- Plenum Installations
- PIM Testing



SPP-250-LLPL

Ø 280

[7.11]

JACKET

#### Description

Pasternack's PE3C5836 4.3-10 female to 7/16 DIN male cable using SPP-250-LLPL coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack 4.3-10 to 7/16 DIN cable assembly has a female to male gender configuration with 50 ohm corrugated SPP-250-LLPL coax. The PE3C5836 4.3-10 female to 7/16 DIN male cable assembly operates to 5.8 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 4.3-10 Female to 7/16 DIN Male Low PIM Cable Using SPP-250-LLPL Coax, LF Solder PE3C5836

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 Phone: (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451





## RF Cable Assemblies Technical Data Sheet

PE3C5836

#### **Electrical Specifications**

Minimum	Typical	Maximum	Units
DC		5.8	GHz
	7,550	1.4:1	
	76		%
100			dB
		-160	dBc
	27 [88.58]		pF/ft [pF/m]
	0.067 [0.22]		uH/ft [uH/m]
	3 [9.84]		Ω/1000ft [Ω/Km]
	DC	76 100 27 [88.58] 0.067 [0.22]	DC 5.8 1.4:1 76 100 -160 27 [88.58] 0.067 [0.22]

## Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.45	0.7	1	2.5	5.8	GHz
Insertion Loss (Max.)	0.038	0.048	0.057	0.094	0.148	dB/ft
	0.12	0.16	0.19	0.31	0.49	dB/m

**Electrical Specification Notes:** 

Insertion loss does not include the loss of the connectors. Insertion loss is estimated as 0.04\*SQRT(FGHz) dB per connector.

### **Mechanical Specifications**

### **Cable Assembly**

#### Cable

Cable Type SPP-250-LLPL Impedance 50 Ohms Inner Conductor Type Solid Inner Conductor Material and Plating Copper **PTFE** Dielectric Type Number of Shields Outer Conductor Material and Plating Copper Jacket Material FEP, Blue Jacket Diameter 0.28 in [7.11 mm] One Time Minimum Bend Radius 1.25 in [31.75 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 4.3-10 Female to 7/16 DIN Male Low PIM Cable Using SPP-250-LLPL Coax , LF Solder PE3C5836

0.8 lbs-ft [1.08 N-m]

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

**Bending Moment** 

Sales@Pasternack.com • Techsupport@Pasternack.com





## **RF Cable Assemblies Technical Data Sheet**

PE3C5836

#### Connectors

Description	Connector 1	Connector 2	
Туре	4.3-10 Female	7/16 DIN Male	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Phosphor Bronze, Silver	Brass, Silver	
Dielectric Type	PTFE	PTFE	
Outer Conductor Material and Plating	Phosphor Bronze, Tri-Metal		
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal	
Coupling Nut Material and Plating		Brass, Tri-Metal	

Mechanical Specification Notes:

#### **Environmental Specifications**

**Temperature** 

Operating Range

-55 to +165 deg C

Compliance Certifications (see product page for current document)

#### **Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 4.3-10 Female to 7/16 DIN Male Low PIM Cable Using SPP-250-LLPL Coax , LF Solder PE3C5836

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

<sup>\*</sup>All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.





## **RF Cable Assemblies Technical Data Sheet**

PE3C5836



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 4.3-10 Female to 7/16 DIN Male Low PIM Cable Using SPP-250-LLPL Coax , LF Solder PE3C5836

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451






## **RF Cable Assemblies Technical Data Sheet**

PE3C5836

#### **How to Order**



Example: PE3C5836-12 = 12 inches long cable PE3C5836-100cm = 100 cm long cable

Plenum 4.3-10 Female to 7/16 DIN Male Low PIM Cable Using SPP-250-LLPL Coax , LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 4.3-10 Female to 7/16 DIN Male Low PIM Cable Using SPP-250-LLPL Coax , LF Solder PE3C5836

URL: https://www.pasternack.com/4.3-10-female-7-16-din-male-spp250llpl-cable-assembly-pe3c5836-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE3C5836 CAD Drawing
Plenum 4.3-10 Female to 7/16 DIN Male Low PIM Cable Using SPP-250-LLPL Coax, LF Solder

