



RF Cable Assemblies Technical Data Sheet

PE3C5891-48

Configuration

Connector 1: 7/16 DIN MaleConnector 2: SMA Male Right Angle


• Cable Type: SPP-250-LLPL

Features

- Max Frequency 5.8 GHz
- Low PIM: -155 dBc Max
- Shielding Effectivity > 100 dB
- 76% Phase Velocity
- FEP Jacket
- 100% Tested with PIM Test Results Marked on Cable
- UL910 Plenum Rated Cable
- Lightweight and Extremely Flexible
- Low Loss with Excellent VSWR
- IP67 (when mated)

Applications


- General Purpose
- Laboratory Use
- Low PIM Applications
- Plenum Installations
- Multi-Carrier Communication Systems
- PIM Testing



Description

Pasternack's PE3C5891-48 7/16 DIN male to SMA male right angle 48 inch cable using SPP-250-LLPL coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack 7/16 DIN to SMA cable assembly has a male to male gender configuration with 50 ohm corrugated SPP-250-LLPL coax. The PE3C5891-48 7/16 DIN male to SMA male cable assembly operates to 5.8 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -155 dBc. The right angle SMA interface on the SPP-250-LLPL cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 7/16 DIN Male to SMA Male Right Angle Low PIM Cable 48 Inch Length Using SPP-250-LLPL Coax, LF Solder PE3C5891-48

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3C5891-48

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------------|---------|--------------|---------|-----------------|
| Frequency Range | DC | | 5.8 | GHz |
| VSWR | | 7,550 | 1.4:1 | |
| Velocity of Propagation | | 76 | | % |
| RF Shielding | 100 | | | dB |
| Passive Intermodulation | | | -155 | dBc |
| Capacitance | | 27 [88.58] | | pF/ft [pF/m] |
| Inductance | | 0.067 [0.22] | | uH/ft [uH/m] |
| DC Resistance Inner Conductor | | 3 [9.84] | | Ω/1000ft [Ω/Km] |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency | 0.45 | 0.7 | 1 | 2.5 | 5.8 | GHz |
| Insertion Loss (Max.) | 0.21 | 0.26 | 0.31 | 0.51 | 0.79 | dB |

Electrical Specification Notes:

The insertion loss data above is based on the performance specifications of the coax cable used in this assembly. The insertion loss includes an estimated insertion loss of 0.04*SQRT(FGHz) dB maximum per connector.

Mechanical Specifications

Cable Assembly

Length* 48 in [121.92 cm]

Cable

Cable Type SPP-250-LLPL 50 Ohms Impedance Inner Conductor Type Solid Inner Conductor Material and Plating Copper **PTFE** Dielectric Type Number of Shields Outer Conductor Material and Plating Copper Jacket Material FEP, Blue Jacket Diameter 0.28 in [7.11 mm] One Time Minimum Bend Radius 1.25 in [31.75 mm] Bending Moment 0.8 lbs-ft [1.08 N-m]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 7/16 DIN Male to SMA Male Right Angle Low PIM Cable 48 Inch Length Using SPP-250-LLPL Coax , LF Solder PE3C5891-48

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3C5891-48

Connectors

| Connector 1 | Connector 2 | |
|------------------|---|--|
| 7/16 DIN Male | SMA Male Right Angle | |
| 50 Ohms | 50 Ohms | |
| Brass, Silver | Brass, Gold | |
| PTFE | PTFE | |
| Brass, Tri-Metal | Brass, Tri-Metal | |
| Brass, Tri-Metal | Brass, Tri-Metal | |
| | 7/16 DIN Male 50 Ohms Brass, Silver PTFE Brass, Tri-Metal | |

Mechanical Specification Notes:

Environmental Specifications

Temperature

Operating Range

-55 to +165 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 7/16 DIN Male to SMA Male Right Angle Low PIM Cable 48 Inch Length Using SPP-250-LLPL Coax , LF Solder PE3C5891-48

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

^{*}All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.





RF Cable Assemblies Technical Data Sheet

PE3C5891-48



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 7/16 DIN Male to SMA Male Right Angle Low PIM Cable 48 Inch Length Using SPP-250-LLPL Coax , LF Solder PE3C5891-48

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com






RF Cable Assemblies Technical Data Sheet

PE3C5891-48

How to Order



Example: PE3C5891-12 = 12 inches long cable PE3C5891-100cm = 100 cm long cable

Plenum 7/16 DIN Male to SMA Male Right Angle Low PIM Cable 48 Inch Length Using SPP-250-LLPL Coax, LF Solder from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: Plenum 7/16 DIN Male to SMA Male Right Angle Low PIM Cable 48 Inch Length Using SPP-250-LLPL Coax, LF Solder PE3C5891-48

URL: https://www.pasternack.com/7-16-din-male-sma-male-spp250llpl-cable-assembly-pe3c5891-48-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE3C5891-48 CAD Drawing
Plenum 7/16 DIN Male to SMA Male Right Angle Low PIM Cable 48 Inch Length Using SPP-250-LLPL Coax, LF Solder

