

2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax



RF Cable Assemblies Technical Data Sheet

PE3C6142

Configuration

- Connector 1: 2.4mm Male
- Connector 2: Mini SMP Female
- Cable Type: PE-P086HF

Features

- Max Frequency 40 GHz
- 70% Phase Velocity
- Double Shielded
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C6142 2.4mm male to Mini SMP female cable using PE-P086HF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 2.4mm to Mini SMP cable assembly has a male to female gender configuration with 50 ohm flexible PE-P086HF coax. The PE3C6142 2.4mm male to Mini SMP female cable assembly operates to 40 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax PE3C6142](#)

2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax



RF Cable Assemblies Technical Data Sheet

PE3C6142

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		40	GHz
VSWR			1.4:1	
Velocity of Propagation		70		%
Capacitance		29.4 [96.46]		pF/ft [pF/m]

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	2.5	5	10	20	40	GHz
Insertion Loss (Typ.)	0.31	0.46	0.68	1	1.55	dB/ft
	1.02	1.51	2.23	3.28	5.09	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.024 lbs [10.89 g]

Cable

Cable Type PE-P086HF
 Impedance 50 Ohms
 Inner Conductor Type Solid
 Inner Conductor Material and Plating Copper, Silver
 Dielectric Type PTFE
 Number of Shields 2
 Shield Layer 1 Silver Plated Copper Tape
 Shield Layer 2 Silver Plated Copper Braid
 Jacket Material FEP, Blue
 Jacket Diameter 0.104 in [2.64 mm]

One Time Minimum Bend Radius 1.5 in [38.1 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax PE3C6142](#)

2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax


RF Cable Assemblies Technical Data Sheet
PE3C6142
Connectors

Description	Connector 1	Connector 2
Type	2.4mm Male	Mini SMP Female
Contact Material and Plating	Beryllium Copper, Gold over Nickel	
Contact Plating Specification	50 μ in minimum	
Dielectric Type	PEI	PTFE
Outer Conductor Material and Plating		Beryllium Copper, Gold
Body Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Body Plating Specification	50 μ in minimum	
Coupling Nut Material and Plating	Passivated Stainless Steel	
Seal Gasket Material	Silicone Rubber	

Environmental Specifications
Temperature

Operating Range

-55 to +150 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax PE3C6142](#)

2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax



RF Cable Assemblies Technical Data Sheet

PE3C6142

How to Order

Part Number Configuration:

PE3C6142

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C6142-12 = 12 inches long cable
PE3C6142-100cm = 100 cm long cable

2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax PE3C6142](#)


URL: <https://www.pasternack.com/2.4mm-male-to-mini-smp-female-cable-using-pe-p086hf-pe3c6142-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C6142 CAD Drawing

2.4mm Male to Mini SMP Female Cable Using PE-P086HF Coax

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
	A	INITIAL RELEASE	01/31/2023	SREITER	AGANWANI



NOTES:

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCH OR LESS,
ONE LABEL APPROX CENTERED. LONGER THAN 36 INCH,
TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR
CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- 2.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED.
THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE

UNLESS OTHERWISE SPECIFIED
LEADING DIMENSIONS ARE INCHES
DIMENSIONS IN [] ARE MILLIMETERS

INTERPRET ALL DIMENSIONS AND
TOLERANCES PER ASME Y14.5

www.kom.com
9261.1920

FEMALE CABLE USING PE-P086HF

SIZE	CAGE CODE	DRAWN BY	ITEM NO.	REV.
2.4mm MALE TO MINI SMP FEMALE CABLE USING PE-P086HF COAX				

101 T-DO-DO 6 5 1 2
EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.
ALL DIMENSIONS ARE FOR REFERENCE ONLY
AND SUBJECT TO CHANGE WITHOUT NOTICE.