

Waterproof IP68 4.3-10 Male (Plug) to SMA Male (Plug) Low Loss Cable 36 Inch Length Using LMR-240 Coax with Times Microwave Components

PE3C6912/WP-36




Configuration

- Connector 1: 4.3-10 Male
- Connector 2: SMA Male
- Cable Type: LMR-240
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- PE Jacket
- Silicone Connector Boot
- IP68 Rated



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C6912/WP-36 4.3-10 male to SMA male 36 inch cable using LMR-240 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack 4.3-10 to SMA cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240 coax. The PE3C6912/WP-36 4.3-10 male to SMA male cable assembly operates to 6 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		3.2 [10.5]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ohms/1000ft [Ohms/Km]
Dielectric Withstanding Voltage (DC)			1,500	Vdc

Waterproof IP68 4.3-10 Male (Plug) to SMA Male
(Plug) Low Loss Cable 36 Inch Length Using
LMR-240 Coax with Times Microwave Components



PE3C6912/WP-36

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			5,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000	MHz	
PE3C6912/WP	Custom Lengths Available	Insertion Loss (Typ.)	0.039	0.055	0.079	0.129	0.204	dB/ft	
			0.13	0.19	0.26	0.43	0.67	dB/m	
PE3C6912/WP-24	24 In	Insertion Loss (Typ.)	0.23	0.29	0.36	0.52	0.76	dB	0.688
PE3C6912/WP-36	36 In	Insertion Loss (Typ.)	0.27	0.34	0.44	0.65	0.96	dB	0.721
PE3C6912/WP-48	48 In	Insertion Loss (Typ.)	0.31	0.2	0.52	0.78	1.17	dB	0.754
PE3C6912/WP-60	60 In	Insertion Loss (Typ.)	0.35	0.45	0.6	0.91	1.37	dB	0.787

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB

Loss due to Connector 2: $0.1 * \sqrt{\text{SQRT}(\text{FGHz})}$ dB

Base Weight: 0.655 pounds

Additional Weight per Inch: 0.00275 pounds

Mechanical Specifications

Cable Assembly

Length	36 in [914.4 mm]
Width/Diameter	0.5 in [12.7 mm]
Weight	0.721 lbs [327.04 g]

Cable

Cable Type	LMR-240
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE
Jacket Diameter	0.24 in [6.1 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.25 lbs-ft [0.34 N-m]
Flat Plate Crush	20 lbs/in [0.36 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

Waterproof IP68 4.3-10 Male (Plug) to SMA Male
(Plug) Low Loss Cable 36 Inch Length Using
LMR-240 Coax with Times Microwave Components



PE3C6912/WP-36

Connectors

Description	Connector 1	Connector 2
Type	4.3-10 Male	SMA Male
Option		Weatherproof Boot
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Silver	Beryllium Copper, Gold
Contact Plating Specification	200 µin minimum	ASTM B488
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating		Passivated Stainless Steel, Gold
Body Material and Plating	Brass, Tri-Metal	Passivated Stainless Steel, Gold
Body Plating Specification	80 µin minimum	SAE-AMS-2700
Coupling Nut Material and Plating	Brass, Tri-Metal	Passivated Stainless Steel
Coupling Nut Plating Specification	80 µin minimum	SAE-AMS-2700
Boot Material	Silicone	Silicone

Environmental Specifications

Ingress Protection (IP) Rating IP68

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:
Values at 25°C, sea level.

Waterproof IP68 4.3-10 Male (Plug) to SMA Male (Plug) Low Loss Cable 36 Inch Length Using LMR-240 Coax with Times Microwave Components



PE3C6912/WP-36

Typical Performance Data

How to Order

Part Number Configuration:

PE3C6912/WP

- xx

uu

Unit of Measure:

cm = Centimeters

<blank> = Inches

Length

Base Number

Example: PE3C6912/WP-12 = 12 inches long cable
PE3C6912/WP-100cm = 100 cm long cable

Waterproof IP68 4.3-10 Male (Plug) to SMA Male (Plug) Low Loss Cable 36 Inch Length Using LMR-240 Coax with Times Microwave Components from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Waterproof IP68 4.3-10 Male \(Plug\) to SMA Male \(Plug\) Low Loss Cable 36 Inch Length Using LMR®-240 Coax with Times Microwave Components PE3C6912/WP-36](https://www.pasternack.com/waterproof-ip68-4.3-10-male-plug-to-sma-male-plug-low-loss-cable-36-inch-length-using-lmr-240-coax-with-times-microwave-components-pe3c6912/wp-36)

URL: <https://www.pasternack.com/waterproof-ip68-4.3-10-male-plug-to-sma-male-plug-low-loss-cable-36-inch-length-using-lmr-240-pe3c6912-wp-36-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C6912/WP-36 CAD Drawing

Waterproof IP68 4.3-10 Male (Plug) to SMA Male (Plug) Low Loss Cable 36 Inch Length Using LMR-240 Coax with Times Microwave Components

