



SMA Male Right Angle to Reverse Polarity TNC Male Right Angle Cable 36 Inch Length Using RG142 Coax

RF Cable Assemblies Technical Data Sheet


PE3C7914-36

**Configuration**

- Connector 1: SMA Male Right Angle
- Connector 2: TNC Male Reverse Polarity Right Angle
- Cable Type: RG142

**Features**

- 70% Phase Velocity
- Double Shielded
- FEP Jacket



**Applications**

- General Purpose
- Laboratory Use

**Description**

Pasternack's PE3C7914-36 SMA male right angle to reverse polarity TNC male right angle 36 inch cable using RG142 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to reverse polarity TNC cable assembly has a male to male gender configuration with 50 ohm flexible RG142 coax. The right angle SMA and right angle TNC interfaces on the RG142 cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

**Electrical Specifications**

| Description             | Minimum | Typical      | Maximum | Units        |
|-------------------------|---------|--------------|---------|--------------|
| VSWR                    |         |              | 1.4:1   |              |
| Velocity of Propagation |         | 70           |         | %            |
| Capacitance             |         | 29.4 [96.46] |         | pF/ft [pF/m] |
| Operating Voltage (AC)  |         |              | 1,900   | Vrms         |
| Operating Voltage (DC)  |         |              | 300     | Vdc          |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to Reverse Polarity TNC Male Right Angle Cable 36 Inch Length Using RG142 Coax PE3C7914-36](#)



SMA Male Right Angle to Reverse Polarity TNC Male  
Right Angle Cable 36 Inch Length Using RG142 Coax

RF Cable Assemblies Technical Data Sheet

PE3C7914-36

**Mechanical Specifications**

**Cable Assembly**

Length\* 36 in [914.4 mm]  
Diameter 0.59 in [14.99 mm]

**Cable**

Cable Type RG142  
Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper Clad Steel, Silver  
Dielectric Type PTFE  
Number of Shields 2  
Shield Layer 1 Silver Plated Copper Braid  
Shield Layer 2 Silver Plated Copper Braid  
Jacket Material FEP, Tan  
Jacket Diameter 0.195 in [4.95 mm]

Repeated Minimum Bend Radius 1 in [25.4 mm]

**Connectors**

| Description                        | Connector 1          | Connector 2                           |
|------------------------------------|----------------------|---------------------------------------|
| Type                               | SMA Male Right Angle | TNC Male Reverse Polarity Right Angle |
| Specification                      | MIL-STD-348A         | MIL-C-39012                           |
| Impedance                          | 50 Ohms              | 50 Ohms                               |
| Contact Material and Plating       | Brass, Gold          | Brass, Gold                           |
| Contact Plating Specification      | 50 µin minimum       | 3µ-5µ in. minimum                     |
| Dielectric Type                    | PTFE                 | Teflon                                |
| Body Material and Plating          | Brass, Nickel        | Brass, Nickel                         |
| Body Plating Specification         | 100 µin minimum      | 70µ in. minimum                       |
| Coupling Nut Material and Plating  | Brass, Nickel        | Brass, Nickel                         |
| Coupling Nut Plating Specification | 100 µin minimum      | 70µ in. minimum                       |
| Hex Size                           | 5/16 inch            |                                       |
| Torque                             | 3 in-lbs [0.34 Nm]   |                                       |

**Environmental Specifications**

**Temperature**

Operating Range -55 to +200 deg C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to Reverse Polarity TNC Male Right Angle Cable 36 Inch Length Using RG142 Coax PE3C7914-36](#)



## SMA Male Right Angle to Reverse Polarity TNC Male Right Angle Cable 36 Inch Length Using RG142 Coax

### RF Cable Assemblies Technical Data Sheet

PE3C7914-36

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

#### How to Order

Part Number Configuration:

**PE3C7914 - xx uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3C7914-12 = 12 inches long cable  
PE3C7914-100cm = 100 cm long cable

SMA Male Right Angle to Reverse Polarity TNC Male Right Angle Cable 36 Inch Length Using RG142 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to Reverse Polarity TNC Male Right Angle Cable 36 Inch Length Using RG142 Coax PE3C7914-36](#)

URL: <https://www.pasternack.com/sma-male-tnc-male-rg142bu-cable-assembly-pe3c7914-36-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3C7914-36 CAD Drawing

## SMA Male Right Angle to Reverse Polarity TNC Male Right Angle

### Cable 36 Inch Length Using RG142 Coax

| REVISIONS |                 |           |          |
|-----------|-----------------|-----------|----------|
| REV.      | DESCRIPTION     | DATE      | APPROVED |
| A         | INITIAL RELEASE | 4/14/2021 | S. ELLIS |



**UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [ ] ARE MILLIMETERS**

**TOLERANCES:**

|               |       |             |        |
|---------------|-------|-------------|--------|
| .X = ± .2     | [.08] | FRACTIONS   |        |
| .XX = ± .02   | [.51] |             | ± 1/32 |
| .XXX = ± .005 | [.13] | ANGLES ± 1° |        |

**CABLE LENGTH (L) TOLERANCES:**

|                      |        |                 |
|----------------------|--------|-----------------|
| L ≤ 12               | [305]  | = +1 [25] / -0  |
| 12 [305] < L ≤ 60    | [1524] | = +2 [51] / -0  |
| 60 [1524] < L ≤ 120  | [3048] | = +4 [102] / -0 |
| 120 [3048] < L ≤ 300 | [7620] | = +6 [152] / -0 |
| 300 [7620] < L ≤ ∞   |        | = +5% / L / -0  |

ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.

**Pasternack Enterprises, Inc.**  
 P. O. Box 16759, Irvine, CA 92623.  
 Phone: 1.949.261.1920 | 1.866.727.8376  
 Fax: 1.949.261.7451  
 Website: www.pasternack.com  
 E-mail: sales@pasternack.com

THIRD-ANGLE PROJECTION

THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNAK CORPORATION. ALL RIGHTS RESERVED.

SHEET 1 OF 1

SCALE N/A

|     |           |          |          |     |
|-----|-----------|----------|----------|-----|
| REV | CAGE CODE | DRAWN BY | ITEM NO. | REV |
| A   | 53919     | K.DANG   | PE3C7914 | A   |

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.