

2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax



RF Cable Assemblies Technical Data Sheet


PE3C8051

Configuration

- Connector 1: 2.2-5 Male
- Connector 2: 4.3-10 Male Right Angle
- Cable Type: 1/4" Superflexible

Features

- Max Frequency 6 GHz
- Low PIM: -160 dBc Max
- Shielding Effectivity > 120 dB
- 82% Phase Velocity
- PE Jacket
- Low PIM and Low Loss
- 100% Tested with PIM Test Results Marked on Cable



Applications

- General Purpose
- Laboratory Use
- Low PIM Applications
- Distributed Antenna Systems (DAS)
- PIM Testing

Description

Pasternack's PE3C8051 2.2-5 male to 4.3-10 male right angle cable using 1/4 inch superflexible coax is part of our full line of RF components available for same-day shipping. Pasternack's corrugated RF cable assemblies are ideal for applications where durability and high power are needed. This Pasternack 2.2-5 to 4.3-10 cable assembly has a male to male gender configuration with 50 ohm corrugated 1/4" superflexible coax. The PE3C8051 2.2-5 male to 4.3-10 male cable assembly operates to 6 GHz. Our low PIM design also offers excellent passive intermodulation performance with PIM levels better than -160 dBc. The right angle 4.3-10 interface on the 1/4" superflexible cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		82		%
RF Shielding	120			dB
Passive Intermodulation			-160	dBc

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax PE3C8051](#)



2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax

RF Cable Assemblies Technical Data Sheet

PE3C8051

Capacitance	24.4 [80.05]	pF/ft [pF/m]
Inductance	0.059 [0.19]	uH/ft [uH/m]
DC Resistance Inner Conductor	3.2 [10.5]	Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor	2.53 [8.3]	Ω/1000ft [Ω/Km]
Jacket Spark	2,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Typ.)	0.01	0.02	0.03	0.05	0.1	dB/ft
	0.03	0.07	0.1	0.16	0.33	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.25dB connector loss.

Mechanical Specifications

Cable Assembly

Cable

Cable Type	1/4" Superflexible
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	1
Shield Layer 1	Helically Corrugated Copper Tube
Jacket Material	PE, Black
Jacket Diameter	0.303 in [7.7 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Typical Flex Cycles	20
Tensile Strength	79 lbs [35.83 Kg]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax PE3C8051](#)

2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax



RF Cable Assemblies Technical Data Sheet

PE3C8051

Connectors

Description	Connector 1	Connector 2
Type	2.2-5 Male	4.3-10 Male Right Angle
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Silver	Brass, Silver
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax PE3C8051](#)

2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax



RF Cable Assemblies Technical Data Sheet

PE3C8051

How to Order

Part Number Configuration:

PE3C8051

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C8051-12 = 12 inches long cable
PE3C8051-100cm = 100 cm long cable

2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax PE3C8051](#)


URL: <https://www.pasternack.com/2.2-5-male-4.3-10-male-pe-1-4-sfhc-cable-assembly-pe3c8051-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C8051 CAD Drawing

2.2-5 Male to 4.3-10 Male Right Angle Low PIM Cable Using 1/4 inch Superflexible Coax

REVISIONS					
REV.	DESCRIPTION	DATE	APPROVED		
A	INITIAL RELEASE	10/03/2021	SELLIS		



NOTES

1. CABLES 84" AND UNDER HAVE 1 LABEL CENTERED, CABLES OVER 84" HAVE 2 LABELS, ONE AT EACH END 12.0" FROM THE END OF THE CONNECTOR.
2. 6" FROM CABLE END 1 PLACE FOR ALL LENGTHS OF CABLE.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS		THIRD-ANGLE PROJECTION
TOLERANCES:		THE INFORMATION AND DESIGN IN THIS DOCUMENT IS THE PROPERTY OF PASTERNACK CORPORATION ALL RIGHTS RESERVED.
X = ± 2 [5.08] FRACTIONS XX = $\pm .02$ [.51] $\pm 1/32$ XXX = $\pm .005$ [.13] ANGLES $\pm 1^\circ$		Pasternack Enterprises, Inc. P.O. Box 16759, Irvine, CA 92623. Phone: 1.949.261.9200 1.866.727.8376 Website: www.pasternack.com E-mail: sales@pasternack.com
CABLE LENGTH (L) TOLERANCES: L \leq 12 [305] = ± 1 [25] / -0 12 [305] < L \leq 60 [1524] = ± 2 [51] / -0 60 [1524] < L \leq 120 [3048] = ± 4 [102] / -0 120 [3048] < L \leq 300 [7620] = ± 6 [152] / -0 300 [7620] < L = $\pm 5\%$ L / -0		SHEET 1 OF 1 SCALE N/A ITEM NO. PE3C8051 DRAWN BY MVEERAPPAN CAGE CODE 53919 SIZE A REV A
ALL DIMENSIONS SHOWN ARE FOR REFERENCE ONLY.		