



50 Ohm SMA Male to 75 Ohm TNC Male Cable
Using 75 Ohm RG179 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C9006/HS

Configuration

- Connector 1: SMA Male
- Connector 2: TNC Male
- Cable Type: RG179

Features

- 70% Phase Velocity
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C9006/HS 50 ohm SMA male to 75 ohm TNC male cable using 75 ohm RG179 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to TNC cable assembly has a male to male gender configuration with 75 ohm flexible RG179 coax.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		70		%
Capacitance		19.4 [63.65]		pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Weight 0.077 lbs [34.93 g]

Cable

Cable Type RG179
Impedance 75 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper Clad Steel, Silver
Dielectric Type PTFE
Number of Shields 1
Shield Layer 1 Silver Plated Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [50 Ohm SMA Male to 75 Ohm TNC Male Cable Using 75 Ohm RG179 Coax with HeatShrink PE3C9006/HS](#)



50 Ohm SMA Male to 75 Ohm TNC Male Cable
Using 75 Ohm RG179 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C9006/HS

Jacket Material	FEP, Tan
Jacket Diameter	0.1 in [2.54 mm]
Repeated Minimum Bend Radius	0.4 in [10.16 mm]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	TNC Male
Specification	MIL-STD-348A	
Impedance	50 Ohms	75 Ohms
Contact Material and Plating	Brass, Gold	
Contact Plating Specification	30 µin minimum	
Dielectric Type	PTFE	
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	
Hex Size	5/16 inch	
Torque	3 in-lbs [0.34 Nm]	

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [50 Ohm SMA Male to 75 Ohm TNC Male Cable Using 75 Ohm RG179 Coax with HeatShrink PE3C9006/HS](#)



50 Ohm SMA Male to 75 Ohm TNC Male Cable Using 75 Ohm RG179 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C9006/HS

How to Order

Part Number Configuration:

PE3C9006/HS

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C9006/HS-12 = 12 inches long cable
PE3C9006/HS-100cm = 100 cm long cable

50 Ohm SMA Male to 75 Ohm TNC Male Cable Using 75 Ohm RG179 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [50 Ohm SMA Male to 75 Ohm TNC Male Cable Using 75 Ohm RG179 Coax with HeatShrink PE3C9006/HS](#)

URL: <https://www.pasternack.com/50-ohm-sma-male-to-75-ohm-tnc-male-cable-using-rg179-with-heatshrink-pe3c9006-hs-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C9006/HS CAD Drawing

50 Ohm SMA Male to 75 Ohm TNC Male Cable Using
75 Ohm RG179 Coax with HeatShrink

1 2 3 4 5 6

REVISION			
ZONE	REV.	DESCRIPTION	DATE
	A	INITIAL RELEASE	01/25/2023
			CHANGED BY
			BPUCHASKI
			APPROVED BY
			AGANWANI



NOTES:

- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY
- THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PE PASTERNAK an INFINITI [®] brand		Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5
DESCRIPTION		50 Ohm SMA Male to 75 Ohm TNC Male Cable Using 75 Ohm RG179 Coax with HeatShrink		SCALE NONE
SIZE		CAGE CODE		SHEET 1 OF 1
A		53919		
DRAWN BY		ITEM NO.		
BPUCHASKI		PE3C9006/HS		
REV		A		