



Reverse Polarity MCX Male to SMA Female Cable Using RG178 Coax

RF Cable Assemblies Technical Data Sheet

PE3C9322

Configuration

- Connector 1: MCX Male Reverse Polarity
- Connector 2: SMA Female
- Cable Type: RG178

Features

- 70% Phase Velocity
- FEP Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C9322 reverse polarity MCX male to SMA female cable using RG178 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity MCX to SMA cable assembly has a male to female gender configuration with 50 ohm flexible RG178 coax.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation	70			%
Capacitance	29.4 [96.46]			pF/ft [pF/m]

Mechanical Specifications

Cable Assembly

Cable

Cable Type	RG178
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PTFE
Number of Shields	1
Shield Layer 1	Silver Plated Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity MCX Male to SMA Female Cable Using RG178 Coax PE3C9322](#)



Reverse Polarity MCX Male to SMA Female Cable Using RG178 Coax

RF Cable Assemblies Technical Data Sheet

PE3C9322

Jacket Material	FEP, Tan
Jacket Diameter	0.072 in [1.83 mm]
Repeated Minimum Bend Radius	0.4 in [10.16 mm]

Connectors

Description	Connector 1	Connector 2
Type	MCX Male Reverse Polarity	SMA Female
Specification	MIL-C-39012	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Beryllium Copper, Gold over Nickel	Beryllium Copper, Gold
Contact Plating Specification	30 μ in minimum	MIL-G-45204
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold over Nickel	Brass, Nickel
Body Plating Specification	10 μ in minimum	QQ-N-290

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity MCX Male to SMA Female Cable Using RG178 Coax PE3C9322](#)




Reverse Polarity MCX Male to SMA Female Cable Using RG178 Coax

RF Cable Assemblies Technical Data Sheet

PE3C9322

How to Order

Part Number Configuration:



Example: PE3C9322-12 = 12 inches long cable
PE3C9322-100cm = 100 cm long cable

Reverse Polarity MCX Male to SMA Female Cable Using RG178 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity MCX Male to SMA Female Cable Using RG178 Coax PE3C9322](#)

URL: <https://www.pasternack.com/reverse-polarity-mcx-male-to-sma-female-cable-using-rg178-pe3c9322-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C9322 CAD Drawing

Reverse Polarity MCX Male to SMA Female Cable Using RG178 Coax

