

BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet


PE3C9573/HS

Configuration

- Connector 1: BNC Female
- Connector 2: SHV Plug
- Cable Type: RG58

Features

- Max Frequency 300 MHz
- 65.9% Phase Velocity
- PVC (NC) Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C9573/HS BNC female to SHV plug cable using RG58 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack BNC to SHV cable assembly has a female to plug gender configuration with 50 ohm flexible RG58 coax. The PE3C9573/HS BNC female to SHV plug cable assembly operates to 300 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink PE3C9573/HS](#)

BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C9573/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		300	MHz
VSWR			1.4:1	
Velocity of Propagation		65.9		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			500	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	50	100	250	500	1,000	MHz
Insertion Loss (Max.)	1.029555 3.38	1.048999 3.44	1.074165 3.52	1.116108 3.66	1.199993 3.94	dB/ft dB/m
VSWR (Max.)	1.4:1	1.4:1	1.4:1	1.4:1	1.4:1	
Return Loss (Max.)	15.56	15.563	15.563	15.563	15.563	dB

Mechanical Specifications

Cable Assembly

Weight 0.089 lbs [40.37 g]

Cable

Cable Type RG58
Impedance 50 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper, Tin
Dielectric Type PE
Number of Shields 1
Shield Layer 1 Tinned Copper Braid
Jacket Material PVC (NC), Black
Jacket Diameter 0.195 in [4.95 mm]

One Time Minimum Bend Radius 0.98 in [24.89 mm]
Repeated Minimum Bend Radius 1.96 in [49.78 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink PE3C9573/HS](#)

BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C9573/HS

Connectors

Description	Connector 1	Connector 2
Type	BNC Female	SHV Plug
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	100 μ in minimum
Coupling Nut Material and Plating		Brass, Nickel
Coupling Nut Plating Specification		100 μ in minimum

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink PE3C9573/HS](#)

BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink

RF Cable Assemblies Technical Data Sheet

PE3C9573/HS

How to Order

Part Number Configuration:

PE3C9573/HS - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3C9573/HS-12 = 12 inches long cable
PE3C9573/HS-100cm = 100 cm long cable

BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink PE3C9573/HS](#)

URL: <https://www.pasternack.com/bnc-female-to-shv-plug-cable-using-rg58-with-heatshrink-pe3c9573-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3C9573/HS CAD Drawing
BNC Female to SHV Plug Cable Using RG58 Coax with HeatShrink

