

## Mini SMP Male to Mini SMP Female VITA 67 Cable Using PE-P086HF Coax with HeatShrink



### PE3C9754

#### Configuration

- Connector 1: Mini SMP Male
- Connector 2: Mini SMP Female
- Coax Cable Group: 2
- Coax Flex Type: Flexible

#### Features

- Max Frequency 26.5 GHz
- Shielding Effectivity > 110 dB
- 70% Phase Velocity
- Standard MIL-STD-348 SMPM interface
- Push-on/snap-on mating style for quick installation
- Mini SMP (SMPM) Female compatible with VITA 67 PE45531/PE45532/PE45537 (4-port) and PE45533/PE45534/PE45538 (8-port) blocks
- Mini SMP Male compatible with VITA 67 PE45531/PE45532/PE45537 (4-port) and PE45533/PE45534/PE45538 (8-port) blocks

#### Applications

- General Purpose
- Laboratory Use
- Scientific research
- High-reliability, high-density for aerospace & defense application
- Ground base station & communication systems, avionics, radar systems

#### Description

Pasternack's PE3C9754 Mini SMP male to Mini SMP female cable using PE-P086HF coax is part of our full line of RF components available for same-day shipping. Pasternack's VITA 67 assemblies are high-density, high-performance RF cable assemblies that fit into VITA 67 blocks and attach to the PCB board which makes it ideal for applications where tight bends and flexure is required. This Pasternack Mini SMP to Mini SMP cable assembly has a male to female gender configuration with 50 ohm flexible coax. The PE3C9754 Mini SMP male to Mini SMP female cable assembly operates to 26.5 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		26.5	GHz
VSWR			1.15:1	
Velocity of Propagation		70		%
RF Shielding	110			dB

## Mini SMP Male to Mini SMP Female VITA 67 Cable Using PE-P086HF Coax with HeatShrink



### PE3C9754

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Capacitance		29.4 [96.46]		pF/ft [pF/m]

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	2	4.5	9	18	GHz
Insertion Loss (Typ.)	0.211	0.305	0.472	0.695	1.046	dB/ft
	0.69	1	1.55	2.28	3.43	dB/m

Electrical Specification Notes:  
Values at 25°C, sea level.

#### Mechanical Specifications

##### Cable Assembly

Weight 0.22 lbs [99.79 g]

##### Cable

Impedance 50 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper Clad Steel, Silver  
Dielectric Type PTFE  
Shield Layer 1 Silver Plated Copper Tape

#### Connectors

Description	Connector 1	Connector 2
Type	Mini SMP Male	Mini SMP Female
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Contact Plating Specification	ASTM B488	MIL-G-45204
Body Material and Plating	Beryllium Copper, Gold	Beryllium Copper, Gold
Body Plating Specification	ASTM B488	MIL-G-45204

#### Environmental Specifications

##### Compliance Certifications

(see product page for current document)

##### Plotted and Other Data

Notes:

Values at 25°C, sea level.

## Mini SMP Male to Mini SMP Female VITA 67 Cable Using PE-P086HF Coax with HeatShrink




### PE3C9754

#### Typical Performance Data

#### How to Order

Part Number Configuration:



Example: PE3C9754-12 = 12 inches long cable  
PE3C9754-100cm = 100 cm long cable

Mini SMP Male to Mini SMP Female VITA 67 Cable Using PE-P086HF Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Mini SMP Male to Mini SMP Female VITA 67 Cable Using PE-P086HF Coax with HeatShrink PE3C9754](#)

URL: <https://www.pasternack.com/mini-smp-male-to-mini-smp-female-vita-67-cable-using-pe-p086hf-with-heatshrink-pe3c9754-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3C9754 CAD Drawing

Mini SMP Male to Mini SMP Female VITA 67 Cable Using PE-P086HF Coax with HeatShrink

