

20KV Female Bulkhead to C Male Cable Using RG213HV Coax



PE3C9794

Configuration

- Connector 1: 20KV Female Bulkhead
- Connector 2: C Male
- Cable Type: RG213HV

Features

- 69% Phase Velocity
- Polyurethane Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3C9794 20KV female bulkhead to type C male cable is part of our full line of RF components available for same-day shipping. This Pasternack 20KV to type C cable assembly has a female to male gender configuration with 50 ohm RG213HV coax. Our RF cable assembly with 20KV bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. Our 20kV high voltage RF cable assemblies are designed to handle higher voltages and minimize the risk of electric shock. Both the connectors used in this cable assemblies have recessed contact design to withstand unmated higher voltage. These cable assemblies are commonly used in applications where high voltage transmission and RF signal integrity are critical. These cable assemblies are constructed with high-quality insulation materials capable of withstanding higher voltages, ensuring safety and preventing electrical breakdown. Our cable assemblies are built with durable and flexible materials to withstand harsh environmental conditions and repetitive movements, ensuring reliable performance over extended periods.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------------------|---------|---------|---------|-------|
| Velocity of Propagation | | 69 | | % |

Electrical Specification Notes:
Values at 25°C, sea level.

Mechanical Specifications

Cable Assembly

| | |
|----------------|--------------------|
| Width/Diameter | 0.5 in [12.7 mm] |
| Weight | 0.028 lbs [12.7 g] |

Cable

| | |
|--------------------------------------|--------------|
| Cable Type | RG213HV |
| Impedance | 50 Ohms |
| Inner Conductor Material and Plating | Copper, Bare |

20KV Female Bulkhead to C Male Cable Using RG213HV Coax



PE3C9794

| | |
|------------------------------|---------------------|
| Dielectric Type | PE |
| Number of Shields | 1 |
| Jacket Material | Polyurethane |
| Jacket Diameter | 0.394 in [10.01 mm] |
| Repeated Minimum Bend Radius | 1.969 in [50.01 mm] |

Connectors

| Description | Connector 1 | Connector 2 |
|------------------------------------|----------------------------------|---------------|
| Type | 20KV Female Bulkhead | C Male |
| Specification | MIL-STD-202 | MIL-STD-348 |
| Impedance | 50 Ohms | 50 Ohms |
| Configuration | Straight | Straight |
| Contact Material and Plating | Beryllium Copper, Gold/Tri-Metal | Silver |
| Contact Plating Specification | | QQ-S-365 |
| Dielectric Type | PE (HD) | PTFE |
| Body Material and Plating | Brass, Nickel Over Copper | Brass, Nickel |
| Body Plating Specification | | QQ-N-290 |
| Coupling Nut Material and Plating | Brass, Nickel Over Copper | Brass, Nickel |
| Coupling Nut Plating Specification | | QQ-N-290 |

Environmental Specifications

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Values at 25°C, sea level.

20KV Female Bulkhead to C Male Cable Using RG213HV Coax




PE3C9794

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3C9794-12 = 12 inches long cable
PE3C9794-100cm = 100 cm long cable

20KV Female Bulkhead to C Male Cable Using RG213HV Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [20KV Female Bulkhead to C Male Cable Using RG213HV Coax PE3C9794](#)

URL: <https://www.pasternack.com/20kv-female-bulkhead-to-c-male-cable-using-rg213hv-pe3c9794-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3C9794 CAD Drawing

20KV Female Bulkhead to C Male Cable Using RG213HV Coax



| SIZE | CAGE CODE | DRAWN BY | ITEM NO. | REV |
|------|-----------|----------|----------|-----|
| A | 53919 | LNAGARAJ | PE3C9794 | B |