



## 78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Cable

### RF Cable Assemblies Technical Data Sheet

**PE3CA2219**

#### Configuration

- Connector 1: TRB Plug
- Connector 2: Blunt Cut Genderless
- Cable Type: 30-02001
- Coax Flex Type: Flexible

#### • Features

- Max Frequency 400 MHz
- PVC Jacket
- MIL-STD-1553
- -20°C to +75°C
- 78 ohms

#### Applications

- General Purpose
- Laboratory Use
- MIL-STD-1553
- Data

#### Description

Pasternack's PE3CA2219 78 ohm TRB plug to Blunt cut genderless cable using 78 ohm PE-30-02001 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to Blunt Cut cable assembly has a plug to genderless gender configuration with 78 ohm flexible 30-02001 twinax. The PE3CA2219 TRB plug to Blunt cut genderless cable assembly operates to 400 MHz. The PE3CA2219 cable assembly consists of a 3-slot solder/clamp TRB plug to Blunt Cut on PE-30-02001, that is a standard lab-rated PVC cable for MIL-STD-1553 applications. It features a larger diameter cable (0.242" O.D.)

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

| Description            | Minimum | Typical      | Maximum | Units        |
|------------------------|---------|--------------|---------|--------------|
| Frequency Range        | DC      |              | 400     | MHz          |
| Capacitance            |         | 19.7 [64.63] |         | pF/ft [pF/m] |
| Operating Voltage (AC) |         |              | 1,000   | Vrms         |

#### Specifications by Frequency

| Description | F1 | F2 | F3  | F4  | F5  | Units |
|-------------|----|----|-----|-----|-----|-------|
| Frequency   | 10 | 50 | 100 | 200 | 400 | MHz   |

#### Electrical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Twinax \(242 O.D.\) Cable PE3CA2219](#)



78 Ohm 3-Slot TRB Solder/Clamp Plug with  
Blunt Cut for PE-30-02001 Cable

**RF Cable Assemblies Technical Data Sheet**

**PE3CA2219**

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

**Mechanical Specifications**

**Cable Assembly**

Weight 0.1928 lbs [87.45 g]

**Cable**

Cable Type 30-02001  
Impedance 78 Ohms  
Inner Conductor Type Stranded  
Inner Conductor Material and Plating Copper, Silver  
Dielectric Type PE  
Shield Layer 1 Silver Plated Copper  
Jacket Material PVC, Blue

One Time Minimum Bend Radius 2.42 in [61.47 mm]

**Connectors**

| Description                           | Connector 1                  | Connector 2          |
|---------------------------------------|------------------------------|----------------------|
| Type                                  | TRB Plug                     | Blunt Cut Genderless |
| Impedance                             | 78 Ohms                      |                      |
| Contact Material and Plating          | Bronze, Gold 30 micro inches |                      |
| Contact Plating Specification         | ASTM-B-488                   |                      |
| Dielectric Type                       | Teflon                       |                      |
| Outer Conductor Material and Plating  | Phosphor Bronze, Gold        |                      |
| Outer Conductor Plating Specification | 30 micro inches              |                      |
| Body Material and Plating             | Brass, Nickel                |                      |
| Body Plating Specification            | ASTM-B-733                   |                      |

**Environmental Specifications**

**Temperature**

Operating Range -20 to +75 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Twinax \(242 O.D.\) Cable PE3CA2219](#)



## 78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Cable

### RF Cable Assemblies Technical Data Sheet

**PE3CA2219**

#### How to Order

Part Number Configuration:

**PE3CA2219**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3CA2219-12 = 12 inches long cable  
PE3CA2219-100cm = 100 cm long cable

78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Cable from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Twinax \(242 O.D.\) Cable PE3CA2219](#)

URL: <https://www.pasternack.com/trb-plug-to-blunt-cut-genderless-1553-cable-using-pe-30-02001-pe3ca2219-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

## 78 Ohm 3-Slot TRB Solder/Clamp Plug with Blunt Cut for PE-30-02001 Cable

| ZONE | REV | DESCRIPTION     | DATE       | CHANGED BY | APPROVED |
|------|-----|-----------------|------------|------------|----------|
|      | A   | INITIAL RELEASE | 04/28/2016 | DMAY       | EKIM     |



| ITEM NUMBER  | LENGTH |        |
|--------------|--------|--------|
|              | FEET   | METERS |
| PE3CA2219-12 | 1.0    | .31    |
| PE3CA2219-24 | 2.0    | .61    |
| PE3CA2219-36 | 3.0    | .92    |
| PE3CA2219-48 | 4.0    | 1.22   |
| PE3CA2219-60 | 5.0    | 1.52   |

NOTES:

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

|                                                                                                                                                                                                                             |  |                                                                                                                                                                         |  |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| UNLESS OTHERWISE SPECIFIED<br>LEADING DIMENSIONS ARE INCHES<br>DIMENSIONS IN [ ] ARE MILLIMETERS                                                                                                                            |  |   |  |
| TOLERANCES:                                                                                                                                                                                                                 |  | INTERPRET ALL DIMENSIONS AND<br>TOLERANCES PER ASME Y14.5                                                                                                               |  |
| .X = ±.2 [ .5 ] FRACTIONS<br>.XX = ±.02 [ .5 ] ± 1/32<br>.XXX = ±.005 [ .13 ] ANGLES ±°                                                                                                                                     |  | SCALE                                                                                                                                                                   |  |
| CABLE LENGTH TOLERANCES:                                                                                                                                                                                                    |  | NONE                                                                                                                                                                    |  |
| s12 [305] = +1 [25] / -0<br>s12 [305] ≤ 60 [1524] = +2 [51] / -0<br>>12 [305] ≤ 120 [3048] = +4 [102] / -0<br>>60 [1524] ≤ 120 [3048] = +4 [102] / -0<br>>120 [3048] ≤ 300 [7620] = +6 [152] / -0<br>>300 [7620] = +5% / -0 |  | SHEET<br>1 OF 1                                                                                                                                                         |  |
| ALL DIMENSIONS ARE FOR REFERENCE ONLY<br>AND SUBJECT TO CHANGE WITHOUT NOTICE.                                                                                                                                              |  | REV                                                                                                                                                                     |  |