

Fiber Optic Patch Cable, Dual SC UPC to ST UPC, MM OM1, 2.0mm Plenum, Orange-5M



PE3FCA145-5M

Features

- Multimode OM1 indoor fiber optic cable assembly
- Dual SC UPC to Dual ST UPC
- Indoor Plenum (OFNP) rated cable
- Suitable for wall, ceiling, conduits, and between buildings
- 2.0mm x 4.1mm duplex zip-cord
- Custom lengths available with the same fast delivery

Applications

- Telecom & Networking
- Data Centers
- Enterprise and Corporate Networks
- Broadcasting & Media Production
- Military & Defense
- Healthcare & Medical Imaging
- Transportation & Rail
- Oil & Gas

Description

The PE3FCA145-5M fiber optic patch cord from Pasternack is a robust and versatile fiber optic cable assembly designed for high-performance data transmission in various environments. Equipped with Dual SC UPC to Dual ST UPC connectors, this duplex OM1 Multimode fiber optic patch cable is optimized for indoor use, featuring a Plenum (OFNP) rated cable that ensures compliance with fire and safety standards. The 2.0mm x 4.1mm diameter construction, combined with its orange color, makes it easy to identify in complex setups, while its operating temperature range of 0°C to 60°C and storage temperature of -20°C to 60°C provides reliable performance across diverse conditions.

Pasternack's PE3FCA145-5M fiber optic jumper is ideal for applications where reliable, short-range data connectivity is critical. The multimode design of the OM1 fiber offers stable, high-speed transmission over short distances, making it suitable for Telecom & Networking, Data Centers, and Corporate Networks. With the flexibility of custom lengths, the Pasternack PE3FCA145-5M fiber optic assembly can be tailored to meet specific installation requirements, ensuring efficient network management in high-density setups without compromising on delivery time or quality.

Beyond networking, the Pasternack PE3FCA145-5M fiber patch cord supports an array of industry applications, from Broadcasting & Media Production and Military & Defense to Healthcare & Medical Imaging. This fiber assembly offers a reliable and durable solution for any setting requiring high-quality data transmission in a controlled, indoor environment. For further information on similar fiber optic products, our expert technical support and trained sales team can get you the ideal fiber optic duplex cable assembly as per your requirements.

Configuration

Function	Patch
Cable Type	Duplex Multimode
Mode	Multimode
Mode Class	OM1
Fiber Diameter	62.5/125 um
Connection 1 Type	SC
Connection 1 Polish	UPC
Connection 2 Type	ST
Connection 2 Polish	UPC
Cable Color	Orange

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Return Loss	30			dB

Fiber Optic Patch Cable, Dual SC UPC to ST UPC, MM OM1, 2.0mm Plenum, Orange-5M



PE3FCA145-5M

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Insertion Loss			0.3	dB

Mechanical Specifications

Cable Assembly

Length	5 m [196.85 in]
Width/Diameter	2 mm
Weight	24.04 g [0.053 lbs]

Cable

Cable Type	Patch
Static Bend Radius	20 mm
Dynamic Bend Radius	40 mm
Max Crush Resistance, Short Term (N/100mm)	300
Max Crush Resistance, Long Term (N/100mm)	100

Connectors

Description	Connector 1	Connector 2
Type	SC	ST
Connector Polish	UPC	UPC

Environmental Specifications

Operating Range Temperature	0 to +60 deg C
Storage Range Temperature	-20 to +60 deg C
Ingress Protection (IP) Rating	Non-Rated

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Fiber Optic Patch Cable, Dual SC UPC to ST UPC, MM OM1, 2.0mm Plenum, Orange-5M




PE3FCA145-5M

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3FCA145-12 = 12 inches long cable
PE3FCA145-100cm = 100 cm long cable

Fiber Optic Patch Cable, Dual SC UPC to ST UPC, MM OM1, 2.0mm Plenum, Orange-5M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fiber Optic Patch Cable, Dual SC UPC to ST UPC, MM OM1, 2.0mm Plenum, Orange-5M PE3FCA145-5M](#)

URL: <https://www.pasternack.com/sc-st-multimode-fiber-optic-cable-assembly-pe3fca145-5m-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA145-5M CAD Drawing

Fiber Optic Patch Cable, Dual SC UPC to ST UPC, MM OM1, 2.0mm Plenum, Orange-5M



NOTES:
 1. SC
 2. AL
 3. CA
 4. CA
 5. CA
 DE

CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND
DESCRIPTION

DUS

ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN)

CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED INSTALLED (NOT SHOWN).

CABLE ASSEMBLY SHALL BE TESTED FOR CONTI

CABLE ASSEMBLY LENGTH DETERMINED BY ITEM

DESCRIPTION

卷之三

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS INC. ANY REPRODUCTION IN PART OR WHOLE, OR THE TRANSFER OF THIS DRAWING TO OTHERS, IS PROHIBITED UNLESS AUTHORIZED IN WRITING BY INFINITE ELECTRONICS INC. NO SOFTWARE, WHETHER EXPORTED FROM THE UNITED STATES OR OTHERWISE, IS ACCORDING TO DIVISION CONTRACT TO US LAW PROHIBITED.

THE INFORMATION
OR WHOLE WIT
OR SOFTWARE
DIVERSION COM
E 06 Bay D4 A4 70