


## 4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm LSZH, 2.0mm breakout, Aqua-25M



### PE3FCA207-25M

#### Features

- 4X LC UPC to 4X ST UPC
- Indoor multimode OM4
- Low Smoke Zero Halogen (LSZH) rated cable
- 4.5mm with tight-buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for confined installations where flame resistance is required

#### Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

#### Description

High-performance fiber optic cable assemblies, including the PE3FCA207-25M from Pasternack, are designed for modern, high-speed network infrastructures and part of a large selection of same day ship cable assemblies. Whether deploying fiber optic distribution assemblies for enterprise networks, fiber optic breakout assemblies for seamless interconnectivity, or fiber optic patch cord assemblies for structured cabling, our solutions ensure durability and precision. Built for data centers, telecommunications, and industrial applications, our fiber optic distribution breakout assemblies deliver superior performance, ensuring optimal signal integrity and minimal loss.

For longer transmission distances and higher bandwidth, the Pasternack PE3FCA207-25M indoor OM4 fiber optic breakout assembly supports 10Gb Ethernet up to 550 meters and 40G/100G Ethernet up to 150 meters. Built with a tight-buffered aramid yarn strength member, this 4-fiber multimode assembly features LC UPC to ST UPC connectors, a 4.5mmmm overall cable diameter, and a 2.0mm breakout diameter, ensuring superior durability and performance. The aqua-colored Low Smoke Zero Halogen (LSZH) rated jacket is suitable for confined installations where flame resistance is required, making it a reliable choice for data centers, telecom networks, and high-performance computing environments.

With a bandwidth of 4700MHz·km, Pasternack's PE3FCA207-25M OM4 fiber optic cable delivers low attenuation and high-speed performance for mission-critical applications. Its 33.75mm (7.5D) minimum bend radius and -20°C to 70°C operating temperature provide the flexibility needed for indoor routing, structured cabling, and conduit installations. Designed for hyperscale data centers and telecom backbones, this fiber optic assembly ensures seamless network connectivity with minimal signal loss. For further information on similar products, our expert technical support and trained sales team can get you the ideal fiber optic multi-fiber cable assembly as per your requirements.

#### Configuration

|                     |                   |
|---------------------|-------------------|
| Function            | Breakout          |
| Cable Type          | 4-Fiber Multimode |
| Mode                | Multimode         |
| Mode Class          | OM4               |
| Fiber Diameter      | 50/125 um         |
| Connection 1 Type   | LC                |
| Connection 1 Polish | UPC               |
| Connection 2 Type   | ST                |
| Connection 2 Polish | UPC               |
| Cable Color         | Aqua Blue         |

#### Optical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------|---------|---------|---------|-------|
| Return Loss | 30      |         |         | dB    |

## 4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm LSZH, 2.0mm breakout, Aqua-25M



### PE3FCA207-25M

#### Optical Specifications

| Description    | Minimum | Typical | Maximum | Units |
|----------------|---------|---------|---------|-------|
| Insertion Loss |         |         | 0.3     | dB    |

#### Mechanical Specifications

##### Cable Assembly

|                |                      |
|----------------|----------------------|
| Length         | 25 m [984.25 in]     |
| Width/Diameter | 4.5 mm               |
| Weight         | 146.96 g [0.324 lbs] |

##### Cable

|                                            |          |
|--------------------------------------------|----------|
| Cable Type                                 | Breakout |
| Static Bend Radius                         | 34 mm    |
| Dynamic Bend Radius                        | 67 mm    |
| Max Crush Resistance, Short Term (N/100mm) | 1,000    |
| Max Crush Resistance, Long Term (N/100mm)  | 300      |

#### Connectors

| Description      | Connector 1 | Connector 2 |
|------------------|-------------|-------------|
| Type             | LC          | ST          |
| Connector Polish | UPC         | UPC         |

#### Environmental Specifications

|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -20 to +70 deg C |
| Storage Range Temperature      | -40 to +70 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution  
Cable, 4.5mm LSZH, 2.0mm breakout, Aqua-25M



**PE3FCA207-25M**

**Typical Performance Data**

**How to Order**

Part Number Configuration:

**PE3FCA207**

**- xx**

**uu**

Unit of Measure:

M = Meters

<blank> = Inches

Length

Base Number

Example: PE3FCA207-12 = 12 inches long cable  
PE3FCA207-100cm = 100 cm long cable

4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm LSZH, 2.0mm breakout, Aqua-25M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm LSZH, 2.0mm breakout, Aqua-25M PE3FCA207-25M](#)

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

4-Fiber LC UPC to ST UPC, OM4 Multimode Distribution Cable, 4.5mm LSZH, 2.0mm breakout, Aqua-25M

