


6-Fiber LC UPC to SC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-25M



PE3FCA257-25M

Features

- 6X LC UPC to 6X SC UPC
- Indoor multimode OM1
- Riser (OFNR) rated cable
- 5.0mm with tight buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for ceilings and riser areas

Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

Description

High-performance fiber optic cable assemblies like the PE3FCA257-25M from Pasternack are essential for efficient and reliable network infrastructures and part of a large selection of same day ship cable assemblies. Whether you need distribution assemblies for large-scale enterprise networks, fiber optic breakout assemblies for seamless connectivity, or fiber optic patch cord assemblies for precision connections, our solutions are engineered for durability and performance. Designed for various applications, including data centers, telecommunications, and industrial environments, our fiber optic distribution breakout assemblies ensure optimal signal integrity and minimal loss, making them the preferred choice for high-speed data transmission.

Our fiber optic distribution cables, including the Pasternack PE3FCA257-25M OM1 indoor fiber optic breakout assembly, cater to various bandwidth and distance requirements. Built with tight buffered aramid yarn construction, this 6-fiber multimode breakout assembly features LC UPC to SC UPC connectors and a Riser (OFNR) rated jacket for fire safety. The 5.0mm overall cable diameter, 2.0mm breakout diameter, and 50mm (10D) minimum bend radius ensure flexibility for indoor installations. Whether for data centers, structured cabling, or conduit routing, this assembly is designed to meet stringent industry standards.

The Pasternack PE3FCA257-25M OM1 fiber optic cable assembly provides 100Mb Ethernet support and 10Gb Ethernet up to 33 meters with a 62.5/125µm core size and an LED light source. With an operating temperature range of -20°C to 70°C, this assembly is ideal for ceilings and riser areas. Engineered for low attenuation and high durability, the tight buffered fiber with aramid yarn reinforcement ensures exceptional performance in demanding network environments. For further information on similar fiber optic products, our expert technical support and trained sales team can get you the ideal fiber optic multi-fiber cable assembly as per your requirements.


Configuration

Function	Breakout
Cable Type	6-Fiber Multimode
Mode	Multimode
Mode Class	OM1
Fiber Diameter	62.5/125 µm
Connection 1 Type	LC
Connection 1 Polish	UPC
Connection 2 Type	SC
Connection 2 Polish	UPC
Cable Color	Orange

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Return Loss	30			dB

6-Fiber LC UPC to SC UPC, OM1 Multimode Distribution
Cable, 5.0mm Riser, 2.0mm breakout, Orange-25M



PE3FCA257-25M

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Insertion Loss			0.3	dB

Mechanical Specifications

Cable Assembly

Length	25 m [984.25 in]
Width/Diameter	5 mm
Weight	174.18 g [0.384 lbs]

Cable

Cable Type	Breakout
Static Bend Radius	50 mm
Dynamic Bend Radius	100 mm
Max Crush Resistance, Short Term (N/100mm)	1,000
Max Crush Resistance, Long Term (N/100mm)	300

Connectors

Description	Connector 1	Connector 2
Type	LC	SC
Connector Polish	UPC	UPC

Environmental Specifications


Operating Range Temperature	-20 to +70 deg C
Storage Range Temperature	-40 to +70 deg C
Ingress Protection (IP) Rating	Non-Rated

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

6-Fiber LC UPC to SC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-25M



PE3FCA257-25M

Typical Performance Data

How to Order

Part Number Configuration: **PE3FCA257 - xx uu**

Unit of Measure:
M = Meters
<blank> = Inches

Length

Base Number

Example: PE3FCA257-12 = 12 inches long cable
PE3FCA257-100cm = 100 cm long cable


6-Fiber LC UPC to SC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-25M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [6-Fiber LC UPC to SC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-25M PE3FCA257-25M](#)

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA257-25M CAD Drawing

6-Fiber LC UPC to SC UPC, OM1 Multimode Distribution Cable, 5.0mm Riser, 2.0mm breakout, Orange-25M



UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE IN MILLIMETERS.

TOLERANCES:

- X = ±.2 [5]
- .XX = ±.02 [0.5]
- .XXX = ±.005 [0.13]

ANGLES ± 1°

CABLE LENGTH TOLERANCES:

- >12 [305] ≤ 60 [1524] = ±1 [25] / -0
- >60 [1524] ≤ 120 [3048] = ±4 [102] / -0
- >120 [3048] ≤ 300 [7620] = ±5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS OF INDIVIDUAL COMPONENTS MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.

PE PASTERNAK
an INFINITO brand

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE: NONE
SHEET: 1 OF 1

DESCRIPTION
6 STRAND LC UPC TO SC UPC, OM1 MULTIMODE DISTRIBUTION CABLE, 5.0mm RISER, 2.0mm BREAKOUT, ORANGE

SIZE	A	53919	HBAKKE	ITEM NO.	PE3FCA257	REV	A
------	---	-------	--------	----------	-----------	-----	---

NOTES:

- ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.
- CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

PE DS Rev-D4 Add