


8-Fiber SC UPC to SC UPC, OM5 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Lime Green-5M



PE3FCA376-5M

Features

- 8X SC UPC to 8X SC UPC
- Indoor multimode OM5
- Plenum (OFNP) rated cable
- 5.6mm with tight buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for wall, ceiling, conduits, and between buildings

Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

Description

High-performance fiber optic cable assemblies, including the PE3FCA376-5M from Pasternack, are designed for modern, high-speed network infrastructures and part of a large selection of same day ship cable assemblies. Whether deploying fiber optic distribution assemblies for enterprise networks, fiber optic breakout assemblies for seamless interconnectivity, or fiber optic patch cord assemblies for structured cabling, our solutions ensure durability and precision. Built for data centers, telecommunications, and industrial applications, our fiber optic distribution breakout assemblies deliver superior performance, ensuring optimal signal integrity and minimal loss.

The Pasternack PE3FCA376-5M indoor OM5 fiber optic distribution cable offers cutting-edge Wideband Multimode Fiber (WBMMF) technology, making it an ideal choice for next-generation networking. Supporting at least four WDM channels at 28Gbps per channel over the 850-953nm wavelength range, this 8 fiber assembly is optimized for shortwave Wavelength Division Multiplexing (SWDM). It features SC UPC to SC UPC connectors, a lime green Plenum (OFNP) jacket, and a tight buffered aramid yarn construction for enhanced durability.

With a bandwidth of 28000MHz·km, Pasternack's PE3FCA376-5M OM5 fiber optic cable assembly provides high-speed, high-density connectivity for cloud computing, data centers, and 400G Ethernet applications. The 5.6mm overall diameter, 2.0mm breakout diameter, and 42mm (7.5D) minimum bend radius offer flexible installation options, while the 0°C to 60°C operating temperature ensures consistent performance in demanding network environments. Engineered for indoor high-speed deployments, this fiber optic assembly guarantees reliability and superior signal integrity. For further information on similar products, our expert technical support and trained sales team can get you the ideal fiber optic multi-fiber cable assembly as per your requirements.


Configuration

| | |
|---------------------|-------------------|
| Function | Breakout |
| Cable Type | 8-Fiber Multimode |
| Mode | Multimode |
| Mode Class | OM5 |
| Fiber Diameter | 50/125 um |
| Connection 1 Type | SC |
| Connection 1 Polish | UPC |
| Connection 2 Type | SC |
| Connection 2 Polish | UPC |
| Cable Color | Lime Green |

Optical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------|---------|---------|---------|-------|
| Return Loss | 30 | | | dB |

8-Fiber SC UPC to SC UPC, OM5 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Lime Green-5M



PE3FCA376-5M

Optical Specifications

| Description | Minimum | Typical | Maximum | Units |
|----------------|---------|---------|---------|-------|
| Insertion Loss | | | 0.3 | dB |

Mechanical Specifications

Cable Assembly

| | |
|----------------|----------------------|
| Length | 5 m [196.85 in] |
| Width/Diameter | 5.6 mm |
| Weight | 134.26 g [0.296 lbs] |

Cable

| | |
|--|----------|
| Cable Type | Breakout |
| Static Bend Radius | 42 mm |
| Dynamic Bend Radius | 84 mm |
| Max Crush Resistance, Short Term (N/100mm) | 1,000 |
| Max Crush Resistance, Long Term (N/100mm) | 300 |

Connectors

| Description | Connector 1 | Connector 2 |
|------------------|-------------|-------------|
| Type | SC | SC |
| Connector Polish | UPC | UPC |

Environmental Specifications

| | |
|--------------------------------|------------------|
| Operating Range Temperature | 0 to +60 deg C |
| Storage Range Temperature | -20 to +60 deg C |
| Ingress Protection (IP) Rating | Non-Rated |


Compliance Certifications

(see product page for current document)

Plotted and Other Data

Notes:

8-Fiber SC UPC to SC UPC, OM5 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Lime Green-5M




PE3FCA376-5M

Typical Performance Data

How to Order

Part Number Configuration:



Example: PE3FCA376-12 = 12 inches long cable
PE3FCA376-100cm = 100 cm long cable

8-Fiber SC UPC to SC UPC, OM5 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Lime Green-5M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [8-Fiber SC UPC to SC UPC, OM5 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Lime Green-5M PE3FCA376-5M](#)

URL: <https://www.pasternack.com/sc-sc-multimode-upc-fiber-optic-cable-assembly-pe3fca376-5m-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA376-5M CAD Drawing

8-Fiber SC UPC to SC UPC, OM5 Multimode Distribution Cable, 5.6mm Plenum, 2.0mm breakout, Lime Green-5M



NOTES:

1. ALL CONNECTORS ACCCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
2. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.
3. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AN DESCRIPTION.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE, WHERE EXPORTED FROM THE UNITED STATES, IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS, DIVERSION CONTRARY TO U.S. LAW PROHIBITED.