


## 12-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 6.2mm Riser, 2.0mm breakout, Orange-15M



### PE3FCA428-15M

#### Features

- 12X SC UPC to 12X ST UPC
- Indoor multimode OM1
- Riser (OFNR) rated cable
- 6.2mm with tight buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for ceilings and riser areas

#### Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

#### Description

High-performance fiber optic cable assemblies like the PE3FCA428-15M from Pasternack are essential for efficient and reliable network infrastructures and part of a large selection of same day ship cable assemblies. Whether you need fiber optic distribution assemblies for large-scale enterprise networks, fiber optic breakout assemblies for seamless connectivity, or fiber optic patch cord assemblies for precision connections, our solutions are engineered for durability and performance. Designed for various applications, including data centers, telecommunications, and industrial environments, our fiber optic distribution breakout assemblies ensure optimal signal integrity and minimal loss, making them the preferred choice for high-speed data transmission.

Our fiber optic distribution cables, including the Pasternack PE3FCA428-15M OM1 indoor fiber optic breakout assembly, cater to various bandwidth and distance requirements. Built with tight buffered aramid yarn construction, this 12-fiber multimode breakout assembly features SC UPC to ST UPC connectors and a Riser (OFNR) rated jacket for fire safety. The 6.2mm overall cable diameter, 2.0mm breakout diameter, and 62.5mm (10D) minimum bend radius ensure flexibility for indoor installations. Whether for data centers, structured cabling, or conduit routing, this assembly is designed to meet stringent industry standards.

The Pasternack PE3FCA428-15M OM1 fiber optic cable assembly provides 100Mb Ethernet support and 10Gb Ethernet up to 33 meters with a 62.5/125µm core size and an LED light source. With an operating temperature range of -20°C to 70°C, this assembly is ideal for ceilings and riser areas. Engineered for low attenuation and high durability, the tight buffered fiber with aramid yarn reinforcement ensures exceptional performance in demanding network environments. For further information on similar fiber optic products, our expert technical support and trained sales team can get you the ideal fiber optic multi-fiber cable assembly as per your requirements.


#### Configuration

|                     |                    |
|---------------------|--------------------|
| Function            | Breakout           |
| Cable Type          | 12-Fiber Multimode |
| Mode                | Multimode          |
| Mode Class          | OM1                |
| Fiber Diameter      | 62.5/125 µm        |
| Connection 1 Type   | SC                 |
| Connection 1 Polish | UPC                |
| Connection 2 Type   | ST                 |
| Connection 2 Polish | UPC                |
| Cable Color         | Orange             |

#### Optical Specifications

| Description | Minimum | Typical | Maximum | Units |
|-------------|---------|---------|---------|-------|
| Return Loss | 30      |         |         | dB    |

## 12-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 6.2mm Riser, 2.0mm breakout, Orange-15M



### PE3FCA428-15M

#### Optical Specifications

| Description    | Minimum | Typical | Maximum | Units |
|----------------|---------|---------|---------|-------|
| Insertion Loss |         |         | 0.3     | dB    |

#### Mechanical Specifications

##### Cable Assembly

|                |                      |
|----------------|----------------------|
| Length         | 15 m [590.55 in]     |
| Width/Diameter | 6.2 mm               |
| Weight         | 234.96 g [0.518 lbs] |

##### Cable

|                                            |          |
|--------------------------------------------|----------|
| Cable Type                                 | Breakout |
| Static Bend Radius                         | 62 mm    |
| Dynamic Bend Radius                        | 124 mm   |
| Max Crush Resistance, Short Term (N/100mm) | 1,000    |
| Max Crush Resistance, Long Term (N/100mm)  | 300      |

#### Connectors

| Description      | Connector 1 | Connector 2 |
|------------------|-------------|-------------|
| Type             | SC          | ST          |
| Connector Polish | UPC         | UPC         |

#### Environmental Specifications


|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -20 to +70 deg C |
| Storage Range Temperature      | -40 to +70 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

12-Fiber SC UPC to ST UPC, OM1 Multimode Distribution  
Cable, 6.2mm Riser, 2.0mm breakout, Orange-15M



**PE3FCA428-15M**

**Typical Performance Data**

**How to Order**

Part Number Configuration:

**PE3FCA428**

**- xx**

**uu**

Unit of Measure:

M = Meters

<blank> = Inches

Length

Base Number

Example: PE3FCA428-12 = 12 inches long cable  
PE3FCA428-100cm = 100 cm long cable

12-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 6.2mm Riser, 2.0mm breakout, Orange-15M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [12-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 6.2mm Riser, 2.0mm breakout, Orange-15M PE3FCA428-15M](#)

URL: <https://www.pasternack.com/sc-st-multimode-upc-fiber-optic-cable-assembly-pe3fca428-15m-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA428-15M CAD Drawing

12-Fiber SC UPC to ST UPC, OM1 Multimode Distribution Cable, 6.2mm Riser, 2.0mm breakout, Orange-15M

