


## 12-Fiber LC UPC to SC UPC, OM4 Multimode Distribution Cable, 6.2mm Plenum, 2.0mm breakout, Aqua-30M



### PE3FCA418-30M

#### Features

- 12X LC UPC to 12X SC UPC
- Indoor multimode OM4
- Plenum (OFNP) rated cable
- 6.2mm with tight buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for wall, ceiling, conduits, and between buildings

#### Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

#### Description

High-performance fiber optic cable assemblies, including the PE3FCA418-30M from Pasternack, are designed for modern, high-speed network infrastructures and part of a large selection of same day ship cable assemblies. Whether deploying fiber optic distribution assemblies for enterprise networks, fiber optic breakout assemblies for seamless interconnectivity, or fiber optic patch cord assemblies for structured cabling, our solutions ensure durability and precision. Built for data centers, telecommunications, and industrial applications, our fiber optic distribution breakout assemblies deliver superior performance, ensuring optimal signal integrity and minimal loss.

For longer transmission distances and higher bandwidth, the Pasternack PE3FCA418-30M indoor OM4 fiber optic breakout assembly supports 10Gb Ethernet up to 550 meters and 40G/100G Ethernet up to 150 meters. Built with a tight buffered aramid yarn strength member, this 12-fiber multimode assembly features LC UPC to SC UPC connectors, a 6.2mmmm overall cable diameter, and a 2.0mm breakout diameter, ensuring superior durability and performance. The aqua-colored Plenum (OFNP) rated jacket is suitable for wall, ceiling, conduits, and between buildings, making it a reliable choice for data centers, telecom networks, and high-performance computing environments.

With a bandwidth of 4700MHz·km, Pasternack's PE3FCA418-30M OM4 fiber optic cable delivers low attenuation and high-speed performance for mission-critical applications. Its 46.5mm (7.5D) minimum bend radius and 0°C to 60°C operating temperature provide the flexibility needed for indoor routing, structured cabling, and conduit installations. Designed for hyperscale data centers and telecom backbones, this fiber optic assembly ensures seamless network connectivity with minimal signal loss. For further information on similar products, our expert technical support and trained sales team can get you the ideal fiber optic multi-fiber cable assembly as per your requirements.


#### Configuration

Function	Breakout
Cable Type	12-Fiber Multimode
Mode	Multimode
Mode Class	OM4
Fiber Diameter	50/125 um
Connection 1 Type	LC
Connection 1 Polish	UPC
Connection 2 Type	SC
Connection 2 Polish	UPC
Cable Color	Aqua Blue

#### Optical Specifications

Description	Minimum	Typical	Maximum	Units
Return Loss	30			dB

12-Fiber LC UPC to SC UPC, OM4 Multimode Distribution Cable, 6.2mm Plenum, 2.0mm breakout, Aqua-30M



**PE3FCA418-30M**

**Optical Specifications**

Description	Minimum	Typical	Maximum	Units
Insertion Loss			0.3	dB

**Mechanical Specifications**

**Cable Assembly**

Length	30 m [1181.10 in]
Width/Diameter	6.2 mm
Weight	303 g [0.668 lbs]

**Cable**

Cable Type	Breakout
Static Bend Radius	47 mm
Dynamic Bend Radius	93 mm
Max Crush Resistance, Short Term (N/100mm)	1,000
Max Crush Resistance, Long Term (N/100mm)	300

**Connectors**

Description	Connector 1	Connector 2
Type	LC	SC
Connector Polish	UPC	UPC

**Environmental Specifications**


Operating Range Temperature	0 to +60 deg C
Storage Range Temperature	-20 to +60 deg C
Ingress Protection (IP) Rating	Non-Rated

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

12-Fiber LC UPC to SC UPC, OM4 Multimode Distribution Cable, 6.2mm Plenum, 2.0mm breakout, Aqua-30M



**PE3FCA418-30M**

**Typical Performance Data**

**How to Order**



Example:    PE3FCA418-12 = 12 inches long cable  
              PE3FCA418-100cm = 100 cm long cable

12-Fiber LC UPC to SC UPC, OM4 Multimode Distribution Cable, 6.2mm Plenum, 2.0mm breakout, Aqua-30M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [12-Fiber LC UPC to SC UPC, OM4 Multimode Distribution Cable, 6.2mm Plenum, 2.0mm breakout, Aqua-30M PE3FCA418-30M](#)

URL: <https://www.pasternack.com/lc-sc-multimode-upc-fiber-optic-cable-assembly-pe3fca418-30m-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

# PE3FCA418-30M CAD Drawing

12-Fiber LC UPC to SC UPC, OM4 Multimode Distribution Cable, 6.2mm Plenum, 2.0mm breakout, Aqua-30M

