

## Fiber Optic Patch Cable, Simplex ST UPC to ST UPC, MM OM5, 2.0mm Riser, Lime Green



### PE3FCA479

#### Features

- Multimode OM5 fiber optic cable assembly
- Simplex ST UPC to ST UPC
- Indoor Riser (OFNR) cable
- Suitable for ceilings and riser areas
- Custom lengths available with the same fast delivery

#### Applications

- Telecom & Networking
- Data Centers
- Enterprise and Corporate Networks
- Broadcasting & Media Production
- Military & Defense
- Healthcare & Medical Imaging
- Transportation & Rail
- Oil & Gas

#### Description

The PE3FCA479 fiber optic patch cord is a high-performance OM5 fiber optic cable assembly from Pasternack, tailored for superior data transmission in high-demand environments. Equipped with simplex ST UPC to ST UPC connectors, this OM5 simplex fiber optic patch cable is optimized for indoor use and comes with a Riser (OFNR) rating that adheres to fire and safety requirements. With a 2.0mm diameter and Lime Green color, this fiber optic jumper is easily identifiable in complex network setups. With an operating temperature range of -20°C to 70°C and storage temperature of -40°C to 70°C, this fiber optic cable assembly is built to perform reliably across diverse conditions.

As an OM5 fiber optic jumper, Pasternack's PE3FCA479 is designed for ultra-high-speed, high-bandwidth data transmission, supporting greater distances and faster speeds than OM1 and OM3 fiber. This makes it ideal for Telecom & Networking, Data Centers, and Enterprise and Corporate Networks, where extended reach and top-tier fiber performance is crucial. Custom lengths are available to meet specific installation needs, providing flexibility for various setups while maintaining quick delivery and consistent quality.

Beyond standard networking, the Pasternack PE3FCA479 OM5 fiber patch cord supports specialized applications in industries like Broadcasting & Media Production, Military & Defense, and Healthcare & Medical Imaging. This fiber assembly delivers a versatile and durable solution for any setup requiring robust, high-speed data transmission in controlled indoor environments. For further information on similar fiber optic products, our expert technical support and trained sales team can get you the ideal fiber optic simplex cable assembly as per your requirements.

#### Configuration

|                     |                   |
|---------------------|-------------------|
| Function            | Patch             |
| Cable Type          | Simplex Multimode |
| Mode                | Multimode         |
| Mode Class          | OM5               |
| Fiber Diameter      | 50/125 um         |
| Connection 1 Type   | ST                |
| Connection 1 Polish | UPC               |
| Connection 2 Type   | ST                |
| Connection 2 Polish | UPC               |
| Cable Color         | Lime Green        |

#### Mechanical Specifications

##### Cable Assembly

|                |                    |
|----------------|--------------------|
| Width/Diameter | 2 mm               |
| Weight         | 8.16 g [0.018 lbs] |

##### Cable

|            |       |
|------------|-------|
| Cable Type | Patch |
|------------|-------|

Fiber Optic Patch Cable, Simplex ST UPC to ST  
UPC, MM OM5, 2.0mm Riser, Lime Green



**PE3FCA479**

|                                            |       |
|--------------------------------------------|-------|
| Static Bend Radius                         | 15 mm |
| Dynamic Bend Radius                        | 30 mm |
| Max Crush Resistance, Short Term (N/100mm) | 200   |
| Max Crush Resistance, Long Term (N/100mm)  | 50    |

**Connectors**

| Description      | Connector 1 | Connector 2 |
|------------------|-------------|-------------|
| Type             | ST          | ST          |
| Connector Polish | UPC         | UPC         |

**Environmental Specifications**

|                                |                  |
|--------------------------------|------------------|
| Operating Range Temperature    | -20 to +70 deg C |
| Storage Range Temperature      | -40 to +70 deg C |
| Ingress Protection (IP) Rating | Non-Rated        |

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

Fiber Optic Patch Cable, Simplex ST UPC to ST UPC, MM OM5, 2.0mm Riser, Lime Green



## PE3FCA479

### Typical Performance Data

### How to Order

Part Number Configuration:

**PE3FCA479**

**-XX**

**UU**

Unit of Measure:

M = Meters

<blank> = Inches

Lengths

Base Number

Example: PE3FCA479-12 = 12 inches long cable  
PE3FCA479-100cm = 100 cm long cable


Fiber Optic Patch Cable, Simplex ST UPC to ST UPC, MM OM5, 2.0mm Riser, Lime Green from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fiber Optic Patch Cable, Simplex ST UPC to ST UPC, MM OM5, 2.0mm Riser, Lime Green PE3FCA479](#)

URL: <https://www.pasternack.com/st-st-multimode-50-125-mm-simplex-riser-fiber-patch-cable-om5-fiber-optic-cable-assembly-pe3fca479-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA479 CAD Drawing
Fiber Optic Patch Cable, Simplex ST UPC to ST UPC, MM OM5, 2.0mm Riser, Lime Green



- NOTES:
- 1. ST CONNECTOR ASSEMBLY POLISH TYPE: UPC.
- 2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
- 3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.
- 4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- 5. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.

|                                                                                                                          |  |                  |  |           |  |        |  |
|--------------------------------------------------------------------------------------------------------------------------|--|------------------|--|-----------|--|--------|--|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. DIMENSIONS IN [ ] ARE MILLIMETERS.                                 |  | TOLERANCES:      |  | FRACTIONS |  | ANGLES |  |
| X = ±.2 [5]                                                                                                              |  | .XX = ±.02 [0.5] |  | ± 1/32    |  | ± 1°   |  |
| .XXX = ±.005 [0.13]                                                                                                      |  |                  |  |           |  |        |  |
| CABLE LENGTH TOLERANCES:                                                                                                 |  |                  |  |           |  |        |  |
| >12 [305] ≤ 60 [1524] = ±.125 [-0]                                                                                       |  |                  |  |           |  |        |  |
| >60 [1524] ≤ 120 [3048] = ±.125 [-0]                                                                                     |  |                  |  |           |  |        |  |
| >120 [3048] ≤ 300 [7620] = ±.125 [-0]                                                                                    |  |                  |  |           |  |        |  |
| ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS OF INDIVIDUAL FEATURES MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY. |  |                  |  |           |  |        |  |

|                                                        |  |                             |  |                                        |  |
|--------------------------------------------------------|--|-----------------------------|--|----------------------------------------|--|
| PE PASTERNAK® an INFINITE® brand                       |  | Website: www.Pasternack.com |  | Phone: 1.866.727.8376   1.949.261.1920 |  |
| INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5 |  | SCALE                       |  | NONE                                   |  |
| SHEET                                                  |  | 1 OF 1                      |  |                                        |  |

|             |  |                                                                                    |  |
|-------------|--|------------------------------------------------------------------------------------|--|
| DESCRIPTION |  | FIBER OPTIC PATCH CABLE, SIMPLEX ST UPC TO ST UPC, MM OM5, 2.0mm RISER, LIME GREEN |  |
| SIZE        |  | A                                                                                  |  |
| CAGE CODE   |  | 53919                                                                              |  |
| DRAWN BY    |  | KGLEBOVA                                                                           |  |
| ITEM NO.    |  | PE3FCA479                                                                          |  |
| REV         |  | A                                                                                  |  |