

Fiber Optic Patch Cable, Duplex ST UPC to ST UPC, MM OM5, 2.0mm Plenum, Lime Green



PE3FCA538

Features

- Multimode OM5 indoor fiber optic cable assembly\\Dual ST UPC to Dual ST UPC\\Indoor Plenum (OFNP) rated cable\\Suitable for wall, ceiling, conduits, and between buildings\\2.0mm x 4.1mm duplex zip-cord\\Custom lengths available with the same fast delivery

Applications

- Telecom & Networking
- Data Centers
- Enterprise and Corporate Networks
- Broadcasting & Media Production
- Military & Defense
- Healthcare & Medical Imaging
- Transportation & Rail
- Oil & Gas

Description

The PE3FCA538 fiber optic patch cord is a high-performance OM5 fiber optic cable assembly, tailored for superior data transmission in high-demand environments. Equipped with Dual ST UPC to Dual ST UPC connectors, this OM5 duplex fiber optic patch cable is optimized for indoor use and comes with a Plenum (OFNP) rated cable that adheres to fire and safety requirements. With a 2.0mm x 4.1mm diameter and lime green color, this fiber optic jumper is easily identifiable in complex network setups. Its operating temperature range of 0°C to 60°C and storage temperature of -20°C to 60°C ensures reliable operation across a variety of environmental conditions.

As an OM5 fiber optic jumper, Pasternack's PE3FCA538 is designed for ultra-high-speed, high-bandwidth data transmission, supporting greater distances and faster speeds than OM3 & OM4 fiber. This makes it ideal for Telecom & Networking, Data Centers, and Enterprise and Corporate Networks, where extended reach and top-tier fiber performance is crucial. Custom lengths are available to meet specific installation needs, providing flexibility for various setups while maintaining quick delivery and consistent quality.

Beyond standard networking, the Pasternack PE3FCA538 OM5 fiber patch cord supports specialized applications in industries like Broadcasting & Media Production, Military & Defense, and Healthcare & Medical Imaging. This fiber assembly delivers a versatile and durable solution for any setup requiring robust, high-speed data transmission in controlled indoor environments. For further information on similar fiber optic products, our expert technical support and trained sales team can get you the ideal fiber optic duplex cable assembly as per your requirements.

Configuration

Function	Patch
Cable Type	Duplex Multimode
Mode	Multimode
Mode Class	OM5
Fiber Diameter	50/125 um
Connection 1 Type	ST
Connection 1 Polish	UPC
Connection 2 Type	ST
Connection 2 Polish	UPC
Cable Color	Lime Green

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Return Loss	30			dB

Fiber Optic Patch Cable, Duplex ST UPC to ST
UPC, MM OM5, 2.0mm Plenum, Lime Green



PE3FCA538

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Insertion Loss			0.3	dB

Mechanical Specifications

Cable Assembly

Length	0 mm [0.00 in]
Width/Diameter	2 mm
Weight	16.78 g [0.037 lbs]

Cable

Cable Type	Patch
Static Bend Radius	15 mm
Dynamic Bend Radius	30 mm
Max Crush Resistance, Short Term (N/100mm)	300
Max Crush Resistance, Long Term (N/100mm)	100

Connectors

Description	Connector 1	Connector 2
Type	ST	ST
Connector Polish	UPC	UPC

Environmental Specifications

Operating Range Temperature	+60 to 0 deg C
Storage Range Temperature	-20 deg C
Ingress Protection (IP) Rating	Non-Rated

Compliance Certifications (see [product page](#) for current document)

DFARS Compliant	60
-----------------	----

Plotted and Other Data

Notes:

Fiber Optic Patch Cable, Duplex ST UPC to ST UPC, MM OM5, 2.0mm Plenum, Lime Green



PE3FCA538

Typical Performance Data

How to Order

Part Number Configuration: **PE3FCA538** **- xx** **uu**

Unit of Measure:
M = Meters
<blank> = Inches

Length

Base Number

Example: PE3FCA538-12 = 12 inches long cable
PE3FCA538-100cm = 100 cm long cable

Fiber Optic Patch Cable, Duplex ST UPC to ST UPC, MM OM5, 2.0mm Plenum, Lime Green from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Fiber Optic Patch Cable, Duplex ST UPC to ST UPC, MM OM5, 2.0mm Plenum, Lime Green PE3FCA538](#)

URL: <https://www.pasternack.com/st-st-multimode-50-125-mm-duplex-plenum-fiber-patch-cable-om5-fiber-optic-cable-assembly-pe3fca538-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA538 CAD Drawing

Fiber Optic Patch Cable, Duplex ST UPC to ST UPC, MM OM5, 2.0mm Plenum, Lime Green



NOTES:

1. ST CONNECTOR POLISH TYPE: UPC.
2. ALL CONNECTORS ACCOMPANIED WITH A DUST CAP INSTALLED (NOT SHOWN).
3. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED.
4. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
5. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND DESCRIPTION.