



MIL-DTL-17 SMA Male to TNC Male Cable 100 cm
Length Using M17/60-RG142 Coax

RF Cable Assemblies Technical Data Sheet

PE3M0026-100CM

Configuration

- Connector 1: M39012/55-3028(SMA Male)
- Connector 2: M39012/26-0011(TNC Male)
- Cable: M17/60-RG142

Features

- Max Frequency 11 GHz
- 69.5% Phase Velocity
- Double Shielded
- FEP Jacket
- Lot Traceability
- J-STD-Soldering
- Qualified (QPL) cable and connectors
- RF Test Plots
- Test Report
- In stock and ready to ship

Applications

- Hi-Rel
- MIL-DTL-17 Requirements
- Avionics
- IFF
- SATCOM
- ECM

Description

Pasternack's MIL-DTL-17 cable assemblies are part of our full line of reliable RF components available for same-day shipping. These commercial-off-the-shelf (COTS), military grade cable assemblies are designed and processed with high reliability in mind. MIL-PRF-39012 connectors and MIL-C-17 coaxial cable are assembled using J-STD soldering processes and WHMA-A-620 workmanship criteria. The combination of materials, processing and acceptance testing work together to create a dependable cable assembly for applications where performance over time is important or the cost of failure is high. Each finished MIL-DTL-17 cable assembly is traceable to its component lots and a test report is available for every lot produced.

Our MIL-DTL-17 cable assembly datasheet specifications and drawing with dimensions are shown below in this PDF. Pasternack's broad catalog of RF, microwave and millimeter wave cable assemblies allow designers to configure and customize their signal connections however they like. Whether the need is to provide reliable mil-spec connections or fielding dependable RF cable assemblies, Pasternack has the right cable assemblies for the job. Pasternack can also expertly build your custom cable assemblies for you and ship same day.

Referenced Specifications

| | |
|----------------|---|
| IPC/WHMA-A-620 | Requirements and Acceptance for Cable and Wire Harness Assemblies |
| MIL-DTL-17 | Cables, Radio Frequency, Flexible and Semirigid, General Specification for |
| MIL-STD-348 | Radio Frequency Connector Interfaces for MIL-DTL-3643, MIL-DTL-3650, MIL-DTL-3655, MIL-DTL-25516, MIL-PRF-31031, MIL-PRF-39012, MIL-PRF-49142, MIL-PRF... |
| MIL-PRF-39012 | Connectors, Coaxial, Radio Frequency, General Specification for |
| IPC J-STD-001 | Requirements for Soldered Electrical and Electronic Assemblies |
| IPC J-STD-006 | Requirements for Electronic Grade Solder Alloys and Fluxed and Non-Fluxed Solid Solders for Electronic Soldering Applications |
| SAE AS5942 | Marking of Electrical Insulating Materials |
| SAE AS23053 | Insulation Sleeving, Electrical, Heat Shrinkable, General Specifications For |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to TNC Male Cable 100 cm Length Using M17/60-RG142 Coax PE3M0026-100CM](#)



MIL-DTL-17 SMA Male to TNC Male Cable 100 cm Length Using M17/60-RG142 Coax

RF Cable Assemblies Technical Data Sheet

PE3M0026-100CM

SAE AS22520

Crimping Tools, Wire Termination, General Specification For

Material Specifications

| Component | Specification |
|---------------|---|
| Cable | M17/60-RG142 in accordance with MIL-DTL-17 |
| Connector 1 | M39012/55-3028 in accordance with MIL-PRF-39012 |
| Connector 2 | M39012/26-0011 in accordance with MIL-PRF-39012 |
| Heat Shrink 1 | M23053/5-106-0 in accordance with SAE AS23053 |
| Heat Shrink 2 | M23053/5-106-0 in accordance with SAE AS23053 |
| Solder | SN63 in accordance with J-STD-006 |

Electrical Specifications

| Description | Minimum | Typical | Maximum | Units |
|--------------------------------------|---------|--------------|---------|--------------|
| Frequency Range | DC | | 11 | GHz |
| VSWR | | | 1.6:1 | |
| Velocity of Propagation | | 69.5 | | % |
| Capacitance | | 29.3 [96.13] | | pF/ft [pF/m] |
| Dielectric Withstanding Voltage (AC) | | | 1,000 | Vrms |

Specifications by Frequency

| Description | F1 | F2 | F3 | F4 | F5 | Units |
|-----------------------|------|------|------|------|------|-------|
| Frequency | 0.4 | 1 | 3 | 8 | 11 | GHz |
| Insertion Loss (Max.) | 0.39 | 0.63 | 1.17 | 2.24 | 3.23 | dB |

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of $0.06 \cdot \sqrt{\text{GHz}}$ dB maximum for the connectors.

Mechanical Specifications

Cable Assembly

| Description | Minimum | Typical | Maximum | Units |
|----------------------|---------------|---------------|------------------|---------|
| Length* | 39.3701 [100] | 39.3701 [100] | 40.3701 [102.54] | in [cm] |
| Cable Outer Diameter | 0.19 | 0.195 | 0.2 | in |
| Weight | | | 0.24 [108.86] | lbs [g] |

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to TNC Male Cable 100 cm Length Using M17/60-RG142 Coax PE3M0026-100CM](#)



MIL-DTL-17 SMA Male to TNC Male Cable 100 cm
 Length Using M17/60-RG142 Coax

RF Cable Assemblies Technical Data Sheet

PE3M0026-100CM

*Length Tolerances: +0.5, -0 inches for Length ≤ 1 foot; +1, -0 inches for Length >1 to 5 feet; +2, -0 inches for Length >5 to 10 feet; +3, -0 inches for Length >10 to 25 feet and +2%, -0 inches for Length >25 feet.

Cable Characteristics

| Description | Specification |
|--------------------------------------|---------------------------|
| Cable Type | M17/60-RG142 |
| Impedance | 50 Ohms |
| Inner Conductor Type | Solid |
| Inner Conductor Material and Plating | Copper Clad Steel, Silver |
| Dielectric Type | PTFE |
| Number of Shields | 2 |
| Shield Layer 1 | Silver Clad Copper |
| Shield Layer 2 | Silver Clad Copper |
| Outer Conductor Diameter | 0.171 in [4.34 mm] |
| Jacket Material | FEP |

Connector Characteristics

| Description | Connector 1 | Connector 2 |
|---------------------------------------|----------------------------|------------------------|
| Type | SMA Male | TNC Male |
| Specification | MIL-PRF-39012 | MIL-PRF-39012 |
| Impedance | 50 Ohms | 50 Ohms |
| Contact Material and Plating | Beryllium Copper, Gold | Brass, Gold |
| Contact Plating Specification | | ASTM B488 |
| Dielectric Type | PTFE | Teflon |
| Outer Conductor Material and Plating | | Beryllium Copper, Gold |
| Outer Conductor Plating Specification | | ASTM B488 |
| Body Material and Plating | Passivated Stainless Steel | Brass, Silver |
| Body Plating Specification | | ASTM B700 |
| Coupling Nut Material and Plating | Passivated Stainless Steel | |
| Seal Gasket Material | Silicone Rubber | Silicone Rubber |
| Contact Gage Specification | 0.000 in min | 0.210 to 0.230 in |
| Insulator Gage Specification | 0.000 in min | 0.208 to 0.228 in |

Mechanical Specification Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to TNC Male Cable 100 cm Length Using M17/60-RG142 Coax PE3M0026-100CM](#)



MIL-DTL-17 SMA Male to TNC Male Cable 100 cm
 Length Using M17/60-RG142 Coax

RF Cable Assemblies Technical Data Sheet

PE3M0026-100CM

Environmental Specifications

| Description | Specification |
|-----------------------------|-------------------|
| Temperature Operating Range | -55 to +165 deg C |

Compliance Certifications (see [product page](#) for current document)

Process Specifications

| Process | Specification |
|-------------|---|
| Soldering | in accordance with J-STD-001, class 3 |
| Crimping | dies in accordance with SAE AS22520 |
| Marking | shall meet the adherence requirements of SAE AS5942 |
| Workmanship | shall be in accordance with IPC/WHMA-A-620, class 3 |

Tests and Inspections

| Description | Sampling |
|---|--------------|
| Connector Gaging (pin and insulator position) | 100% |
| Insertion Loss | 100% |
| VSWR | 100% |
| Dielectric Withstanding Voltage (DWV) | 100% |
| Visual - workmanship, configuration and marking | 100% |
| Length | C=0, 1.5 AQL |
| Mass | C=0, 1.5 AQL |

Plotted and Other Data

Notes:

- Values at 25°C, sea level.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to TNC Male Cable 100 cm Length Using M17/60-RG142 Coax PE3M0026-100CM](#)



MIL-DTL-17 SMA Male to TNC Male Cable 100 cm
Length Using M17/60-RG142 Coax

RF Cable Assemblies Technical Data Sheet

PE3M0026-100CM

How to Order

Part Number Configuration:

PE3M0026

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3M0026-12 = 12 inches long cable
PE3M0026-100cm = 100 cm long cable

MIL-DTL-17 SMA Male to TNC Male Cable 100 cm Length Using M17/60-RG142 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [MIL-DTL-17 SMA Male to TNC Male Cable 100 cm Length Using M17/60-RG142 Coax PE3M0026-100CM](https://www.pasternack.com/sma-male-tnc-male-m17-60-rg142-cable-assembly-pe3m0026-100cm-p.aspx)

URL: <https://www.pasternack.com/sma-male-tnc-male-m17-60-rg142-cable-assembly-pe3m0026-100cm-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3M0026-100CM CAD Drawing

MIL-DTL-17 SMA Male to TNC Male Cable 100 cm Length Using M17/60-RG142 Coax



| STANDARD TOLERANCES | |
|---------------------|--------|
| .X | ±0.2 |
| .XX | ±0.01 |
| .XXX | ±0.005 |

NOTES:
 *STANDARD TOLERANCES APPLY ONLY TO DIMENSIONS IN INCHES
 1. BLACK HEAT SHRINK WITH WHITE MARKINGS 3 PLACES.

| | | | | | | |
|---|--|--|---|---------------------------------------|------------------------------------|---------------|
| <p>PASTERNACK® <small>THE ENGINEER'S RF-SOURCE</small> Pasternack Enterprises, Inc. P.O. Box 16759 Irvine CA 92623 Phone: (949) 261-1920 Fax: (949) 261-7451 Website: www.pasternack.com E-Mail: sales@pasternack.com</p> | | <p>DWG TITLE PE3M0026</p> | <p>CAD FILE 08/14/18</p> | <p>SCALE N/A</p> | <p>SIZE A</p> | <p>CN2379</p> |
| <p>NOTES: 1. UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE NOMINAL. 2. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE WITHOUT NOTICE AT ANY TIME. 3. DIMENSIONS ARE IN INCHES [mm].</p> | | | | | | |
| <p>CAGE CODE 53919</p> | | | | | | |