

4-Fiber LC UPC to ST UPC, OS2 Single Mode Indoor Distribution Cable, 4.5mm Riser, 2.0mm breakout, Yellow-15M



PE3FCA561-15M

Features

- 4X LC UPC to 4X ST UPC
- Indoor single mode OS2
- Riser (OFNR) rated cable
- 4.5mm with tight-buffer and aramid yarn strength member
- 2mm TIA 598 color coded, .5M breakout
- Suitable for ceilings and riser areas

Applications

- Data centers
- Passive Optical Networks (PON)
- Local Area Networks (LAN)
- Enterprise Networking
- Storage and cloud based services
- AI data storage and communications
- Headend termination to a fiber backbone
- Terminations of data center fiber rack system

Description

High-performance fiber optic cable assemblies, including the PE3FCA561-15M from Pasternack, are designed for modern, high-speed network infrastructures and part of a large selection of same day ship cable assemblies. Whether deploying fiber optic distribution assemblies for enterprise networks, fiber optic breakout assemblies for seamless interconnectivity, or fiber optic patch cord assemblies for structured cabling, our solutions ensure durability and precision. Built for data centers, telecommunications, and industrial applications, our fiber optic distribution breakout assemblies deliver superior performance, ensuring optimal signal integrity and minimal loss.

For long-distance and high-speed transmission, the Pasternack PE3FCA561-15M indoor Single Mode G.657.A1 OS2 fiber optic cable assembly offers ultra-low attenuation over distances up to 10km for 10G Ethernet and beyond. Built with a 9/125µm core size, this LC UPC to ST UPC fiber optic distribution assembly ensures minimal signal loss for campus networks, metro Ethernet, and telecom infrastructure. The yellow Riser (OFNR) rated jacket, tight-buffered aramid yarn construction, and 33.75mm (7.5D) minimum bend radius provide maximum durability and performance.

With an operating temperature range of -20°C to 70°C, Pasternack's PE3FCA561-15M OS2 fiber optic cable is designed for indoor environments, supporting ceilings and riser areas. The 4.5mm overall cable diameter and 2.0mm breakout diameter allow for flexible routing while maintaining low insertion loss and superior signal integrity. Whether for enterprise backbones, long-haul networking, or high-speed data transmission, this OS2 fiber optic assembly delivers exceptional reliability for critical infrastructure deployments. For further information on similar products, our expert technical support and trained sales team can get you the ideal fiber optic multi-fiber cable assembly as per your requirements.

Configuration

Function	Breakout
Cable Type	4-Fiber Single Mode
Mode	Single Mode
Mode Class	OS2
Fiber Diameter	9/125 µm
Connection 1 Type	LC
Connection 1 Polish	UPC
Connection 2 Type	ST
Connection 2 Polish	UPC
Cable Color	Yellow

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Return Loss	50			dB

4-Fiber LC UPC to ST UPC, OS2 Single Mode Indoor Distribution Cable, 4.5mm Riser, 2.0mm breakout, Yellow-15M



PE3FCA561-15M

Optical Specifications

Description	Minimum	Typical	Maximum	Units
Insertion Loss			0.3	dB

Mechanical Specifications

Cable Assembly

Length	15 m [590.55 in]
Width/Diameter	4.5 mm
Weight	110.68 g [0.244 lbs]

Cable

Cable Type	Breakout
Static Bend Radius	34 mm
Dynamic Bend Radius	67 mm
Max Crush Resistance, Short Term (N/100mm)	1,000
Max Crush Resistance, Long Term (N/100mm)	300

Connectors

Description	Connector 1	Connector 2
Type	LC	ST
Connector Polish	UPC	UPC

Environmental Specifications

Operating Range Temperature	-20 to +70 deg C
Storage Range Temperature	-40 to +70 deg C
Ingress Protection (IP) Rating	Non-Rated

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

4-Fiber LC UPC to ST UPC, OS2 Single Mode Indoor
Distribution Cable, 4.5mm Riser, 2.0mm breakout, Yellow-15M



PE3FCA561-15M

Typical Performance Data

How to Order

Part Number Configuration:

PE3FCA561

- XX

uu

- Unit of Measure:

M = Meters

<blank> = Inches

- Length

- Base Number

Example: PE3FCA561-12 = 12 inches long cable
PE3FCA561-100cm = 100 cm long cable

4-Fiber LC UPC to ST UPC, OS2 Single Mode Indoor Distribution Cable, 4.5mm Riser, 2.0mm breakout, Yellow-15M from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [4-Fiber LC UPC to ST UPC, OS2 Single Mode Indoor Distribution Cable, 4.5mm Riser, 2.0mm breakout, Yellow-15M PE3FCA561-15M](#)

URL: <https://www.pasternack.com/lc-st-single-mode-9-125-sm-4.5mm-db-cable-2.0mm-bo-0.5m-riser-fiber-optic-cable-assembly-pe3fca561-15m-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3FCA561-15M CAD Drawing
4-Fiber LC UPC to ST UPC, OS2 Single Mode Indoor Distribution
Cable, 4.5mm Riser, 2.0mm breakout, Yellow-15M

