



TRB Plug to TRB Plug Right Angle 1553 Cable
Using 78 Ohm M17/176-00002 Coax

RF Cable Assemblies Technical Data Sheet

PE3MP2166

Configuration

- Connector 1: TRB Plug
- Connector 2: TRB Plug Right Angle
- Cable Type: M17/176-00002
- Coax Flex Type: Flexible

Features

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Description

Pasternack's PE3MP2166 78 ohm TRB plug to 78 ohm TRB plug right angle cable using 78 ohm M17/176-00002 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to TRB cable assembly has a plug to plug gender configuration with 78 ohm flexible M17/176-00002 twinax. The PE3MP2166 TRB plug to TRB plug cable assembly operates to 10 MHz. The right angle TRB interface on the M17/176-00002 cable allows for easier connections in tight spaces.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB Plug to TRB Plug Right Angle 1553 Cable Using 78 Ohm M17/176-00002 Coax PE3MP2166](#)



TRB Plug to TRB Plug Right Angle 1553 Cable
Using 78 Ohm M17/176-00002 Coax

RF Cable Assemblies Technical Data Sheet

PE3MP2166

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	7	10	MHz
Insertion Loss (Typ.)	0.014	0.021	0.028	0.035	0.045	dB/ft
	0.05	0.07	0.09	0.11	0.15	dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB for the straight connector and 0.2 dB for the right angle connector.

Mechanical Specifications

Cable Assembly

Weight 0.135 lbs [61.23 g]

Cable

Cable Type M17/176-00002
Impedance 78 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper, Silver
Dielectric Type PTFE
Shield Layer 1 Silver Plated Copper
Jacket Material PFA, Blue

One Time Minimum Bend Radius 1.5 in [38.1 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB Plug to TRB Plug Right Angle 1553 Cable Using 78 Ohm M17/176-00002 Coax PE3MP2166](#)



TRB Plug to TRB Plug Right Angle 1553 Cable
Using 78 Ohm M17/176-00002 Coax

RF Cable Assemblies Technical Data Sheet

PE3MP2166

Connectors

Description	Connector 1	Connector 2
Type	TRB Plug	TRB Plug Right Angle
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

Environmental Specifications

Temperature

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB Plug to TRB Plug Right Angle 1553 Cable Using 78 Ohm M17/176-00002 Coax PE3MP2166](#)



TRB Plug to TRB Plug Right Angle 1553 Cable
Using 78 Ohm M17/176-00002 Coax

RF Cable Assemblies Technical Data Sheet

PE3MP2166

How to Order

Part Number Configuration:

PE3MP2166

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3MP2166-12 = 12 inches long cable
PE3MP2166-100cm = 100 cm long cable

TRB Plug to TRB Plug Right Angle 1553 Cable Using 78 Ohm M17/176-00002 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB Plug to TRB Plug Right Angle 1553 Cable Using 78 Ohm M17/176-00002 Coax PE3MP2166](#)

URL: <https://www.pasternack.com/trb-plug-to-trb-plug-1553-cable-using-m17-176-00002-pe3mp2166-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

TRB Plug to TRB Plug Right Angle 1553 Cable Using 78 Ohm M17/176-00002 Coax

