



78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief
2-Slot TRB Solder/Clamp Plug for M17/176-00002 60" Cable

RF Cable Assemblies Technical Data Sheet

PE3MP2232-60

Configuration

- Connector 1: TRB Plug
- Connector 2: TRB Plug
- Cable Type: M17/176-00002
- Coax Flex Type: Flexible

Features

- Max Frequency 10 MHz
- PFA Jacket
- MIL-STD-1553
- -55°C to +200°C
- 78 ohms

Applications

- General Purpose
- Laboratory Use
- Vehicle High Temperature
- Data
- MIL-STD-1553

Description

Pasternack's PE3MP2232-60 78 ohm TRB plug to 78 ohm TRB plug 60 inch cable using 78 ohm M17/176-00002 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to TRB cable assembly has a plug to plug gender configuration with 78 ohm flexible M17/176-00002 twinax. The PE3MP2232-60 TRB plug to TRB plug cable assembly operates to 10 MHz. The PE3MP2232 cable assembly consists of a Bend Relief 3-slot solder/clamp TRB plug to a Bend Relief 2-slot solder/clamp TRB plug on M17/176-00002 Twinax cable, that is in the High Temperature-rated bus cabling category for MIL-STD-1553 applications. This thicker cable (0.129" O.D.) provides a robust cabling solution with less attenuation per foot. These cable assemblies come with a 1.700" steel spring-style bend relief that helps to minimize cable damage when exceeding the cables minimum bend radius. These assemblies are built to withstand severe shocks and vibrations.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 Twinax \(.129 O.D.\) 60" Cable PE3MP2232-60](#)



78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief
2-Slot TRB Solder/Clamp Plug for M17/176-00002 60" Cable

RF Cable Assemblies Technical Data Sheet

PE3MP2232-60

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		10	MHz
Capacitance		24 [78.74]		pF/ft [pF/m]
Operating Voltage (AC)			750,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	1	3	5	7	10	MHz
Insertion Loss (Typ.)	0.27	0.305	0.34	0.375	0.425	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Length*	60 in [152.4 cm]
Weight	0.36603 lbs [166.03 g]

Cable

Cable Type	M17/176-00002
Impedance	78 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PTFE
Shield Layer 1	Silver Plated Copper
Jacket Material	PFA, Blue

One Time Minimum Bend Radius	1.5 in [38.1 mm]
------------------------------	------------------

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 Twinax \(.129 O.D.\) 60" Cable PE3MP2232-60](#)



78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief
2-Slot TRB Solder/Clamp Plug for M17/176-00002 60" Cable

RF Cable Assemblies Technical Data Sheet

PE3MP2232-60

Connectors

Description	Connector 1	Connector 2
Type	TRB Plug	TRB Plug
Impedance	78 Ohms	78 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

Environmental Specifications

Temperature

Operating Range -55 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 Twinax \(.129 O.D.\) 60" Cable PE3MP2232-60](#)



78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 60" Cable

RF Cable Assemblies Technical Data Sheet

PE3MP2232-60

How to Order

Part Number Configuration:

PE3MP2232

- **xx**

uu

Unit of Measure:
 cm = Centimeters
 <blank> = Inches
 Length
 Base Number

Example: PE3MP2232-12 = 12 inches long cable
 PE3MP2232-100cm = 100 cm long cable

78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 60" Cable from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief 2-Slot TRB Solder/Clamp Plug for M17/176-00002 Twinax \(.129 O.D.\) 60" Cable PE3MP2232-60](#)

URL: <https://www.pasternack.com/trb-plug-to-trb-plug-1553-cable-60-inch-length-using-m17-176-00002-pe3mp2232-60-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3MP2232-60 CAD Drawing

78 Ohm Bend Relief 3-Slot TRB Solder/Clamp Plug to Bend Relief
2-Slot TRB Solder/Clamp Plug for M17/176-00002 60" Cable



ITEM NUMBER	LENGTH	
	FEET	METERS
PE3MP2232-12	1.0	.31
PE3MP2232-24	2.0	.61
PE3MP2232-36	3.0	.92
PE3MP2232-48	4.0	1.22
PE3MP2232-60	5.0	1.52

ZONE	REV	DESCRIPTION	DATE	CHANGED BY	APPROVED
	A	INITIAL RELEASE	5/24/2023	DMAY	EKIM

PE PASTERNAK
an INFINITO brand

Website: www.Pasternack.com
Phone: 1.866.727.8376 | 1.949.261.1920

INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5

SCALE: NONE SHEET: 1 OF 1

DESCRIPTION: 3SLT-2SLT TWINAX W/BEND RELIEF

SIZE: A	CAGE CODE: 53919	DRAWN BY: DMAY	ITEM NO.: PE3MP2232
---------	------------------	----------------	---------------------

UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE INCHES DIMENSIONS IN [] ARE MILLIMETERS

X = ±.2 [.5] FRACTIONS ±.02 [.5] ±.1/32
 .XX = ±.005 [.13] ANGLES ± 1°

CABLE LENGTH TOLERANCES:
 ≤12 [305] = +1 [25] / -0
 >12 [305] ≤ 60 [1524] = +2 [51] / -0
 >60 [1524] ≤ 120 [3048] = +4 [102] / -0
 >120 [3048] ≤ 300 [7620] = +6 [152] / -0
 >300 [7620] = +5% / -0

ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.

- NOTES:**
- CABLE ASSEMBLY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED, LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6 INCHES FROM EACH CONNECTOR.
 - CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.