



100 Ohm 3-Slot TRB Solder/Clamp Plug
to Plug for 0024A0024-9X Cable

RF Cable Assemblies Technical Data Sheet

PE3MP5771

Configuration

- Connector 1: TRB Plug
- Connector 2: TRB Plug
- Cable Type: 0024A0024-9X
- Coax Flex Type: Flexible

• Features

- Max Frequency 400 MHz
- Modified FEP Jacket
- MIL-STD-1553
- -65°C to +200°C
- 100 ohms

Applications

- General Purpose
- Laboratory Use
- High Temperature
- MIL-STD-1553
- Data

Description

Pasternack's PE3MP5771 100 ohm TRB plug to 100 ohm TRB plug cable using 100 ohm 0024A0024-9X twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB to TRB cable assembly has a plug to plug gender configuration with 100 ohm flexible 0024A0024-9X twinax. The PE3MP5771 TRB plug to TRB plug cable assembly operates to 400 MHz. The PE3MP5771 cable assembly consists of a 100 Ohm 3-Slot TRB Solder/Clamp Plug to 3-Slot TRB Solder/Clamp Plug for 0024A0024-9X Shielded Twisted Pair cable, that is suitable for high temperature applications..

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [100 Ohm 3-Slot TRB Solder/Clamp Plug to Plug for 0024A0024-9X Shielded Twisted Pair \(.149 O.D.\) Cable PE3MP5771](#)



100 Ohm 3-Slot TRB Solder/Clamp Plug
to Plug for 0024A0024-9X Cable

RF Cable Assemblies Technical Data Sheet

PE3MP5771

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		400	MHz
Capacitance		13.5 [44.29]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	400	MHz
Insertion Loss (Typ.)	0.012	0.028	0.041	0.064	0.102	dB/ft
	0.04	0.09	0.13	0.21	0.33	dB/m

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax and connectors used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1 dB per connector.

Mechanical Specifications

Cable Assembly

Weight 0.25 lbs [113.4 g]

Cable

Cable Type 0024A0024-9X
Impedance 100 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper, Silver
Dielectric Type Rayfoam H
Shield Layer 1 Silver Plated Copper
Jacket Material Modified FEP, White

One Time Minimum Bend Radius 1.788 in [45.42 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [100 Ohm 3-Slot TRB Solder/Clamp Plug to Plug for 0024A0024-9X Shielded Twisted Pair \(.149 O.D.\) Cable PE3MP5771](#)



100 Ohm 3-Slot TRB Solder/Clamp Plug
to Plug for 0024A0024-9X Cable

RF Cable Assemblies Technical Data Sheet

PE3MP5771

Connectors

Description	Connector 1	Connector 2
Type	TRB Plug	TRB Plug
Impedance	100 Ohms	100 Ohms
Contact Material and Plating	Bronze, Gold 30 micro inches	Bronze, Gold 30 micro inches
Contact Plating Specification	ASTM-B-488	ASTM-B-488
Dielectric Type	Teflon	Teflon
Outer Conductor Material and Plating	Phosphor Bronze, Gold	Phosphor Bronze, Gold
Outer Conductor Plating Specification	30 micro inches	30 micro inches
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	ASTM-B-733	ASTM-B-733

Environmental Specifications

Temperature

Operating Range -65 to +200 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [100 Ohm 3-Slot TRB Solder/Clamp Plug to Plug for 0024A0024-9X Shielded Twisted Pair \(.149 O.D.\) Cable PE3MP5771](#)



100 Ohm 3-Slot TRB Solder/Clamp Plug to Plug for 0024A0024-9X Cable

RF Cable Assemblies Technical Data Sheet

PE3MP5771

How to Order

Part Number Configuration:

PE3MP5771

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3MP5771-12 = 12 inches long cable
PE3MP5771-100cm = 100 cm long cable

100 Ohm 3-Slot TRB Solder/Clamp Plug to Plug for 0024A0024-9X Cable from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [100 Ohm 3-Slot TRB Solder/Clamp Plug to Plug for 0024A0024-9X Shielded Twisted Pair \(.149 O.D.\) Cable PE3MP5771](#)

URL: <https://www.pasternack.com/trb-plug-to-trb-plug-1553-cable-using-0024a0024-9x-pe3mp5771-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

