



RF Cable Assemblies Technical Data Sheet

PE3W00020-100CM


Configuration

Connector 1: N Male Right AngleConnector 2: TNC Male Right Angle

• Cable Type: LMR-195

Features

- Max Frequency 3 GHz
- Shielding Effectivity > 90 dB
- 80% Phase Velocity
- · Double Shielded
- PE Jacket



Applications

· General Purpose

· Laboratory Use

Description

Pasternack's PE3W00020-100CM type N male right angle to TNC male right angle low loss 100 cm cable using LMR-195 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to TNC cable assembly has a male to male gender configuration with 50 ohm flexible LMR-195 coax. The PE3W00020-100CM type N male to TNC male cable assembly operates to 3 GHz. The right angle type N and right angle TNC interfaces on the LMR-195 cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male Right Angle to TNC Male Right Angle Low Loss Cable 100 cm Length Using LMR-195 Coax PE3W00020-100CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3W00020-100CM

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR		7,55	1.4:1	
Velocity of Propagation		80		%
RF Shielding	90			dB
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.6 [24.93]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ω/1000ft [Ω/Km]
Jacket Spark			3,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.1	0.25	0.5	1	3	GHz
Insertion Loss (Max.)	0.52	0.6	0.67	0.76	1	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax cable used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.1dB per connector

Mechanical Specifications

Cable Assembly

Length* 39.37 in [100 cm]
Diameter 0.8 in [20.32 mm]

Cable

Cable TypeLMR-195Impedance50 OhmsInner Conductor TypeSolidInner Conductor Material and PlatingCopperDielectric TypePE (F)Number of Shields2

Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male Right Angle to TNC Male Right Angle Low Loss Cable 100 cm Length Using LMR-195 Coax PE3W00020-100CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3W00020-100CM

Jacket Material

PE, Black Jacket Diameter 0.195 in [4.95 mm]

One Time Minimum Bend Radius Repeated Minimum Bend Radius **Bending Moment**

Flat Plate Crush Tensile Strength 0.5 in [12.7 mm] 2 in [50.8 mm] 0.2 lbs-ft [0.27 N-m] 15 lbs/in [0.27 Kg/mm] 40 lbs [18.14 Kg]

Connectors

Description	Connector 1	Connector 2 TNC Male Right Angle	
Туре	N Male Right Angle		
Specification		MIL-STD-348A	
Impedance	50 Ohms	50 Ohms	
Mating Cycles	500		
Contact Material and Plating	Brass, Gold	Brass, Gold	
Contact Plating Specification	50μ in. minimum	30μ in. minimum	
Dielectric Type	Teflon	Teflon	
Body Material and Plating	Brass, Tri-Metal	Brass, Nickel	
Body Plating Specification	80μ in. minimum	100μ in. minimum	
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Nickel	
Coupling Nut Plating Specification	80µ in. minimum	100µ in. minimum	

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male Right Angle to TNC Male Right Angle Low Loss Cable 100 cm Length Using LMR-195 Coax PE3W00020-100CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • Fax: (949) 261-7451

^{*}All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.







RF Cable Assemblies Technical Data Sheet

PE3W00020-100CM

Typical Performance Data





Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male Right Angle to TNC Male Right Angle Low Loss Cable 100 cm Length Using LMR-195 Coax PE3W00020-100CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3W00020-100CM

How to Order



Example: PE3W00020-12 = 12 inches long cable PE3W00020-100cm = 100 cm long cable

N Male Right Angle to TNC Male Right Angle Low Loss Cable 100 cm Length Using LMR-195 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: N Male Right Angle to TNC Male Right Angle Low Loss Cable 100 cm Length Using LMR-195 Coax PE3W00020-100CM

URL: https://www.pasternack.com/n-male-tnc-male-lmr195-cable-assembly-pe3w00020-100cm-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE3W00020-100CM CAD DrawingN Male Right Angle to TNC Male Right Angle Low Loss Cable 100 cm Length Using LMR-195 Coax

