



SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax

TECHNICAL DATA SHEET


PE3W00112

Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: TNC Female Bulkhead
- Cable Type: LMR-100A
- Coax Flex Type: Flexible

Features

- Max Frequency 3 GHz
- Shielding Effectivity > 90 dB
- 66% Phase Velocity
- Double Shielded
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W00112 SMA male right angle to TNC female bulkhead cable using LMR-100 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to TNC cable assembly has a male to female gender configuration with 50 ohm flexible LMR-100A coax. The PE3W00112 SMA male to TNC female cable assembly operates to 3 GHz. The right angle SMA interface on the LMR-100A cable allows for easier connections in tight spaces. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax PE3W00112](#)



SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax

TECHNICAL DATA SHEET

PE3W00112

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		3	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
RF Shielding	90			dB
Group Delay		1.54 [5.05]		ns/ft [ns/m]
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Inductance		0.077 [0.25]		uH/ft [uH/m]
DC Resistance Inner Conductor		81 [265.75]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		9.5 [31.17]		Ω/1000ft [Ω/Km]
Jacket Spark			2,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	100	250	500	1000	3000	MHz	
PE3W00112	Custom Lengths Available	Insertion Loss (Typ.)	0.06	0.12	0.17	0.24	0.43	dB/ft	
			0.21	0.38	0.55	0.79	1.42	dB/m	
PE3W00112-24	24 inch	Insertion Loss (Typ.)	0.43	0.53	0.63	0.78	1.17	dB	0.073
PE3W00112-36	36 inch	Insertion Loss (Typ.)	0.5	0.65	0.8	1.02	1.6	dB	0.082
PE3W00112-48	48 inch	Insertion Loss (Typ.)	0.56	0.76	0.96	1.26	2.03	dB	0.091
PE3W00112-100CM	100 cm	Insertion Loss (Typ.)	0.51	0.68	0.85	1.09	1.72	dB	0.085
PE3W00112-200CM	200 cm	Insertion Loss (Typ.)	0.72	1.06	1.39	1.88	3.14	dB	0.115

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB
Loss due to Connector 2: 0.2 dB
Base Weight: 0.064 pounds
Additional Weight per Inch: 0.00075 pounds

Mechanical Specifications

Cable Assembly

Weight 0.064 lbs [29.03 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax PE3W00112](#)



SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax

TECHNICAL DATA SHEET

PE3W00112

Cable

Cable Type	LMR-100A
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Steel
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.11 in [2.79 mm]

One Time Minimum Bend Radius	0.25 in [6.35 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]
Bending Moment	0.1 lbs-ft [0.14 N-m]
Flat Plate Crush	10 lbs/in [0.18 Kg/mm]
Tensile Strength	15 lbs [6.8 Kg]

Connectors

Description	Connector 1	Connector 2
Type	SMA Male Right Angle Threaded	TNC Female Bulkhead Threaded
Specification	MIL-STD-348A	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	50 μ in minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 μ in minimum	
Hex Size	5/16 in	5/8 in
Torque	5 in-lbs [0.57 Nm]	

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax PE3W00112](#)



SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax

TECHNICAL DATA SHEET

PE3W00112


Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

How to Order

Part Number Configuration:



Example: PE3W00112-12 = 12 inches long cable
PE3W00112-100cm = 100 cm long cable

SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax PE3W00112](#)

URL: <https://www.pasternack.com/sma-male-right-angle-to-tnc-female-bulkhead-low-loss-cable-using-lmr-100-pe3w00112-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W00112 CAD Drawing

SMA Male Right Angle to TNC Female Bulkhead Low Loss Cable Using LMR-100 Coax

