



TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable
Using 124 Ohm TWC-124-2 Coax

RF Cable Assemblies Technical Data Sheet

PE3MSA00651

Configuration

- Connector 1: TRB 3-Slot Plug
- Connector 2: Blunt Cut Genderless
- Cable Type: TWC-124-2
- Coax Flex Type: Flexible

Features

- Max Frequency 500 MHz
- PVC Jacket
- 124 ohms
- Twinaxial
- MIL-STD-1553B
- -40°C to +80°C
- Lead Free Solder
- Standard and Custom Lengths Available

Applications

- General Purpose
- Laboratory Use
- MIL-STD-1553B Applications
- Data Transmission

Description

Pasternack's PE3MSA00651 78 ohm TRB 3-Slot plug to Blunt cut genderless cable using 124 ohm TWC-124-2 twinax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TRB 3-Slot to Blunt Cut cable assembly has a plug to genderless gender configuration with 124 ohm flexible TWC-124-2 twinax. The PE3MSA00651 TRB 3-Slot plug to Blunt cut genderless cable assembly operates to 500 MHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable Using 124 Ohm TWC-124-2 Coax PE3MSA00651](#)



TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable
Using 124 Ohm TWC-124-2 Coax

RF Cable Assemblies Technical Data Sheet

PE3MSA00651

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		500	MHz
Capacitance		12.3 [40.35]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	10	50	100	200	500	MHz

Mechanical Specifications

Cable Assembly

Weight 0.13 lbs [58.97 g]

Cable

Cable Type TWC-124-2
Impedance 124 Ohms
Inner Conductor Type Stranded
Inner Conductor Material and Plating Copper, Silver
Dielectric Type PE
Shield Layer 1 Silver Plated Copper
Jacket Material PVC, Blue

One Time Minimum Bend Radius 1.25 in [31.75 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable Using 124 Ohm TWC-124-2 Coax PE3MSA00651](#)



TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable
Using 124 Ohm TWC-124-2 Coax

RF Cable Assemblies Technical Data Sheet

PE3MSA00651

Connectors

Description	Connector 1	Connector 2
Type	TRB 3-Slot Plug Bayonet	Blunt Cut Genderless Other
Specification	MIL-STD-1553	
Impedance	78 Ohms	
Contact Material and Plating	Bronze, Gold 30 micro inches	
Contact Plating Specification	ASTM-B-488	
Dielectric Type	Teflon	
Outer Conductor Material and Plating	Phosphor Bronze, Gold	
Outer Conductor Plating Specification	30 micro inches	
Body Material and Plating	Brass, Nickel	
Body Plating Specification	ASTM-B-733	
Seal Gasket Material	Rubber	

Environmental Specifications

Temperature

Operating Range

-40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable Using 124 Ohm TWC-124-2 Coax PE3MSA00651](#)



TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable Using 124 Ohm TWC-124-2 Coax

RF Cable Assemblies Technical Data Sheet

PE3MSA00651

How to Order

Part Number Configuration:

PE3MSA00651

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3MSA00651-12 = 12 inches long cable
PE3MSA00651-100cm = 100 cm long cable

TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable Using 124 Ohm TWC-124-2 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TRB 3-Slot Plug to Blunt Cut Genderless 1553 Cable Using 124 Ohm TWC-124-2 Coax PE3MSA00651](https://www.pasternack.com/trb-3-slot-plug-to-blunt-cut-genderless-1553-cable-using-twc-124-2-pe3msa00651-p.aspx)

URL: <https://www.pasternack.com/trb-3-slot-plug-to-blunt-cut-genderless-1553-cable-using-twc-124-2-pe3msa00651-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

