

## Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink



### RF Cable Assemblies Technical Data Sheet


**PE3W01868/HS**

#### Configuration

- Connector 1: TNC Plug Reverse Polarity
- Connector 2: N Male
- Cable Type: LMR-400-UF

#### Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- Double Shielded
- TPE Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W01868/HS reverse polarity TNC plug to type N male cable using LMR-400-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack reverse polarity TNC to type N cable assembly has a plug to male gender configuration with 50 ohm flexible LMR-400-UF coax. The PE3W01868/HS reverse polarity TNC plug to type N male cable assembly operates to 5.8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR-400-UF Coax with Heat-Shrink PE3W01868/HS](#)



## Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet

**PE3W01868/HS**

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.07 [3.51]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		1.65 [5.41]		Ω/1000ft [Ω/Km]
Jacket Spark			8,000	Vrms

#### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.023	0.034	0.049	0.081	0.13	dB/ft
	0.08	0.11	0.16	0.27	0.43	dB/m

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

#### Mechanical Specifications

##### Cable Assembly

Weight 0.219 lbs [99.34 g]

##### Cable

Cable Type LMR-400-UF  
Impedance 50 Ohms  
Inner Conductor Type Stranded  
Inner Conductor Material and Plating Copper  
Dielectric Type PE (F)  
Number of Shields 2  
Shield Layer 1 Aluminum Tape  
Shield Layer 2 Tinned Copper Braid  
Jacket Material TPE, Black  
Jacket Diameter 0.405 in [10.29 mm]

One Time Minimum Bend Radius 1 in [25.4 mm]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR-400-UF Coax with Heat-Shrink PE3W01868/HS](#)



## Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink

### RF Cable Assemblies Technical Data Sheet

**PE3W01868/HS**

Repeated Minimum Bend Radius  
Bending Moment  
Flat Plate Crush  
Tensile Strength

4 in [101.6 mm]  
0.38 lbs-ft [0.52 N-m]  
20 lbs/in [0.36 Kg/mm]  
160 lbs [72.57 Kg]

#### Connectors

Description	Connector 1	Connector 2
Type	TNC Plug Reverse Polarity	N Male
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Phosphor Bronze, Gold	Brass, Gold
Contact Plating Specification		15 $\mu$ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Nickel	Brass, Tri-Metal
Hex Size		18 mm

#### Environmental Specifications

##### Temperature

Operating Range

-40 to +85 deg C

#### Compliance Certifications (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR-400-UF Coax with Heat-Shrink PE3W01868/HS](#)

Reverse Polarity TNC Plug to N Male Low Loss Cable  
Using LMR-400-UF Coax with HeatShrink




**RF Cable Assemblies Technical Data Sheet**

**PE3W01868/HS**

**How to Order**

Part Number Configuration:



Example: PE3W01868/HS-12 = 12 inches long cable  
PE3W01868/HS-100cm = 100 cm long cable

Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR-400-UF Coax with HeatShrink PE3W01868/HS](#)

URL: <https://www.pasternack.com/reverse-polarity-tnc-plug-to-n-male-low-loss-cable-using-lmr-400-uf-with-heatshrink-pe3w01868-hs-p.aspx>


The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W01868/HS CAD Drawing

## Reverse Polarity TNC Plug to N Male Low Loss Cable

## Using LMR-400-UF Coax with HeatShrink

ZONE	REV.	DESCRIPTION	DATE	CHANGED BY	APPROVED BY
A		INITIAL RELEASE	01/27/2023	KDANG	AGANWANI



NOTES:

1. CABLE ASSY LENGTH LABEL PLACEMENT: 36 INCHES OR LESS, ONE LABEL APPROX CENTERED. LONGER THAN 36 INCHES, TWO LABELS APPROX 6 INCHES FROM EACH CONNECTOR.  
CABLES ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.
- 2.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. ALL USES OF THESE COMMODITIES, TECHNOLOGY OR SOFTWARE ARE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EMBARGO AND TRADE CONTROL LAWS OF THE UNITED STATES.

PE PASTERNACK® an INFINIT® brand		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5		REV A
		SCALE	SHEET 1 OF 1	
UNLESS OTHERWISE SPECIFIED LEADING DIMENSIONS ARE IN INCHES DIMENSIONS IN [ ] ARE MILLIMETERS				
TOLERANCES:				
$X = \pm 2$ [5]	FRACTIONS			
$XX = \pm 0.02$ [5]	$\pm 1/32$			
$XXX = \pm 0.005$ [13]	ANGLES $\pm 1^\circ$			
CABLE LENGTH TOLERANCES:				
$>12$ [305] $\leq$ $<12$ [305] $= \pm 1$ [25] / -0				
$>12$ [305] $\leq$ $<12$ [305] $= +2$ [51] / -0				
$>60$ [1524] $\leq$ $<60$ [1524] $= +4$ [102] / -0				
$>120$ [3048] $\leq$ $<120$ [3048] $= +6$ [152] / -0				
$>300$ [7620] $\leq$ $<300$ [7620] $= +5\%$ / -0				
ALL DIMENSIONS ARE FOR REFERENCE ONLY AND SUBJECT TO CHANGE WITHOUT NOTICE.				
SIZE A	CAGE CODE 53919	DRAWN BY KDANG	ITEM NO. PE3W01868/HS	
DESCRIPTION Reverse Polarity TNC Plug to N Male Low Loss Cable Using LMR- 400-UJ Coax with HeatShrink	Website: <a href="http://www.Pasternack.com">www.Pasternack.com</a>	Phone: 1.866.727.8376   1.949.261.1920		