

N Male to N Female Bulkhead Cable Using RG174 Coax with HeatShrink





PE3W02956/HS

Configuration

- Connector 1: N Male
- Connector 2: N Female Bulkhead
- Cable Type: RG174
- Coax Flex Type: Flexible

Features

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W02956/HS type N male to type N female bulkhead cable using RG174 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to type N cable assembly has a male to female gender configuration with 50 ohm flexible RG174 coax. The PE3W02956/HS type N male to type N female cable assembly operates to 1 GHz. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation	66			%
Capacitance	31.1 [102.03]			pF/ft [pF/m]

Specifications by Frequency

N Male to N Female Bulkhead Cable Using RG174 Coax with HeatShrink



PE3W02956/HS

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
		Frequency	100	250	500	1000	MHz	
PE3W02956/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.08	0.14	0.21	0.32	dB/ft	
			0.28	0.45	0.7	1.05	dB/m	
PE3W02956/HS-12	12 inch	Insertion Loss (Typ.)	0.29	0.34	0.42	0.52	dB	0.077
PE3W02956/HS-24	24 inch	Insertion Loss (Typ.)	0.37	0.48	0.63	0.84	dB	0.086
PE3W02956/HS-36	36 inch	Insertion Loss (Typ.)	0.46	0.62	0.84	1.16	dB	0.095
PE3W02956/HS-48	48 inch	Insertion Loss (Typ.)	0.54	0.75	1.05	1.48	dB	0.104
PE3W02956/HS-72	72 inch	Insertion Loss (Typ.)	0.71	1.03	1.47	2.12	dB	0.122

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.1 dB

Loss due to Connector 2: 0.1 dB

Base Weight: 0.077 pounds

Additional Weight per Inch: 0.00075 pounds

Mechanical Specifications

Cable Assembly

Weight 0.154 lbs [69.85 g]

Cable

Cable Type	RG174
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper Clad Steel, Silver
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Tinned Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.11 in [2.79 mm]

N Male to N Female Bulkhead Cable Using RG174 Coax with HeatShrink



PE3W02956/HS

Connectors

Description	Connector 1	Connector 2
Type	N Male	N Female Bulkhead
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	100 μ in minimum
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 μ in minimum	

Environmental Specifications

Operating Range Temperature

-40 to +80 deg C

Compliance Certifications

(see product page for current document)

Plotted and Other Data

Notes:

N Male to N Female Bulkhead Cable Using RG174 Coax with HeatShrink



PE3W02956/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3W02956/HS - xx uu

Legend:

- Unit of Measure:
cm = Centimeters
<blank> = Inches
- Length
- Base Number

Example: PE3W02956/HS-12 = 12 inches long cable
PE3W02956/HS-100cm = 100 cm long cable

N Male to N Female Bulkhead Cable Using RG174 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to N Female Bulkhead Cable Using RG174 Coax with HeatShrink PE3W02956/HS](#)

URL: <https://www.pasternack.com/n-male-to-n-female-bulkhead-cable-using-rg174-with-heatshrink-pe3w02956-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W02956/HS CAD Drawing

N Male to N Female Bulkhead Cable Using RG174 Coax with HeatShrink



NOTES:
1. C/A OF LC 61 C/A C/A DE

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODITIES, TECHNOLOGY OR SOFTWARE ARE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVISION CONTRARY TO U.S. LAW IS PROHIBITED.

© 2023 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.

+1 (866) 558-2786 | sales@pasternack.com | pasternack.com