



RF Cable Assemblies Technical Data Sheet


PE3W01661/HS-50CM

Configuration

Connector 1: SMA MaleConnector 2: N MaleCable Type: LMR-200

Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 83% Phase Velocity
- · Double Shielded
- PE Jacket



Applications

· General Purpose

· Laboratory Use

Description

Pasternack's PE3W01661/HS-50CM SMA male to type N male 50 cm cable using LMR-200 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-200 coax. The PE3W01661/HS-50CM SMA male to type N male cable assembly operates to 5.8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Male Cable 50 CM Length Using LMR-200 Coax with HeatShrink PE3W01661/HS-50CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451





RF Cable Assemblies Technical Data Sheet

PE3W01661/HS-50CM

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR		7,65	1.4:1	
Velocity of Propagation		83		%
RF Shielding	90			dB
Group Delay		1.22 [4]		ns/ft [ns/m]
Capacitance		24.5 [80.38]		pF/ft [pF/m]
Inductance		0.061 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		5.36 [17.59]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ω/1000ft [Ω/Km]
Jacket Spark			3,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.5	1	2	4	5.8	GHz
Insertion Loss (Max.)	0.32	0.37	0.45	0.55	0.63	dB

Electrical Specification Notes:

The Insertion Loss data above is based on the performance specifications of the coax used in this assembly. The Insertion Loss includes an estimated insertion loss of 0.2dB of connector loss.

Mechanical Specifications

Cable Assembly

Length* 19.69 in [500.13 mm]
Diameter 0.89 in [22.61 mm]

Cable

Cable TypeLMR-200Impedance50 OhmsInner Conductor TypeSolidInner Conductor Material and PlatingCopperDielectric TypePE (F)Number of Shields2

Shield Layer 1 Aluminum Tape
Shield Layer 2 Tinned Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Male Cable 50 CM Length Using LMR-200 Coax with HeatShrink PE3W01661/HS-50CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

Sales@Pasternack.com • Techsupport@Pasternack.com





RF Cable Assemblies Technical Data Sheet

PE3W01661/HS-50CM

Jacket Material

Jacket Diameter

One Time Minimum Bend Radius Repeated Minimum Bend Radius

Bending Moment Flat Plate Crush Tensile Strength 0.5 in [12.7 mm] 2 in [50.8 mm] 0.2 lbs-ft [0.27 N-m] 15 lbs/in [0.27 Kg/mm] 40 lbs [18.14 Kg]

0.195 in [4.95 mm]

PE, Black

Connectors

Description	Connector 1	Connector 2	
Туре	SMA Male	N Male	
Specification		MIL-STD-348	
Impedance	50 Ohms	50 Ohms	
Contact Material and Plating	Brass, Gold	Brass, Gold	
Dielectric Type	Teflon	PTFE	
Body Material and Plating	Brass, Gold	Brass, Tri-Metal	
Coupling Nut Material and Plating	Brass, Gold	Phosphor Bronze	
Hex Size	1/4 Inch	13/16 Inch	

Mechanical Specification Notes:

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Male Cable 50 CM Length Using LMR-200 Coax with HeatShrink PE3W01661/HS-50CM

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

^{*}All cable assemblies have a length tolerance of 1.5% or ± 3/8", whichever is greater.






RF Cable Assemblies Technical Data Sheet

PE3W01661/HS-50CM

Typical Performance Data



Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Male Cable 50 CM Length Using LMR-200 Coax with HeatShrink PE3W01661/HS-50CM





RF Cable Assemblies Technical Data Sheet

PE3W01661/HS-50CM

How to Order

Part Number Configuration:

PE3W01661/HS - xx uu

Unit of Measure:
cm = Centimeters

Length
Base Number

Example: PE3W01661/HS-12 = 12 inches long cable PE3W01661/HS-100cm = 100 cm long cable

SMA Male to N Male Cable 50 CM Length Using LMR-200 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: SMA Male to N Male Cable 50 CM Length Using LMR-200 Coax with HeatShrink PE3W01661/HS-50CM

URL: https://www.pasternack.com/sma-male-n-male-lmr200-cable-assembly-pe3w01661-hs-50cm-p.aspx

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

Pasternack Enterprises, Inc. • P.O. Box 16759, Irvine, CA 92623 **Phone:** (866) 727-8376 or (949) 261-1920 • **Fax:** (949) 261-7451

PE3W01661/HS-50CM CAD Drawing
SMA Male to N Male Cable 50 CM Length Using LMR-200 Coax with HeatShrink

