

## UHF Male to N Female Bulkhead Low Loss Cable Using LMR-195 Coax with HeatShrink




### PE3W03867/HS

#### Configuration

- Connector 1: UHF Male
- Connector 2: N Female Bulkhead
- Cable Type: LMR-195
- Coax Flex Type: Flexible

#### Features

- Max Frequency 300 MHz
- Shielding Effectivity > 90 dB
- 80% Phase Velocity
- Double Shielded
- PE Jacket



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W03867/HS UHF male to type N female bulkhead cable using LMR-195 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack UHF to type N cable assembly has a male to female gender configuration with 50 ohm flexible LMR-195 coax. The PE3W03867/HS UHF male to type N female cable assembly operates to 300 MHz. Our RF cable assembly with type N bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		300	GHz
VSWR			1.4:1	
Velocity of Propagation		80		%
RF Shielding	90			dB
Group Delay		1.27 [4.17]		ns/ft [ns/m]
Capacitance		25.4 [83.33]		pF/ft [pF/m]
Inductance		0.064 [0.21]		uH/ft [uH/m]
DC Resistance Inner Conductor		7.6 [24.93]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		4.9 [16.08]		Ohms/1000ft [Ohms/Km]

## UHF Male to N Female Bulkhead Low Loss Cable Using LMR-195 Coax with HeatShrink



### PE3W03867/HS

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			3,000	Vrms

#### Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
			Frequency				MHz	
PE3W03867/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.025	0.035	0.057	0.062	dB/ft	
			0.09	0.12	0.19	0.21	dB/m	
PE3W03867/HS-12	12 In	Insertion Loss (Typ.)	0.23	0.24	0.26	0.27	dB	0.152
PE3W03867/HS-24	24 In	Insertion Loss (Typ.)	0.25	0.27	0.32	0.33	dB	0.175
PE3W03867/HS-36	36 In	Insertion Loss (Typ.)	0.28	0.31	0.38	0.39	dB	0.197
PE3W03867/HS-48	48 In	Insertion Loss (Typ.)	0.3	0.34	0.43	0.45	dB	0.219
PE3W03867/HS-60	60 In	Insertion Loss (Typ.)	0.33	0.38	0.49	0.51	dB	0.241

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.152 pounds
Additional Weight per Inch:	0.00184 pounds

#### Mechanical Specifications

##### Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.15 lbs [68.04 g]

##### Cable

Cable Type	LMR-195
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]
One Time Minimum Bend Radius	0.5 in [12.7 mm]
Repeated Minimum Bend Radius	2 in [50.8 mm]
Bending Moment	0.2 lbs-ft [0.27 N-m]
Flat Plate Crush	15 lbs/in [0.27 Kg/mm]
Tensile Strength	40 lbs [18.14 Kg]

UHF Male to N Female Bulkhead Low Loss Cable  
Using LMR-195 Coax with HeatShrink



**PE3W03867/HS**

**Connectors**

Description	Connector 1	Connector 2
Type	UHF Male	N Female Bulkhead
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Phosphor Bronze, Gold
Contact Plating Specification	30 µin minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Tri-Metal
Body Plating Specification	100 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	

**Environmental Specifications**

Operating Range Temperature -40 to +85 deg C

**Compliance Certifications** (see [product page](#) for current document)

**Plotted and Other Data**

Notes:

## UHF Male to N Female Bulkhead Low Loss Cable Using LMR-195 Coax with HeatShrink




### PE3W03867/HS

#### Typical Performance Data

#### How to Order

Part Number Configuration:



Example: PE3W03867/HS-12 = 12 inches long cable  
PE3W03867/HS-100cm = 100 cm long cable

UHF Male to N Female Bulkhead Low Loss Cable Using LMR-195 Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [UHF Male to N Female Bulkhead Low Loss Cable Using LMR-195 Coax with HeatShrink PE3W03867/HS](#)

URL: <https://www.pasternack.com/uhf-male-to-n-female-bulkhead-low-loss-cable-using-lmr-195-with-heatshrink-pe3w03867-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

