

SMA Male to N Male Low Loss Cable Using LMR-400-DB Coax with HeatShrink




PE3W01979/HS

Configuration

- Connector 1: SMA Male
- Connector 2: N Male
- Cable Type: LMR-400-DB
- Coax Flex Type: Flexible

Features

- Max Frequency 8 GHz
- Shielding Effectivity > 90 dB
- 85% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W01979/HS SMA male to type N male cable using LMR-400-DB coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-400-DB coax. The PE3W01979/HS SMA male to type N male cable assembly operates to 8 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		8	GHz
VSWR			1.4:1	
Velocity of Propagation		85		%
RF Shielding	90			dB
Group Delay		1.2 [3.94]		ns/ft [ns/m]
Capacitance		23.9 [78.41]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		1.39 [4.56]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		1.65 [5.41]		Ohms/1000ft [Ohms/Km]

SMA Male to N Male Low Loss Cable Using LMR-400-DB Coax with HeatShrink



PE3W01979/HS

Electrical Specifications

Description	Minimum	Typical					Maximum	Units
Jacket Spark						8,000		Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	500	1000	2000	4000	8000	MHz	
PE3W01979/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.028	0.041	0.06	0.079	0.108	dB/ft	
			0.1	0.14	0.2	0.26	0.36	dB/m	
PE3W01979/HS-12	12 inch	Insertion Loss (Typ.)	0.23	0.25	0.26	0.28	0.31	dB	0.215
PE3W01979/HS-24	24 inch	Insertion Loss (Typ.)	0.26	0.29	0.32	0.36	0.42	dB	0.286
PE3W01979/HS-36	36 inch	Insertion Loss (Typ.)	0.29	0.33	0.38	0.44	0.53	dB	0.356
PE3W01979/HS-48	48 inch	Insertion Loss (Typ.)	0.32	0.37	0.44	0.52	0.64	dB	0.426
PE3W01979/HS-60	60 inch	Insertion Loss (Typ.)	0.34	0.41	0.5	0.6	0.74	dB	0.496

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.215 pounds
Additional Weight per Inch:	0.00584 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.145 lbs [65.77 g]

Cable

Cable Type	LMR-400-DB
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper Clad Aluminum
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.405 in [10.29 mm]
One Time Minimum Bend Radius	1 in [25.4 mm]
Repeated Minimum Bend Radius	4 in [101.6 mm]
Bending Moment	0.5 lbs·ft [0.68 N·m]
Flat Plate Crush	40 lbs/in [0.71 Kg/mm]
Tensile Strength	160 lbs [72.57 Kg]

SMA Male to N Male Low Loss Cable Using LMR-400-DB Coax with HeatShrink



PE3W01979/HS

Connectors

Description	Connector 1	Connector 2
Type	SMA Male	N Male
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification		15 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Gold	Brass, Tri-Metal
Coupling Nut Material and Plating	Brass, Gold	Brass, Tri-Metal
Hex Size	5/16 inch	18 mm
Torque	3 in-lbs 0.34 Nm	

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications

(see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male to N Male Low Loss Cable Using LMR-400-DB Coax with HeatShrink



PE3W01979/HS

Typical Performance Data

How to Order

Part Number Configuration:

PE3W01979/HS - xx uu

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3W01979/HS-12 = 12 inches long cable
PE3W01979/HS-100cm = 100 cm long cable

SMA Male to N Male Low Loss Cable Using LMR-400-DB Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to N Male Low Loss Cable Using LMR-400-DB Coax with HeatShrink PE3W01979/HS](#)

URL: <https://www.pasternack.com/sma-male-to-n-male-low-loss-cable-using-lmr-400-db-with-heatshrink-pe3w01979-hs-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W01979/HS CAD Drawing

SMA Male to N Male Low Loss Cable Using LMR-400-DB Coax with HeatShrink



NOTE

1. CABLE ASSEMBLY LENGTH LABEL PLACEMENT:
 36 INCHES OR LESS, ONE LABEL APPROXIMATELY CENTERED.
 LONGER THAN 36 INCHES, TWO LABELS APPROXIMATELY 6
 INCHES FROM EACH CONNECTOR.

2. CABLE ASSEMBLIES SHALL BE TESTED FOR CONTINUITY.

3. CABLE ASSEMBLY LENGTH DETERMINED BY ITEM PN AND
 DESCRIPTION.

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF INFINITE ELECTRONICS, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF INFINITE ELECTRONICS, INC. IS PROHIBITED. THESE COMMODIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW PROHIBITED.

COAX WITH HEATSHRINK			
ITEM NO.	DRAWING BY	CAGE CODE	SIZE
PE3W01979/HS	KGLEBOVA	53919	A
1			
2			
3			

© 2025 Infinite Electronics, Inc. Pasternack is a registered trademark of Infinite Electronics, Inc.

+1 (866) 558-2786 | sales@pasternack.com | pasternack.com