



TNC Female Right Angle Bulkhead to SMA Male Low Loss Cable Using PE-C200 Coax

TECHNICAL DATA SHEET


PE3W04333

Configuration

- Connector 1: TNC Female Right Angle Bulkhead
- Connector 2: SMA Male
- Cable Type: PE-C200
- Coax Flex Type: Flexible

Features

- Shielding Effectivity > 90 dB
- 83% Phase Velocity
- Double Shielded
- PE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W04333 TNC female right angle bulkhead to SMA male cable using PE-C200 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to SMA cable assembly has a female to male gender configuration with 50 ohm flexible PE-C200 coax. The right angle TNC interface on the PE-C200 cable allows for easier connections in tight spaces. Our RF cable assembly with TNC bulkhead interface allows designers to create external connections on their product enclosures, and can be used in a variety of other rack mount and panel mount applications. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		83		%
RF Shielding	90			dB
Capacitance		24.5 [80.38]		pF/ft [pF/m]
Jacket Spark			3,000	Vrms

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Female Right Angle Bulkhead to SMA Male Low Loss Cable Using PE-C200 Coax PE3W04333](#)



TNC Female Right Angle Bulkhead to SMA Male Low Loss Cable Using PE-C200 Coax

TECHNICAL DATA SHEET

PE3W04333

Mechanical Specifications

Cable Assembly

Weight 0.119 lbs [53.98 g]

Cable

Cable Type	PE-C200
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	PE, Black
Jacket Diameter	0.195 in [4.95 mm]

Connectors

Description	Connector 1	Connector 2
Type	TNC Female Right Angle Bulkhead Threaded	SMA Male Threaded
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	
Dielectric Type	PTFE	PTFE
Outer Conductor Material and Plating	Brass, Nickel	
Body Material and Plating	Brass, Nickel	Brass, Gold
Body Plating Specification	100 µin minimum	
Coupling Nut Material and Plating		Brass, Gold
Hex Size		5/16 Inch

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Female Right Angle Bulkhead to SMA Male Low Loss Cable Using PE-C200 Coax PE3W04333](#)



TNC Female Right Angle Bulkhead to SMA Male Low Loss Cable Using PE-C200 Coax

TECHNICAL DATA SHEET

PE3W04333

How to Order

Part Number Configuration:

PE3W04333

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W04333-12 = 12 inches long cable
PE3W04333-100cm = 100 cm long cable

TNC Female Right Angle Bulkhead to SMA Male Low Loss Cable Using PE-C200 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Female Right Angle Bulkhead to SMA Male Low Loss Cable Using PE-C200 Coax PE3W04333](https://www.pasternack.com/tnc-female-right-angle-bulkhead-to-sma-male-low-loss-cable-using-pe-c200-pe3w04333)

URL: <https://www.pasternack.com/tnc-female-right-angle-bulkhead-to-sma-male-low-loss-cable-using-pe-c200-pe3w04333-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

