

SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax with Times Microwave Components with 270 Deg. Clock

PE3W02628/SP




Configuration

- Connector 1: SMA Male Right Angle
- Connector 2: SMA Male Right Angle
- Cable Type: LMR-240-UF
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- TPE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W02628/SP SMA male right angle to SMA male right angle cable using LMR-240-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to SMA cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240-UF coax. The PE3W02628/SP SMA male to SMA male cable assembly operates to 6 GHz. The right angle SMA interfaces on the LMR-240-UF cable allow for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		4.28 [14.04]		Ohms/1000ft [Ohms/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ohms/1000ft [Ohms/Km]

SMA Male Right Angle to SMA Male Right Angle Low
Loss Cable Using LMR-240-UF Coax with Times
Microwave Components with 270 Deg. Clock



PE3W02628/SP

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Jacket Spark			5,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000	MHz	
PE3W02628/SP	Custom Lengths Available	Insertion Loss (Typ.)	0.046	0.066	0.096	0.155	0.244	dB/ft	
			0.16	0.22	0.32	0.51	0.81	dB/m	
PE3W02628/SP-12	12 inch	Insertion Loss (Typ.)	0.55	0.57	0.6	0.66	0.75	dB	0.074
PE3W02628/SP-24	24 inch	Insertion Loss (Typ.)	0.6	0.64	0.7	0.81	0.99	dB	0.107
PE3W02628/SP-36	36 inch	Insertion Loss (Typ.)	0.64	0.7	0.79	0.97	1.24	dB	0.139
PE3W02628/SP-60	60 inch	Insertion Loss (Typ.)	0.73	0.83	0.98	1.28	1.72	dB	0.203
PE3W02628/SP-300	300 inch	Insertion Loss (Typ.)	1.65	2.15	2.9	4.38	6.6	dB	0.843

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.25 dB
Loss due to Connector 2:	0.25 dB
Base Weight:	0.074 pounds
Additional Weight per Inch:	0.00267 pounds

Mechanical Specifications

Cable Assembly

Width/Diameter	0.5 in [12.7 mm]
Weight	0.074 lbs [33.57 g]

Cable

Cable Type	LMR-240-UF
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	TPE, Black
Jacket Diameter	0.24 in [6.1 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.13 lbs-ft [0.18 N-m]
Flat Plate Crush	13 lbs/in [0.23 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax with Times Microwave Components with 270 Deg. Clock



PE3W02628/SP

Connectors

Description	Connector 1	Connector 2
Type	SMA Male Right Angle	SMA Male Right Angle
Specification	MIL-STD-348	MIL-STD-348
Impedance	50 Ohms	50 Ohms
Configuration	Right Angle	Right Angle
Contact Material and Plating	Brass/Phosphor Bronze, Gold	Brass/Phosphor Bronze, Gold
Contact Plating Specification	50 μinch	50 μinch
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 μinch	80 μinch
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	80 μinch	80 μinch
Hex Size	5/16 Inch	5/16 Inch

Environmental Specifications

Operating Range Temperature -40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax with Times Microwave Components with 270 Deg. Clock



PE3W02628/SP

Typical Performance Data

How to Order

Part Number Configuration: **PE3W02628/SP - xx uu**

Unit of Measure:
cm = Centimeters
<blank> = Inches

Length

Base Number

Example: PE3W02628/SP-12 = 12 inches long cable
PE3W02628/SP-100cm = 100 cm long cable

SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax with Times Microwave Components with 270 Deg. Clock from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.


Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR®-240-UF Coax with Times Microwave Components with 270 Deg. Clock PE3W02628/SP](#)

URL: <https://www.pasternack.com/sma-male-right-angle-to-sma-male-low-loss-cable-using-lmr-240-uf-with-270-deg.-clock-pe3w02628-sp-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W02628/SP CAD Drawing

SMA Male Right Angle to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax with Times Microwave Components with 270 Deg. Clock



REVISION			
ZONE	REV	DATE	CHANGED BY
	B	02/17/2026	TDUFRENE
DESCRIPTION		SRAUTUS	
ECO-15454			

[PE] PASTERNAK[®] an INFINITE [®] brand		Website: www.Pasternack.com Phone: 1.866.727.8376 1.949.261.1920		INTERPRET ALL DIMENSIONS AND TOLERANCES PER ASME Y14.5	
				SCALE: NONE	
				SHEET: 1 OF 1	

DESCRIPTION SMA MALE RIGHT ANGLE TO SMA MALE RIGHT ANGLE LOW LOSS CABLE USING LMR-240-UF COAX WITH TIMES MICROWAVE COMPONENTS WITH 270 DEG. CLOCK		ITEM NO. PE3W02628/SP	
SIZE A	CAGE CODE 53919	DRAWN BY HBKAKE	REV B

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES. DIMENSIONS IN [] ARE IN MILLIMETERS.		TOLERANCES:	
X = ±.2 [5]		FRACTIONS	
.XX = ±.02 [0.5]		± 1/32	
.XXX = ±.005 [0.13]		ANGLES ± 1°	
CABLE LENGTH TOLERANCES:			
>12 [305] ≤ 60 [1524] = ±.125 [-0]			
>60 [1524] ≤ 120 [3048] = ±.125 [-0]			
>120 [3048] ≤ 300 [7620] = ±.125 [-0]			
>300 [7620] = ±.125 [-0]			
ALL DIMENSIONS ARE FOR REFERENCE ONLY. DIMENSIONS OF INDIVIDUAL COMPONENTS MAY VARY IN SIZE AND LOCATION. COLORS MAY VARY.			

LENGTH NOTE 3

LMR-240-UF COAX CABLE

2X 8mm HEX

SMA MALE RIGHT ANGLE CONNECTOR FIXED POSITION

PASTERNAK.COM EXXXXXXXXXXX

LABEL SEE NOTE 1