

## TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink



### RF Cable Assemblies Technical Data Sheet


**PE3W04949/HS**

#### Configuration

- Connector 1: TNC Male
- Connector 2: SMA Male Right Angle
- Cable Type: LMR-240-UF

#### Features

- Max Frequency 5.8 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- TPE Jacket
- 500 Mating Cycles



#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W04949/HS TNC male to SMA male right angle cable using LMR-240-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to SMA cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240-UF coax. The PE3W04949/HS TNC male to SMA male cable assembly operates to 5.8 GHz. The right angle SMA interface on the LMR-240-UF cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink PE3W04949/HS](#)

# TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink



## RF Cable Assemblies Technical Data Sheet

**PE3W04949/HS**

### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		5.8	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		4.28 [14.04]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ω/1000ft [Ω/Km]
Jacket Spark			5,000	Vrms

### Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	0.25	0.5	1	2.5	5.8	GHz
Insertion Loss (Typ.)	0.046	0.066	0.095	0.15	0.24	dB/ft
	0.15	0.22	0.31	0.49	0.79	dB/m

#### Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.2 dB for the right angle connector and 0.1 dB for the straight connector.

### Mechanical Specifications

#### Cable Assembly

Weight 0.102 lbs [46.27 g]

#### Cable

Cable Type	LMR-240-UF
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink PE3W04949/HS](#)

# TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink



## RF Cable Assemblies Technical Data Sheet

**PE3W04949/HS**

Jacket Material	TPE, Black
Jacket Diameter	0.24 in [6.1 mm]
One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.13 lbs-ft [0.18 N-m]
Flat Plate Crush	13 lbs/in [0.23 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

### Connectors

Description	Connector 1	Connector 2
Type	TNC Male	SMA Male Right Angle
Specification		MIL-STD-348
Impedance	50 Ohms	50 Ohms
Mating Cycles	500	500
Contact Material and Plating	Brass, Gold	Brass/Phosphor Bronze, Gold
Contact Plating Specification	50 $\mu$ inch	50 $\mu$ inch
Dielectric Type	Teflon	Teflon
Body Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Body Plating Specification	80 $\mu$ inch	80 $\mu$ inch
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Tri-Metal
Coupling Nut Plating Specification	80 $\mu$ inch	80 $\mu$ inch
Hex Size		5/16 Inch
Torque	8 in-lbs [0.9 Nm]	7 in-lbs [0.79 Nm]

### Environmental Specifications

#### Temperature

Operating Range

-40 to +85 deg C

### Compliance Certifications

(see [product page](#) for current document)

### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink PE3W04949/HS](#)

TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink



**RF Cable Assemblies Technical Data Sheet**

**PE3W04949/HS**

**How to Order**

Part Number Configuration:

**PE3W04949/HS - xx uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3W04949/HS-12 = 12 inches long cable  
PE3W04949/HS-100cm = 100 cm long cable

TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink PE3W04949/HS](#)

URL: <https://www.pasternack.com/tnc-male-to-sma-male-low-loss-cable-using-lmr-240-uf-with-heatshrink-pe3w04949-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

# PE3W04949/HS CAD Drawing

TNC Male to SMA Male Right Angle Low Loss Cable Using LMR-240-UF Coax With Times Microwave Components with HeatShrink

