

N Male to TNC Male Cable Using RG223 Coax




PE3W02862

Configuration

- Connector 1: N Male
- Connector 2: TNC Male
- Cable Type: RG223
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- 66% Phase Velocity
- Double Shielded
- PVC Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W02862 type N male to TNC male cable using RG223 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack type N to TNC cable assembly has a male to male gender configuration with 50 ohm flexible RG223 coax. The PE3W02862 type N male to TNC male cable assembly operates to 6 GHz. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			500	Vrms

Specifications by Frequency



N Male to TNC Male Cable Using RG223 Coax

PE3W02862

Part Number	Length	Description	F1	F2	F3	F4	Units	Weight (lbs)
		Frequency	500	1000	2500	6000	MHz	
PE3W02862	Custom Lengths Available	Insertion Loss (Typ.)	0.09	0.13	0.21	0.36	dB/ft	
			0.3	0.43	0.69	1.19	dB/m	
PE3W02862-12	12 inch	Insertion Loss (Typ.)	0.29	0.33	0.41	0.56	dB	0.132
PE3W02862-24	24 inch	Insertion Loss (Typ.)	0.38	0.46	0.62	0.92	dB	0.164
PE3W02862-36	36 inch	Insertion Loss (Typ.)	0.47	0.59	0.83	1.28	dB	0.195
PE3W02862-60	60 inch	Insertion Loss (Typ.)	0.65	0.85	1.25	2	dB	0.257
PE3W02862-72	72 inch	Insertion Loss (Typ.)	0.74	0.98	1.46	2.36	dB	0.288

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1:	0.1 dB
Loss due to Connector 2:	0.1 dB
Base Weight:	0.132 pounds
Additional Weight per Inch:	0.00259 pounds

Mechanical Specifications

Cable Assembly

Weight	0.132 lbs [59.87 g]
--------	---------------------

Cable

Cable Type	RG223
Impedance	50 Ohms
Inner Conductor Type	Solid
Inner Conductor Material and Plating	Copper, Silver
Dielectric Type	PE
Number of Shields	2
Shield Layer 1	Silver Plated Copper Braid
Shield Layer 2	Silver Plated Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.209 in [5.31 mm]
Repeated Minimum Bend Radius	1 in [25.4 mm]

N Male to TNC Male Cable Using RG223 Coax



PE3W02862

Connectors

Description	Connector 1	Connector 2
Type	N Male	TNC Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Configuration	Straight	Straight
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 µin minimum	30 µin minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Tri-Metal	Brass, Nickel
Body Plating Specification		100 µin minimum
Coupling Nut Material and Plating	Brass, Tri-Metal	Brass, Nickel
Coupling Nut Plating Specification		100 µin minimum
Hex Size	18 mm	
Torque	9 in-lbs 1.02 Nm	

Environmental Specifications

Operating Range Temperature -40 to +80 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

N Male to TNC Male Cable Using RG223 Coax



PE3W02862

Typical Performance Data

How to Order

Part Number Configuration:

PE3W02862

- XX

uu

- Unit of Measure:
cm = Centimeters
<blank> = Inches

- Length

- Base Number

Example: PE3W02862-12 = 12 inches long cable
PE3W02862-100cm = 100 cm long cable

N Male to TNC Male Cable Using RG223 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [N Male to TNC Male Cable Using RG223 Coax PE3W02862](#)

URL: <https://www.pasternack.com/n-male-to-tnc-male-cable-using-rg223-pe3w02862-p.aspx>

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to implement improvements. Pasternack Enterprises reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack Enterprises does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack Enterprises does not assume liability arising out of the use of any part or document.

PE3W02862 CAD Drawing
N Male to TNC Male Cable Using RG223 Coax

