



HN Male to N Male Cable Using RG213 Coax

RF Cable Assemblies Technical Data Sheet

PE3W05409

Configuration

- Connector 1: HN Male
- Connector 2: N Male
- Cable Type: RG213

Features

- Max Frequency 1 GHz
- 66% Phase Velocity
- PVC Jacket

Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W05409 HN male to type N male cable using RG213 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack HN to type N cable assembly has a male to male gender configuration with 50 ohm flexible RG213 coax. The PE3W05409 HN male to type N male cable assembly operates to 1 GHz.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male to N Male Cable Using RG213 Coax PE3W05409](#)



HN Male to N Male Cable Using RG213 Coax

RF Cable Assemblies Technical Data Sheet
PE3W05409
Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		1,000	MHz
VSWR			1.4:1	
Velocity of Propagation		66		%
Capacitance		30.8 [101.05]		pF/ft [pF/m]
Operating Voltage (AC)			1,000	Vrms

Specifications by Frequency

Description	F1	F2	F3	F4	F5	Units
Frequency	100	250	500	1,000		MHz
Insertion Loss (Typ.)	0.021	0.034	0.053	0.08		dB/ft
	0.07	0.11	0.17	0.26		dB/m

Electrical Specification Notes:

Insertion Loss does not include the loss of the connectors. Insertion Loss is estimated as 0.1 dB per connector.

Mechanical Specifications
Cable Assembly

Weight 0.351 lbs [159.21 g]

Cable

Cable Type	RG213
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	PE
Number of Shields	1
Shield Layer 1	Copper Braid
Jacket Material	PVC, Black
Jacket Diameter	0.405 in [10.29 mm]

Repeated Minimum Bend Radius 1.6 in [40.64 mm]

 Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male to N Male Cable Using RG213 Coax PE3W05409](#)



HN Male to N Male Cable Using RG213 Coax

RF Cable Assemblies Technical Data Sheet
PE3W05409
Connectors

Description	Connector 1	Connector 2
Type	HN Male	N Male
Specification	MIL-STD-348A	MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification	30 μ in minimum	30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 μ in minimum	100 μ in minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification	100 μ in minimum	100 μ in minimum

Environmental Specifications
Temperature

Operating Range

-25 to +70 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male to N Male Cable Using RG213 Coax PE3W05409](#)



HN Male to N Male Cable Using RG213 Coax

RF Cable Assemblies Technical Data Sheet

PE3W05409

How to Order

Part Number Configuration:

PE3W05409

- **xx**

uu

Unit of Measure:
cm = Centimeters
<blank> = Inches
Length
Base Number

Example: PE3W05409-12 = 12 inches long cable
PE3W05409-100cm = 100 cm long cable

HN Male to N Male Cable Using RG213 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [HN Male to N Male Cable Using RG213 Coax PE3W05409](#)

URL: <https://www.pasternack.com/hn-male-to-n-male-cable-using-rg213-pe3w05409-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W05409 CAD Drawing
HN Male to N Male Cable Using RG213 Coax

