



## SMA Male to UHF Female Cable Using 53 Ohm RG55 Coax

### RF Cable Assemblies Technical Data Sheet

**PE3W03544**

#### Configuration

- Connector 1: SMA Male
- Connector 2: UHF Female
- Cable Type: RG55

#### Features

- 66% Phase Velocity
- Double Shielded
- PE Jacket

#### Applications

- General Purpose
- Laboratory Use

#### Description

Pasternack's PE3W03544 SMA male to UHF female cable using 53 ohm RG55 coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack SMA to UHF cable assembly has a male to female gender configuration with 53 ohm flexible RG55 coax. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

#### Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Velocity of Propagation		66		%
Capacitance		28.8 [94.49]		pF/ft [pF/m]

#### Mechanical Specifications

##### Cable Assembly

Weight 0.113 lbs [51.26 g]

##### Cable

Cable Type RG55  
Impedance 53 Ohms  
Inner Conductor Type Solid  
Inner Conductor Material and Plating Copper, Silver  
Dielectric Type PE  
Number of Shields 2

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to UHF Female Cable Using 53 Ohm RG55 Coax PE3W03544](#)



## SMA Male to UHF Female Cable Using 53 Ohm RG55 Coax

### RF Cable Assemblies Technical Data Sheet

**PE3W03544**

Shield Layer 1  
Shield Layer 2  
Jacket Material  
Jacket Diameter

Tinned Copper Braid  
Tinned Copper Braid  
PE, Black  
0.202 in [5.13 mm]

#### Connectors

Description	Connector 1	Connector 2
Type	SMA Male	UHF Female
Specification	MIL-STD-348A	
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Gold
Contact Plating Specification	50 µin minimum	
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification	100 µin minimum	
Coupling Nut Material and Plating	Brass, Nickel	
Coupling Nut Plating Specification	100 µin minimum	
Hex Size	5/16 inch	
Torque	3 in-lbs [0.34 Nm]	

**Compliance Certifications** (see [product page](#) for current document)

#### Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to UHF Female Cable Using 53 Ohm RG55 Coax PE3W03544](#)



## SMA Male to UHF Female Cable Using 53 Ohm RG55 Coax

### RF Cable Assemblies Technical Data Sheet

**PE3W03544**

#### How to Order

Part Number Configuration:

**PE3W03544**

- **xx**

**uu**

Unit of Measure:  
cm = Centimeters  
<blank> = Inches  
Length  
Base Number

Example: PE3W03544-12 = 12 inches long cable  
PE3W03544-100cm = 100 cm long cable

SMA Male to UHF Female Cable Using 53 Ohm RG55 Coax from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [SMA Male to UHF Female Cable Using 53 Ohm RG55 Coax PE3W03544](https://www.pasternack.com/sma-male-to-uhf-female-cable-using-rg55-pe3w03544-p.aspx)

URL: <https://www.pasternack.com/sma-male-to-uhf-female-cable-using-rg55-pe3w03544-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W03544 CAD Drawing  
SMA Male to UHF Female Cable Using 53 Ohm RG55 Coax

