



TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink

TECHNICAL DATA SHEET


PE3W05742/HS

Configuration

- Connector 1: TNC Male Right Angle
- Connector 2: N Male
- Cable Type: LMR-240-UF
- Coax Flex Type: Flexible

Features

- Max Frequency 6 GHz
- Shielding Effectivity > 90 dB
- 84% Phase Velocity
- Double Shielded
- TPE Jacket



Applications

- General Purpose
- Laboratory Use

Description

Pasternack's PE3W05742/HS TNC male right angle to type N male cable using LMR-240-UF coax is part of our full line of RF components available for same-day shipping. Pasternack's flexible RF cable assemblies are ideal for applications where tight bends and flexure are required. This Pasternack TNC to type N cable assembly has a male to male gender configuration with 50 ohm flexible LMR-240-UF coax. The PE3W05742/HS TNC male to type N male cable assembly operates to 6 GHz. The right angle TNC interface on the LMR-240-UF cable allows for easier connections in tight spaces. The double shielding of this Pasternack cable assembly provides excellent shielding effectiveness of better than 90 dB.

Custom versions of most RF cable assemblies can be built and shipped same day. Custom cable assembly lengths can be obtained by specifying the desired length on the web site at time of order or by contacting a sales representative. Other available RF cable assembly value added services include connector orientation or clocking, heat shrink booting and custom labeling. RF testing can also be performed to document the electrical performance of your cable assembly.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink PE3W05742/HS](#)



TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink

TECHNICAL DATA SHEET

PE3W05742/HS

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	DC		6	GHz
VSWR			1.4:1	
Velocity of Propagation		84		%
RF Shielding	90			dB
Group Delay		1.21 [3.97]		ns/ft [ns/m]
Capacitance		24.2 [79.4]		pF/ft [pF/m]
Inductance		0.06 [0.2]		uH/ft [uH/m]
DC Resistance Inner Conductor		4.28 [14.04]		Ω/1000ft [Ω/Km]
DC Resistance Outer Conductor		3.89 [12.76]		Ω/1000ft [Ω/Km]
Jacket Spark			5,000	Vrms

Specifications by Frequency

Part Number	Length	Description	F1	F2	F3	F4	F5	Units	Weight (lbs)
		Frequency	250	500	1000	2500	6000		
PE3W05742/HS	Custom Lengths Available	Insertion Loss (Typ.)	0.05	0.07	0.1	0.16	0.24	dB/ft	
			0.16	0.22	0.32	0.51	0.81	dB/m	
PE3W05742/HS-12	12 inch	Insertion Loss (Typ.)	0.35	0.37	0.4	0.46	0.55	dB	0.152
PE3W05742/HS-24	24 inch	Insertion Loss (Typ.)	0.4	0.44	0.5	0.61	0.79	dB	0.185
PE3W05742/HS-36	36 inch	Insertion Loss (Typ.)	0.44	0.5	0.59	0.77	1.04	dB	0.217
PE3W05742/HS-60	60 inch	Insertion Loss (Typ.)	0.53	0.63	0.78	1.08	1.52	dB	0.281
PE3W05742/HS-300	300 inch	Insertion Loss (Typ.)	1.45	1.95	2.7	4.18	6.4	dB	0.921

The insertion loss data for the base model does not include loss due to the connectors. Each length includes insertion loss due to the connectors.

Loss due to Connector 1: 0.2 dB
Loss due to Connector 2: 0.1 dB
Base Weight: 0.152 pounds
Additional Weight per Inch: 0.00267 pounds

Mechanical Specifications

Cable Assembly

Weight 0.152 lbs [68.95 g]

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink PE3W05742/HS](#)



TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink

TECHNICAL DATA SHEET

PE3W05742/HS

Cable

Cable Type	LMR-240-UF
Impedance	50 Ohms
Inner Conductor Type	Stranded
Inner Conductor Material and Plating	Copper
Dielectric Type	PE (F)
Number of Shields	2
Shield Layer 1	Aluminum Tape
Shield Layer 2	Tinned Copper Braid
Jacket Material	TPE, Black
Jacket Diameter	0.24 in [6.1 mm]

One Time Minimum Bend Radius	0.75 in [19.05 mm]
Repeated Minimum Bend Radius	2.5 in [63.5 mm]
Bending Moment	0.13 lbs-ft [0.18 N-m]
Flat Plate Crush	13 lbs/in [0.23 Kg/mm]
Tensile Strength	80 lbs [36.29 Kg]

Connectors

Description	Connector 1	Connector 2
Type	TNC Male Right Angle Threaded	N Male Threaded
Specification		MIL-STD-348A
Impedance	50 Ohms	50 Ohms
Contact Material and Plating	Brass, Gold	Brass, Gold
Contact Plating Specification		30 μ in minimum
Dielectric Type	PTFE	PTFE
Body Material and Plating	Brass, Nickel	Brass, Nickel
Body Plating Specification		100 μ in minimum
Coupling Nut Material and Plating	Brass, Nickel	Brass, Nickel
Coupling Nut Plating Specification		100 μ in minimum

Environmental Specifications

Temperature

Operating Range

-40 to +85 deg C

Compliance Certifications (see [product page](#) for current document)

Plotted and Other Data

Notes:

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink PE3W05742/HS](#)




TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink

TECHNICAL DATA SHEET

PE3W05742/HS

How to Order

Part Number Configuration:



Example: PE3W05742/HS-12 = 12 inches long cable
PE3W05742/HS-100cm = 100 cm long cable

TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink from Pasternack Enterprises has same day shipment for domestic and International orders. Our RF, microwave and millimeter wave products maintain a 99.4% availability and are part of the broadest selection in the industry.

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: [TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink PE3W05742/HS](#)

URL: <https://www.pasternack.com/tnc-male-right-angle-to-n-male-low-loss-cable-using-lmr-240-uf-with-heatshrink-pe3w05742-hs-p.aspx>

The information contained in this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part, in order to implement improvements. Pasternack reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. Pasternack does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and Pasternack does not assume any liability arising out of the use of any part or documentation.

PE3W05742/HS CAD Drawing

TNC Male Right Angle to N Male Low Loss Cable Using LMR-240-UF Coax with HeatShrink

